




Cable Length L		Part Number	Max. IL
Meters	[Inches]		
1m ± 0.05m	[39.37" ± 1.97"]	17-300870-01	0.50 dB
2m ± 0.05m	[78.74" ± 1.97"]	17-300870-02	0.51 dB
3m ± 0.05m	[118.11" ± 1.97"]	17-300870-03	0.51 dB
4m ± 0.08m	[157.48" ± 3.15"]	17-300870-04	0.51 dB
5m ± 0.08m	[196.85" ± 3.15"]	17-300870-05	0.52 dB
6m ± 0.08m	[236.22" ± 3.15"]	17-300870-06	0.52 dB
7m ± 0.08m	[275.59" ± 3.15"]	17-300870-07	0.52 dB
8m ± 0.15m	[314.96" ± 5.91"]	17-300870-08	0.53 dB
9m ± 0.15m	[354.33" ± 5.91"]	17-300870-09	0.53 dB
10m ± 0.15m	[393.70" ± 5.91"]	17-300870-10	0.54 dB
11m ± 0.15m	[433.07" ± 5.91"]	17-300870-11	0.54 dB
12m ± 0.15m	[472.44" ± 5.91"]	17-300870-12	0.54 dB
13m ± 0.15m	[511.81" ± 5.91"]	17-300870-13	0.55 dB
14m ± 0.15m	[551.18" ± 5.91"]	17-300870-14	0.55 dB
15m ± 0.15m	[590.55" ± 5.91"]	17-300870-15	0.55 dB
16m ± 0.30m	[629.92" ± 11.81"]	17-300870-16	0.56 dB
17m ± 0.30m	[669.29" ± 11.81"]	17-300870-17	0.56 dB
18m ± 0.30m	[708.66" ± 11.81"]	17-300870-18	0.56 dB
19m ± 0.30m	[748.03" ± 11.81"]	17-300870-19	0.57 dB
20m ± 0.30m	[787.40" ± 11.81"]	17-300870-20	0.57 dB

Cable Length L		Part Number	Max. IL
Meters	[Inches]		
21m ± 0.30m	[826.77" ± 11.81"]	17-300870-21	0.57 dB
22m ± 0.30m	[866.14" ± 11.81"]	17-300870-22	0.58 dB
23m ± 0.30m	[905.51" ± 11.81"]	17-300870-23	0.58 dB
24m ± 0.30m	[944.88" ± 11.81"]	17-300870-24	0.58 dB
25m ± 0.30m	[984.25" ± 11.81"]	17-300870-25	0.59 dB
26m ± 0.30m	[1023.62" ± 11.81"]	17-300870-26	0.59 dB
27m ± 0.30m	[1062.99" ± 11.81"]	17-300870-27	0.59 dB
28m ± 0.30m	[1102.36" ± 11.81"]	17-300870-28	0.60 dB
29m ± 0.30m	[1141.73" ± 11.81"]	17-300870-29	0.60 dB
30m ± 0.30m	[1181.10" ± 11.81"]	17-300870-30	0.61 dB
31m ± 0.30m	[1220.47" ± 11.81"]	17-300870-31	0.61 dB
32m ± 0.30m	[1259.84" ± 11.81"]	17-300870-32	0.61 dB
33m ± 0.30m	[1299.21" ± 11.81"]	17-300870-33	0.62 dB
34m ± 0.30m	[1338.58" ± 11.81"]	17-300870-34	0.62 dB
35m ± 0.35m	[1377.95" ± 13.78"]	17-300870-35	0.62 dB
36m ± 0.35m	[1417.32" ± 13.78"]	17-300870-36	0.63 dB
37m ± 0.35m	[1456.69" ± 13.78"]	17-300870-37	0.63 dB
38m ± 0.35m	[1496.06" ± 13.78"]	17-300870-38	0.63 dB
39m ± 0.35m	[1535.43" ± 13.78"]	17-300870-39	0.64 dB
40m ± 0.40m	[1574.80" ± 15.75"]	17-300870-40	0.64 dB

Cable Length L		Part Number	Max. IL
Meters	[Inches]		
41m ± 0.40m	[1614.17" ± 15.75"]	17-300870-41	0.64 dB
42m ± 0.40m	[1653.54" ± 15.75"]	17-300870-42	0.65 dB
43m ± 0.40m	[1692.91" ± 15.75"]	17-300870-43	0.65 dB
44m ± 0.40m	[1732.28" ± 15.75"]	17-300870-44	0.65 dB
45m ± 0.40m	[1771.65" ± 15.75"]	17-300870-45	0.66 dB
46m ± 0.40m	[1811.02" ± 15.75"]	17-300870-46	0.66 dB
47m ± 0.40m	[1850.39" ± 15.75"]	17-300870-47	0.66 dB
48m ± 0.40m	[1889.76" ± 15.75"]	17-300870-48	0.67 dB
49m ± 0.40m	[1929.13" ± 15.75"]	17-300870-49	0.67 dB
50m ± 0.50m	[1968.50" ± 19.69"]	17-300870-50	0.68 dB
51m ± 0.50m	[2007.87" ± 19.69"]	17-300870-51	0.68 dB
52m ± 0.50m	[2047.24" ± 19.69"]	17-300870-52	0.68 dB
53m ± 0.50m	[2208.33" ± 19.69"]	17-300870-53	0.69 dB
54m ± 0.50m	[2125.98" ± 19.69"]	17-300870-54	0.69 dB
55m ± 0.50m	[2165.35" ± 19.69"]	17-300870-55	0.69 dB
56m ± 0.50m	[2204.72" ± 19.69"]	17-300870-56	0.70 dB
57m ± 0.50m	[2244.09" ± 19.69"]	17-300870-57	0.70 dB
58m ± 0.50m	[2283.46" ± 19.69"]	17-300870-58	0.70 dB
59m ± 0.50m	[2322.83" ± 19.69"]	17-300870-59	0.71 dB
60m ± 0.60m	[2362.21" ± 23.62"]	17-300870-60	0.71 dB

Cable Length L		Part Number	Max. IL
Meters	[Inches]		
61m ± 0.60m	[2401.57" ± 23.62"]	17-300870-61	0.71 dB
62m ± 0.60m	[2440.95" ± 23.62"]	17-300870-62	0.72 dB
63m ± 0.60m	[2480.31" ± 23.62"]	17-300870-63	0.72 dB
64m ± 0.60m	[2519.68" ± 23.62"]	17-300870-64	0.72 dB
65m ± 0.60m	[2559.05" ± 23.62"]	17-300870-65	0.73 dB
66m ± 0.60m	[2598.42" ± 23.62"]	17-300870-66	0.73 dB
67m ± 0.60m	[2637.80" ± 23.62"]	17-300870-67	0.74 dB
68m ± 0.60m	[2677.16" ± 23.62"]	17-300870-68	0.74 dB
69m ± 0.60m	[2716.53" ± 23.62"]	17-300870-69	0.74 dB
70m ± 0.70m	[2755.91" ± 27.56"]	17-300870-70	0.75 dB
71m ± 0.70m	[2795.28" ± 27.56"]	17-300870-71	0.75 dB
72m ± 0.70m	[2834.65" ± 27.56"]	17-300870-72	0.75 dB
73m ± 0.70m	[2874.02" ± 27.56"]	17-300870-73	0.76 dB
74m ± 0.70m	[2913.39" ± 27.56"]	17-300870-74	0.76 dB
75m ± 0.70m	[2952.76" ± 27.56"]	17-300870-75	0.76 dB
76m ± 0.70m	[2992.13" ± 27.56"]	17-300870-76	0.77 dB
77m ± 0.70m	[3031.50" ± 27.56"]	17-300870-77	0.77 dB
78m ± 0.70m	[3070.87" ± 27.56"]	17-300870-78	0.77 dB
79m ± 0.70m	[3110.24" ± 27.56"]	17-300870-79	0.78 dB
80m ± 0.80m	[3149.61" ± 31.50"]	17-300870-80	0.78 dB

Preliminary Drawing

NOTES:

1. MAXIMUM CONNECTOR INSERTION LOSS (IL): 0.5dB,
PLUS CABLE ATTENUATION OF 3.5dB PER 1.5 km AT 850nm

2. TEST DATA PROVIDED WITH EACH ASSEMBLY

A ← → B

B ← → A

FIBER PATH DETAIL

Directive 2002/95/EC RoHS Compliant

THIS DRAWING MAY NOT BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, WITHOUT THE WRITTEN PERMISSION OF CONEC CORPORATION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION.	Customer:			Tolerance Unless otherwise specified			Scale: NTS		Dim. in m [inches]			
	Name	Title	Approval Date				Material:					
				2012	Date		Title:					
				Draw.	Jul. 23		IP67 Industrial Duplex LC (ODVA)					
DO NOT ALTER CAD DRAWING BY HAND				Appd.	Jul. 23		MM Fiber Optic Patch Cords (62.5/125um)					
							Nickel Plated Zinc Die-Cast Version					
							Drawing No.: 17K1A344					
							Part No.: SEE TABLE					
Rev. Changes				Date	Name	DIN A3		Sheet 1/1				