


MATERIALS

BODY	PASSIVATED STAINLESS STEEL
CONTACT	GOLD PLATED
INSULATOR	PTFE
COUPLING NUT	BRASS NICKEL PLATED



SPECIFICATIONS

FREQUENCY RANGE: DC TO 18 GHz
ATTENUATION: 40 dB
IMPEDANCE: 50 OHMS
ACCURACY: ± 1.50 dB
VSWR: 1.35:1 MAXIMUM
AVG. POWER HANDLING CAPABILITY: 2 WATTS



PASTERNAK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE7005-40

DES. SMA ATTENUATOR, 40 dB FREQUENCY
RANGE: DC TO 18 GHz

SIZE A	FSCM NO. 53919	CAD FILE 081805	SCALE N/A	127
--------	----------------	-----------------	-----------	-----

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.