


CN1 CONTACT No.	1	2	3	4	5	SHELL
SIGNAL	Vcc	DATA-	DATA+	NON WIRING	GND	BRAIDED WIRE + DRAIN WIRE
WIRING COLOR	RED	WHITE	GREEN		BLACK	
CN2 CONTACT No.	1	2	3		4	SHELL



2 THIS PRODUCT IS USING THE CABLE MADE FORM LTK INTERNATIONAL LIMITED, AND QU-USB-156D.

FORM NC0011-5-7

APPLICABLE STANDARD		USB2.0 SPECIFICATION AND MICRO-USB CABLE AND CONNECTORS SPECIFICATION.	
RATING	OPERATING TEMPERATURE RANGE	-30°C TO +80°C	-30°C TO +80°C
	VOLTAGE	AC 30V	
	CURRENT		SIGNAL ONLY 1.0 A/pin POWER APPLY 1.8 A/pin (PIN No.1, No.5) 0.5 A/pin (PIN No.2-No.4)
SPECIFICATIONS			
ITEM	TEST METHOD	REQUIREMENTS	QT AT
CONSTRUCTION			
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X X
MARKING	CONFIRMED VISUALLY.		X X
ELECTRICAL CHARACTERISTICS			
VOLTAGE PROOF	100 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X X
CONTACT RESISTANCE	100 mA DC.	CONTACT No.1,5,340 mΩ MAX. Δ CONTACT No.2,3,470 mΩ MAX.	X X
COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED
1	DIS-E-002836	MO. SHIMOYAMA	KN. ICHIKAWA
REMARK		APPROVED	DATE
A connector independent performance is based on CL242-0002-4. HIROSE will not guarantee the performance on these specifications in case this product will be mated with the others which is not HIROSE'S. Unless otherwise specified, refer to USB2.0 or EIA 364 .		KN. ICHIKAWA	09.09.15
		CHECKED	09.03.30
		DESIGNED	09.03.30
		DRAWN	09.03.27
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC4-126987-00
SPECIFICATION SHEET		PART NO.	ZX40-B-5S-1500-STD A
HIROSE ELECTRIC CO., LTD.		CODE NO.	CL242-1007-3-00 Δ 1/1