


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PANDUIT *<br>PART NO. | BUNDLE DIA.    |                | A<br>in<br>(mm) | B<br>in<br>(mm) | C<br>in<br>(mm) | D<br>in<br>(mm) | E<br>in<br>(mm) | F<br>in<br>(mm) | G<br>in<br>(mm) | MIN. LOOP<br>TENSILE lbs<br>(N) | CROSS-<br>SECTION | TIP<br>STYLE | WEIGHT<br>lbs/100pcs<br>(g) |
|-----------------------|----------------|----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|---------------------------------|-------------------|--------------|-----------------------------|
|                       | MIN in<br>(mm) | MAX in<br>(mm) |                 |                 |                 |                 |                 |                 |                 |                                 |                   |              |                             |
| PRT1S                 | .06<br>(1.5)   | 1.00<br>(25)   | .052<br>(1.3)   | .190<br>(4.8)   | .258<br>(6.5)   | .219<br>(5.6)   | .316<br>(8.0)   | 4.8<br>(122)    | .318<br>(8.1)   | 50<br>(222)                     | STANDARD          | CURVED       | .13<br>(59)                 |
| PRT1.5S               | .06<br>(1.5)   | 1.50<br>(38)   | .052<br>(1.3)   | .190<br>(4.8)   | .258<br>(6.5)   | .219<br>(5.6)   | .316<br>(8.0)   | 6.3<br>(160)    | .318<br>(8.1)   | 50<br>(222)                     | STANDARD          | CURVED       | .26<br>(119)                |
| PRT2S                 | .06<br>(1.5)   | 1.88<br>(48)   | .052<br>(1.3)   | .190<br>(4.8)   | .258<br>(6.5)   | .219<br>(5.6)   | .316<br>(8.0)   | 7.4<br>(188)    | .318<br>(8.1)   | 50<br>(222)                     | STANDARD          | CURVED       | .29<br>(132)                |
| PRT3S                 | .06<br>(1.5)   | 3.00<br>(76)   | .052<br>(1.3)   | .190<br>(4.8)   | .265<br>(6.7)   | .219<br>(5.6)   | .337<br>(8.6)   | 11.5<br>(292)   | .318<br>(8.1)   | 50<br>(222)                     | STANDARD          | CURVED       | .45<br>(205)                |
| PRT4S                 | .06<br>(1.5)   | 4.00<br>(102)  | .052<br>(1.3)   | .190<br>(4.8)   | .265<br>(6.7)   | .219<br>(5.6)   | .337<br>(8.6)   | 14.5<br>(368)   | .318<br>(8.1)   | 50<br>(222)                     | STANDARD          | CURVED       | .56<br>(255)                |

NOTES:

\* 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATIONS FOR PACKAGE SIZE AND PART COLOR.

|     |         |     |     |                                         |  |      |    |      |     | DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.                                                                                   |                     |                                                                                               |                        |
|-----|---------|-----|-----|-----------------------------------------|--|------|----|------|-----|----------------------------------------------------------------------------------------------------------------------------------|---------------------|-----------------------------------------------------------------------------------------------|------------------------|
|     |         |     |     |                                         |  |      |    |      |     | PANDUIT CORP. TINLEY PARK, ILLINOIS                                                                                              |                     |                                                                                               |                        |
|     |         |     |     |                                         |  |      |    |      |     | PAN-TY CABLE TIES<br>RELEASABLE SERIES                                                                                           |                     |                                                                                               |                        |
|     |         |     |     |                                         |  |      |    |      |     | UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE:<br>(.X) ± .0005 (XXX) ± .020 (.51)<br>(.XX) ± .02 (.5) ANGLES ± .0005 |                     | UNLESS OTHERWISE SPECIFIED,<br>ALL DIMENSIONS ARE GIVEN<br>IN INCHES, THIRD ANGLE PROJECTION. |                        |
| --  | ----    | --- |     | CORRECTED MATERIAL NAME                 |  | ---- | -- |      |     | DRAWN BY<br>CEW                                                                                                                  | MAT'L:<br>NYLON 6.6 |                                                                                               | SCALE<br>NONE          |
| 13  | 6/22/05 | ERW |     | ADDED TOLERANCE TO DIMENSIONS 'A' & 'B' |  | 4472 | 13 |      |     | DATE<br>7-31-85                                                                                                                  |                     |                                                                                               | DRAWING NO.<br>SS-4472 |
| REV | DATE    | BY  | CHK | DESCRIPTION                             |  | ECN  | R  | CUST | SUP | CHK'D<br>HVP                                                                                                                     |                     |                                                                                               | SHEET 1 OF 2           |
|     |         |     |     |                                         |  |      |    |      |     |                                                                                                                                  |                     |                                                                                               | DWG<br>A<br>SIZE       |