


SERIES 1080 - MINIATURE SNAP-ACTION SWITCHES

TO 21 (8) A 250 V AC



PRODUCT FEATURES

- ◆ The precise mounting of the moving contact part (milled bearing blade) offers optimum snap-action even with slow actuation
- ◆ Wide range of ratings from 3 (1) A 250 V AC to 21 (8) A 250 V AC
- ◆ Versions with gold-plated contacts for signal current applications
- ◆ Various auxiliary actuators, two suspension points

ON REQUEST

- ◆ Low operating forces (≤ 0.15 N)
- ◆ Customized additional actuators
- ◆ Plug connection 4.8 x 0.5

Design	DIN 41635 A
Mechanical life endurance	2E6 (basic type 1080) 20E4 (basic type 1085)
Contact resistance (new condition)	< 100 mOhm (1 A 12 V DC)
Insulation resistance (new condition)	> 100 MOhm (500 V DC)
Voltage strength at 250 V	1 500 V function insulation / basic insulation 3 000 V reinforced insulation (depending on installation situation) 500 V small contact distance
Proof tracking	250 PTI
Insulation spacing	acc. to EN 61058 for reinforced or double insulation
Protection type	IP 40 (actuator side)
Ambient temperature	-40 °C ... +125 °C
Flammability	UL 94 V-0
Heat and fire resistance	850 °C (category D)
Material	actuator: PETP glass fiber-reinforced additional actuator: stainless steel housing: PA glass fiber-reinforced / PETP glass fiber-reinforced connections: silver-plated / CuZn
Bounce time	< 10 ms
Approval marks	  
Suitable for appliances of protection class II under compliance with the installation conditions required on the equipment side	



ROCKER SWITCHES

PUSHBUTTON SWITCHES

TOGGLE SWITCHES

SLIDE SWITCHES

ROTARY SWITCHES

FOOT SWITCHES

POWER TOOL SWITCHES

TACT AND KEY SWITCHES

SNAP-ACTION SWITCHES

MICRO-SIGNAL SWITCHES

SENSORS

SERIES 1080 - MINIATURE SNAP-ACTION SWITCHES

TO 21 (8) A 250 V AC


[illegible]

SERIES 1080 - MINIATURE SNAP-ACTION SWITCHES

TO 21 (8) A 250 V AC



	Changeover switch (SPDT momentary)				
	1085.0203	1085.0403	1085.5203	1080.0279	1085.0375
21 (8) A 250 V AC 1E4					
16 (8) A 250 V AC 1E4					
16 (4) A 250 V AC 5E4					
16 (4) A 250 V AC 25E3	●	●	●		
10 (4) A 250 V AC 25E3					
6 (3) A 250 V AC 6E4				●	
6 (2) A 250 V AC 5E4					
4 (4) A 250 V AC 5E4					
3 (1) A 250 V AC 5E4					
3 (1) A 250 V AC 25E3					●
21 A 250 V AC 2 HP					
21 A 125 V AC 1 HP					
16 A 250 V AC 1/2 HP					
16 A 125 - 250 V AC 1/2 HP	●	●	●		
16 A 125 V AC 1/3 HP					
10 A 250 V AC 1/3 HP					
10 A 125 V AC 1/8 HP					
6 A 250 V AC 1/4 HP				●	
6 A 125 V AC 1/10 HP				●	
3 A 125 - 250 V AC					●
Connection type					
Connection description		6.3			standing
Contact material	Ag	Ag	Ag	Au	Ag
Operating force in N	≤ 4.0	≤ 4.0	≤ 1.8	≤ 1.0	≤ 1.7
Operating position (OP) in mm	14.7 ± 0.5	14.7 ± 0.5	15.3 ± 1.5	14.7 ± 0.5	14.7 ± 0.5
Difference travel max. in mm	0.3	0.3	0.7	0.3	0.3
Free position (FP) max. in mm	16.2	16.2	19.5	16.2	16.2
Permissible total travel position (TP) in mm	13.2	13.2	12.5	13.2	13.2
Actuator description					
Lever drawing			L02		
Contact distance	< 3	< 3	< 3	< 3	< 3
EN 60335 cap. 30 conform "G"					
Stock version		●			



ROCKER SWITCHES

PUSHBUTTON SWITCHES

TOGGLE SWITCHES

SLIDE SWITCHES

ROTARY SWITCHES

FOOT SWITCHES

POWER TOOL SWITCHES

TACT AND KEY SWITCHES

SNAP-ACTION SWITCHES

MICRO-SIGNAL SWITCHES


SENSORS

SERIES 1080 - MINIATURE SNAP-ACTION SWITCHES


TO 21 (8) A 250 V AC




Terminal variants




Quick-connect terminal 4.8 x 0.8




Quick-connect terminal 6.3




Quick-connect terminal 6.3
PITCH 5




Quick-connect terminal 6.3
PITCH 7



Solder terminal




Short solder terminal



PCB terminal standing



Switching positions




FP: free position
OP: operating position
TP: total travel position

SERIES 1080 - MINIATURE SNAP-ACTION SWITCHES


TO 21 (8) A 250 V AC




Auxiliary actuators




L01: straight lever
191.080.091




L02: straight lever
191.080.101




L03: straight lever




L11: roller lever
191.079.013



L12: roller lever
191.079.023



L21: simulated roller
191.080.451



L22: simulated roller
191.080.471

ROCKER SWITCHES

PUSHBUTTON SWITCHES

TOGGLE SWITCHES

SLIDE SWITCHES

ROTARY SWITCHES

FOOT SWITCHES

POWER TOOL SWITCHES

TACT AND KEY SWITCHES

SNAP-ACTION SWITCHES

MICRO-SIGNAL SWITCHES

SENSORS