


TENTATIVE TOSHIBA PHOTOCOUPLER GaAs IRED & PHOTO-TRIAC

TLP3530

TRIAC DRIVER
PROGRAMMABLE CONTROLLERS
AC-OUTPUT MODULE
SOLID STATE RELAY

The TOSHIBA TLP3530 consists of a photo-triac optically coupled to a gallium arsenide infrared emitting diode in a 16 lead plastic DIP package for 2 channels output.

- Peak Off-State Voltage : 400 V (min)
- Trigger LED Current : 10 mA (max)
- On-State Current : 1.0 Arms (max per 1ch)
1.4 Arms (max per 2ch)
- Isolation Voltage : 2500 Vrms (min)



Weight : 1.09 g


Trigger LED Current

CLASSI- FICATION*	TRIGGER LED CURRENT (mA)		MARKING OF CLASSIFICATION
	V _T = 6 V, T _a = 25°C		
	Min	Max	
(IFT7)	—	7.0	T7
Blank	—	10	T7, Blank

* : (IFT7) : TLP3530 (IFT7)
(Note) : Application type name for certification test, please use standard product type name, i.e.
TLP3530 (IFT7) : TLP3530

3, 6 : ANODE
2, 7 : CATHODE
4, 5 : N.C
12, 13 : TRIAC T2 (COMMON)
10, 15 : TRIAC T1
9, 16 : TRIAC GATE*

PIN CONFIGURATION (TOP VIEW)



000707EBC2

● TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property. In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc.

● The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.

MAXIMUM RATINGS (Ta = 25°C)

CHARACTERISTIC			SYMBOL	RATING	UNIT
LED	Forward Current		I _F	50	mA
	Forward Current Derating (Ta ≥ 53°C)		ΔI _F / °C	−0.7	mA / °C
	Peak Forward Current (100 μs pulse, 100 pps)		I _{FP}	1	A
	Reverse Voltage		V _R	5	V
	Junction Temperature		T _j	125	°C
DETECTOR	Off-State Output Terminal Voltage		V _{DRM}	400	V
	On-State RMS Current	Ta = 40°C	I _T (RMS)	1.0 (per 1 ch)	A
				1.4 (per 2 ch)	
		Ta = 60°C		0.7 (per 1 ch)	
				1.0 (per 2 ch)	
	On-State Current Derating (Ta ≥ 40°C)		ΔI _T / °C	−14.3 (per 1 ch) −20.0 (per 2 ch)	mA / °C
	Peak Current from Snubber Circuit (100 μs pulse, 120 pps)		I _{SP}	2	A
	Peak Nonrepetitive Surge Current (50 Hz, Peak)		I _{TSM}	10	A
	Junction Temperature		T _j	110	°C
	Storage Temperature Range		T _{stg}	−40~125	°C
	Operating Temperature Range		T _{opr}	−20~80	°C
	Lead Soldering Temperature (10 s)		T _{sol}	260	°C
	Isolation Voltage (AC, 1 min., R.H. ≤ 60%) (Note)		BV _S	2500	Vrms

(Note) : Device considered a two terminal : LED side pins shorted together and DETECTOR side pins shorted together.

RECOMMENDED OPERATING CONDITIONS

CHARACTERISTIC	SYMBOL	Min	Typ.	Max	UNIT
Supply Voltage	V _{AC}	—	—	120	Vac
Forward Voltage	I _F	15	20	25	mA
Peak Current from Snubber Circuit	I _{SP}	—	—	1	A
Operating Temperature	T _{opr}	−20	—	80	°C

000707EBC2'

- Gallium arsenide (GaAs) is a substance used in the products described in this document. GaAs dust and fumes are toxic. Do not break, cut or pulverize the product, or use chemicals to dissolve them. When disposing of the products, follow the appropriate regulations. Do not dispose of the products with other industrial waste or with domestic garbage.
- The products described in this document are subject to the foreign exchange and foreign trade laws.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.

INDIVIDUAL ELECTRICAL CHARACTERISTICS (Ta = 25°C)

CHARACTERISTIC		SYMBOL	TEST CONDITION	Min	Typ.	Max	UNIT
LED	Forward Voltage	V_F	$I_F = 10 \text{ mA}$	1.0	1.15	1.3	V
	Reverse Current	I_R	$V_R = 5 \text{ V}$	—	—	10	μA
	Capacitance	C_T	$V = 0, f = 1 \text{ MHz}$	—	30	—	pF
DETECTOR	Peak Off-State Current	I_{DRM}	$V_{DRM} = 400 \text{ V}, T_a = 110^\circ\text{C}$	—	—	100	μA
	Peak On-State Voltage	V_{TM}	$I_{TM} = 1.5 \text{ A}$	—	—	3.0	V
	Holding Current	I_H	$R_L = 100 \Omega$	—	—	25	mA
	Critical Rate of Rise of Off-State Voltage	dv/dt	$V_{in} = 250 \text{ V}$	200	500	—	$\text{V} / \mu\text{s}$
	Critical Rate of Rise of Commutating Voltage	$dv/dt(c)$	$V_{in} = 120 \text{ V}_{rms}, I_T = 1.0 \text{ A}_{rms}$	—	5	—	$\text{V} / \mu\text{s}$

COUPLED ELECTRICAL CHARACTERISTICS (Ta = 25°C)

CHARACTERISTIC	SYMBOL	TEST CONDITION	Min	Typ.	Max	UNIT
Trigger LED Current	I_{FT}	$V_T = 6 \text{ V}$	—	—	10	mA
Capacitance (Input to Output)	C_S	$V_S = 0, f = 1 \text{ MHz}$	—	1.5	—	pF
Isolation Resistance	R_S	$V_S = 500 \text{ V}, \text{R.H.} \leq 60\%$	5×10^{10}	10^{14}	—	Ω
Isolation Voltage	BV_S	AC, 1 minute	2500	—	—	V_{rms}
		AC, 1 second, in oil	—	5000	—	
		DC, 1 minute, in oil	—	5000	—	V_{dc}

