



Thyristor/Diode and Thyristor/Thyristor, 430 A (SUPER MAGN-A-PAK™ Power Modules)

**SUPER MAGN-A-PAK™****FEATURES**

- High current capability
- High surge capability
- High voltage ratings up to 2000 V
- 3000 V_{RMS} isolating voltage with non-toxic substrate
- Industrial standard package
- UL recognition pending
- Lead (Pb)-free

**RoHS**
COMPLIANT**TYPICAL APPLICATIONS**

- Motor starters
- DC motor controls - AC motor controls
- Uninterruptable power supplies
- Wind mill

PRODUCT SUMMARY

$I_{T(AV)}$	430 A
-------------	-------

MAJOR RATINGS AND CHARACTERISTICS

SYMBOL	CHARACTERISTICS	VALUES	UNITS
$I_{T(AV)}$	82 °C	430	A
$I_{T(RMS)}$		675	A
	T_C	82	°C
I_{TSM}	50 Hz	15.7	kA
	60 Hz	16.4	
I^2t	50 Hz	1232	kA ² s
	60 Hz	1125	
$I^2\sqrt{t}$		12 320	kA ² √s
V_{RRM}	Range	1600 to 2000	V
T_J	Range	- 40 to 150	°C
T_{Stg}		- 40 to 130	

ELECTRICAL SPECIFICATIONS**VOLTAGE RATINGS**

TYPE NUMBER	VOLTAGE CODE	V_{RRM}/V_{DRM} , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	V_{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I_{RRM}/I_{DRM} MAXIMUM AT $T_J = T_J$ MAXIMUM mA
VSK.430..	16	1600	1700	100
	18	1800	1900	
	20	2000	2100	

ON-STATE CONDUCTION							
PARAMETER	SYMBOL	TEST CONDITIONS			VALUES	UNITS	
Maximum average on-state current at case temperature	$I_{T(AV)}$, $I_{F(AV)}$	180° conduction, half sine wave			430	A	
					82	°C	
Maximum RMS on-state current	$I_{T(RMS)}$	180° conduction, half sine wave at $T_C = 82\text{ °C}$			675	A	
Maximum peak, one-cycle, non-repetitive surge current	I_{TSM} , I_{FSM}	t = 10 ms	No voltage reapplied	Sinusoidal half wave, initial $T_J = T_J$ maximum	15.7	kA	
		t = 8.3 ms			16.4		
		t = 10 ms	100 % V_{RRM} reapplied		13.2		kA ² s
		t = 8.3 ms			13.8		
Maximum I^2t for fusing	I^2t	t = 10 ms	No voltage reapplied		1232		
		t = 8.3 ms			1125		
		t = 10 ms	100 % V_{RRM} reapplied		871		
		t = 8.3 ms			795		
Maximum $I^2\sqrt{t}$ for fusing	$I^2\sqrt{t}$	t = 0.1 to 10 ms, no voltage reapplied			12 320	kA ² √s	
Low level value of threshold voltage	$V_{F(TO)1}$	$(16.7\text{ \%} \times \pi \times I_{T(AV)} < I < \pi \times I_{T(AV)})$, $T_J = T_J$ maximum			0.96	V	
High level value of threshold voltage	$V_{F(TO)2}$	$(I > \pi \times I_{T(AV)})$, $T_J = T_J$ maximum			1.06		
Low level value of on-state slope resistance	r_{f1}	$(16.7\text{ \%} \times \pi \times I_{T(AV)} < I < \pi \times I_{T(AV)})$, $T_J = T_J$ maximum			0.51	mΩ	
High level value of on-state slope resistance	r_{f2}	$(I > \pi \times I_{T(AV)})$, $T_J = T_J$ maximum			0.45		
Maximum on-state voltage drop	V_{TM}	$I_{pk} = 1500\text{ A}$, $T_J = 25\text{ °C}$, $t_p = 10\text{ ms}$ sine pulse			1.65	V	
Maximum forward voltage drop	V_{FM}	$I_{pk} = 1500\text{ A}$, $T_J = 25\text{ °C}$, $t_p = 10\text{ ms}$ sine pulse			1.65	V	
Maximum holding current	I_H	$T_J = 25\text{ °C}$, anode supply 12 V resistive load			500	mA	
Typical latching current	I_L				1000		

SWITCHING				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum rate of rise of turned-on current	di/dt	$T_J = T_J\text{ maximum}$, $I_{TM} = 400\text{ A}$, V_{DRM} applied	1000	A/μs
Typical delay time	t_d	Gate current 1 A, $di_g/dt = 1\text{ A/μs}$ $V_d = 0.67\% V_{DRM}$, $T_J = 25\text{ °C}$	2.0	μs
Typical turn-off time	t_q	$I_{TM} = 750\text{ A}$, $T_J = T_J\text{ maximum}$, $di/dt = -60\text{ A/μs}$ $V_R = 50$, $dV/dt = 20\text{ V/μs}$, Gate 0 V 100 Ω	200	

BLOCKING				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum critical rate of rise of off-state voltage	dV/dt	$T_J = 130\text{ °C}$, linear to $V_D = 80\% V_{DRM}$	1000	V/μs
RMS insulation voltage	V_{INS}	$t = 1\text{ s}$	3000	V
Maximum peak reverse and off-state leakage current	I_{RRM} , I_{DRM}	$T_J = T_J\text{ maximum}$, rated V_{DRM}/V_{RRM} applied	100	mA

**Thyristor/Diode and Thyristor/Thyristor, 430 A Vishay High Power Products
(SUPER MAGN-A-PAK™ Power Modules)**

THERMAL AND MECHANICAL SPECIFICATIONS				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction operating temperature range	T_J		- 40 to 130	°C
Maximum storage temperature range	T_{Stg}		- 40 to 150	
Maximum thermal resistance, junction to case per junction	R_{thJC}	DC operation	0.065	K/W
Maximum thermal resistance, case to heatsink	R_{thC-hs}		0.02	
Mounting torque $\pm 10\%$ SMAP to heatsink busbar to SMAP		A mounting compound is recommended and the torque should be rechecked after a period of 3 hours to allow for the spread of the compound.	6 to 8	Nm
			12 to 15	
Approximate weight			1500	g
Case style		See dimensions - link at the end of datasheet	SUPER MAGN-A-PAK	

ΔR_{thJC} CONDUCTION				
CONDUCTION ANGLE	SINUSOIDAL CONDUCTION	RECTANGULAR CONDUCTION	TEST CONDITIONS	UNITS
180°	0.009	0.006	$T_J = T_J$ maximum	K/W
120°	0.011	0.011		
90°	0.014	0.015		
60°	0.021	0.022		
30°	0.037	0.038		

Note

- The table above shows the increment of thermal resistance R_{thJC} when devices operate at different conduction angles than DC




Fig. 1 - Current Ratings Characteristics




Fig. 4 - On-State Power Loss Characteristics




Fig. 2 - Current Ratings Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 3 - On-State Power Loss Characteristics




Fig. 6 - Maximum Non-Repetitive Surge Current



Thyristor/Diode and Thyristor/Thyristor, 430 A Vishay High Power Products (SUPER MAGN-A-PAK™ Power Modules)




Fig. 7 - On-State Power Loss Characteristics




Fig. 8 - On-State Power Loss Characteristics




Fig. 9 - On-State Power Loss Characteristics

VSK.430..PbF Series



Vishay High Power Products Thyristor/Diode and Thyristor/Thyristor, 430 A
(SUPER MAGN-A-PAK™ Power Modules)




Fig. 10 - On-State Voltage Drop Characteristics




Fig. 11 - Thermal Impedance Z_{thJC} Characteristics




Fig. 12 - Gate Characteristics

ORDERING INFORMATION TABLE


Device code	VSK	T	430	-	20	PbF
	①	②	③		④	⑤
①	-	Module type				
②	-	Circuit configuration (see end of datasheet)				
③	-	Current rating				
④	-	Voltage code x 100 = V_{RRM} (see Voltage Ratings table)				
⑤	-	Lead (Pb)-free				

Note

- To order the optional hardware go to www.vishay.com/doc?95172



CIRCUIT CONFIGURATION



LINKS TO RELATED DOCUMENTS

Dimensions

<http://www.vishay.com/doc?95283>



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[VSKL430-18](#) [VSKH430-16](#) [VSKT430-16](#) [VSKT430-18](#) [VSKT430-20](#) [VS-VSKT430-20PBF](#) [VS-VSKT430-18PBF](#)
[VS-VSKH430-16PBF](#) [IRKH430-16](#) [IRKL430-18](#) [IRKT430-16](#) [IRKT430-18](#) [IRKT430-20](#) [VSKT430-16PBF](#) [VSKT430-20PBF](#) [VS-VSKL430-18PBF](#) [VS-VSKT430-16PBF](#)