

TDA Series

Ultra-miniature Surface Mount Half-pitch DIP Switches

NEW!

H

DIP



Features/Benefits

- Bifurcated contact for increased electrical reliability
- Process sealed for surface mount soldering and washable processing
- RoHS compliant

Typical Applications

- Hand-held electronic devices
- Portable computer and electronic devices
- Instrumentation and controls

Specifications

SWITCH FUNCTION: SPST – 1, 2, 4, 6, 8 & 10 positions.

CONTACT RATING:

24 V DC, 25 mA (switching).

50 V DC, 100 mA (steady state).

MECHANICAL AND ELECTRICAL LIFE: 1,000 cycles.

CONTACT RESISTANCE: 100 mΩ max.

INSULATION RESISTANCE: 100 MΩ @ 100 V DC min.

DIELECTRIC STRENGTH: 300 V AC min.

STORAGE TEMPERATURE: -40°C to 85°C.

OPERATING TEMPERATURE: -40°C to 85°C.

OPERATING FORCE: 4.9N max.

SOLDERABILITY: Per MIL-STD-202F method 208D, or

EIA RS-186E method 9 (1 hour steam aging).

PACKAGING: Switches supplied in rigid dispensing tubes in full tube quantities only, this may affect order quantity. Numbers of switches per tube varies with model. Tape and reel packaging quantity varies with model.

Materials

CASE & COVER: PPS (UL94V-0)

ACTUATOR: LCP (UL94V-0).

CONTACTS: Copper alloy, with gold plate over nickel plate.

TERMINALS: Copper alloy, with gold flash over nickel plate.

All terminals are insert molded.

TAPE SEAL: Polyimide.


Note: Specifications and materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center.

Note: All switches supplied in "OFF" position.

How To Order

The Build-A Switch concept allows you to mix and match options to create the switch you need. Below is a complete listing of options shown in catalog. To order, simply select desired option from each category and place in the appropriate box.

All switches supplied in "OFF" position.



* TDA01H0JB1R is not available, TDA01 only offered in tape & reel



Third Angle
Projection


Dimensions are shown: mm

Specifications and dimensions subject to change











TDA Series





Ultra-miniature Surface Mount Half-pitch DIP Switches



TDA08H0SB1



TDA10H0JB1



Tube Package

ROHS PART NUMBER	NO. POS.	DIM. 'A'	QUANTITY PER TUBE
TDA02H0_B1	2	3,67	125
TDA04H0_B1	4	6,21	70
TDA06H0_B1	6	8,75	50
TDA08H0_B1	8	11,29	40
TDA10H0_B1	10	13,83	30

Schematic

SPST

Tape & Reel Package

ROHS PART NUMBER	NO. POS.	DIM. 'W'	QUANTITY PER REEL
TDA01H0SB1R*	1	16,0	2500
TDA02H0_B1R	2	16,0	2000
TDA04H0_B1R	4	16,0	2000
TDA06H0_B1R	6	16,0	2000
TDA08H0_B1R	8	24,0	2000
TDA10H0_B1R	10	24,0	2000

* see next page for TDA01 tape & reel drawing



Dimensions are shown: mm
Specifications and dimensions subject to change



11



Technical drawing of a circular manhole cover assembly, showing multiple views and dimensions:

- Top View:** Shows the overall circular shape with a diameter of $\varnothing 330$. The cover has a central rectangular opening. Dimensions include a top flange width of 1.75 ± 0.10 , a central opening width of 4.00 ± 0.10 , and a distance from the center to the edge of the central opening of 8.00 ± 0.10 . The total width of the cover is 16.0 ± 0.30 . The central opening has a diameter of $\varnothing 1.5$ with a tolerance of $+0.10 / -0.00$. The distance from the center to the edge of the central opening is 7.50 ± 0.10 .
- Side View:** Shows the profile of the cover. The total height is 8.60 . The distance from the top flange to the bottom of the central opening is 6.55 . The top flange has a thickness of 0.40 ± 0.05 .
- Detail A:** A cross-section of the top flange. It shows a thickness of 1 ± 0.1 and a radius of $R0.3$ MAX. The distance from the center to the edge of the flange is 2.90 . The height of the flange is 2.65 .
- Detail B:** A cross-section of the central opening. It shows a diameter of $\varnothing 13 \pm 0.5$ and a distance from the center to the edge of the opening of 2 ± 0.5 . The height of the opening is 2.90 .
- Bottom View:** Shows the underside of the cover. It has a diameter of $\varnothing 330$ and a central opening with a diameter of $\varnothing 21 \pm 0.8$. The distance from the center to the edge of the central opening is 2 ± 0.5 .
- Other Dimensions:** The distance from the center to the edge of the central opening is 2.90 . The distance from the center to the edge of the central opening is 2.90 . The distance from the center to the edge of the central opening is 2.90 .

