


LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
FT	64				C	REV PER 063C-0104-01	04SEP01	JO

1. RECEPTACLE ACCEPTS A 0.20-0.36 [.008-.014] THICK I.C. LEAD.
2. TUBE LOADED FOR AUTOMATIC INSERTION.


CIRCUIT CAVITY NO. 1



1.32
[.052] TYP

7.49
[.295]

A




A

2.54±0.20
[.100±.008] TYP

0.58±0.05
[.023±.002] TYP



1.22
[.048]



RECOMMENDED MOUNTING HOLE PATTERN
SCALE 4:1

Ø0.91±0.08
[Ø.036±.003] TYP

0.23
[.009] M



SECTION A-A
SCALE 10:1

OBSOLETE	TINNED	PHOS.BRZ. 0.15 [.006]	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-382882-3
	GOLD	BE.CU. 0.15 [.006]	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-382882-2
	TINNED	BE.CU. 0.15 [.006]	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-382882-1
CONTACT FINISH		CONTACT MAT'L	HOUSING MATERIAL	PART NO.
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.13 [.005] ANGLES ± 0°,30' MATERIAL SEE TABLE FINISH SEE TABLE			DR 7-5-94 R.TALLEY	AMP AMP Incorporated Harrisburg, PA 17105-3608 NAME SOCKET ASSY, DIP, 6 POS, DIPLOMATE DL
			CHK 7-5-94 R.TALLEY	
			APPD 7-5-94 M.HUDDLESTON	
			APPD 7-5-94 M.STADDON	
			PRODUCT SPEC 108-1066	SIZE D CAGE CODE 00779 DRAWING NO C-382882
			APPLICATION SPEC 114-1049	
			WEIGHT -	
THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.			SCALE 5:1	SHEET 1 OF 1

CUSTOMER DRAWING