





NOTES.


1. MATERIAL : BRASS
2. FINISHES : SEE TABLE 1
0.8~1.8 μ m TIN PLATING
OVERALL 0.3~0.8 μ m COPPER PLATING
3. PRODUCT SPECIFICATIONS : PS-35544-001
PS-35702-001
PS-68428-001
4. MATES WITH : 0.5t TAB
5. APPLICABLE WIRE RANGE : AWG #20~#16

MATERIAL NO.	PART NO.	FINISH	TRADE MARK
357110700	35711-0700	UNPLATED	MK2
357110710	35711-0710	⊙ PRE-TIN PLATED	
357110701	35711-0701	UNPLATED	L MK1
357110711	35711-0711	⊙ PRE-TIN PLATED	

<TABLE 1>



SECTION B-B'



SECTION C-C'

PART NO.	"G" CONTACT GAP
35711-0700	0.3 - 0.4
35711-0710	
35711-0701	0.42 - 0.47
35711-0711	

<TABLE 2>

REVISED	EC NO: KOR2009-0111 DRWN: JHPARK01 2009/01/30 CHKD: W. YANG 2009/01/30 APPR: YUNSIKKIM 2009/01/30	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 8:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
					mm	INCH	DRAWN BY WY. YANG	DATE 1993/04/15	TITLE .110 SLIP-ON RECEPTACLE	
				4 PLACES	± ---	± ---	CHECKED BY BK. CHOI	DATE 1993/04/15		
				3 PLACES	± ---	± ---				
				2 PLACES	± ---	± ---				
				1 PLACE	± 0.30	± ---	APPROVED BY CW. LEE	DATE 1993/04/15	 MOLEX INCORPORATED	
				ANGULAR ± --- °		MATERIAL NO.	DOCUMENT NO.	SHEET NO.		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SEE TABLE		SD-35711-07*0		1 OF 01		
SIZE A 3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										