


HOW TO ORDER

AVX PART NUMBER:



RIPPLE CURRENT MULTIPLIERS vs. Frequency, temperature and applied voltage^{1/2/}

Frequency of Applied Ripple Current	120Hz				800Hz				1kHz				
	≤55	85	105	125	≤55	85	105	125	≤55	85	105	125	
Ambient Still Air Temperature (°C)													
% of 85°C	100%	0.60	0.39	-	-	0.71	0.43	-	-	0.72	0.45	-	-
Rated	90%	0.60	0.46	-	-	0.71	0.55	-	-	0.72	0.55	-	-
	80%	0.60	0.52	0.35	-	0.71	0.62	0.42	-	0.72	0.62	0.42	-
Peak	70%	0.60	0.58	0.44	-	0.71	0.69	0.52	-	0.72	0.70	0.52	-
	Voltage	66-2/3%	0.60	0.60	0.46	0.27	0.71	0.71	0.55	0.32	0.72	0.72	0.55

Frequency of Applied Ripple Current	10kHz				40kHz				100kHz				
	≤55	85	105	125	≤55	85	105	125	≤55	85	105	125	
Ambient Still Air Temperature (°C)													
% of 85°C	100%	0.88	0.55	-	-	1.00	0.63	-	-	1.10	0.69	-	-
Rated	90%	0.88	0.67	-	-	1.00	0.77	-	-	1.10	0.85	-	-
	80%	0.88	0.76	0.52	-	1.00	0.87	0.59	-	1.10	0.96	0.65	-
Peak	70%	0.88	0.85	0.64	-	1.00	0.97	0.73	-	1.10	1.07	0.80	-
	Voltage	66-2/3%	0.88	0.88	0.68	0.40	1.00	1.00	0.77	0.45	1.10	1.10	0.85

1/ At 125°C the rated voltage of the capacitors decreases to 66 2/3 of the 85°C rated voltage.

2/ The peak of the applied ac ripple voltage plus the applied dc voltage must not exceed the dc voltage rating of the capacitors.

RATINGS & PART NUMBER REFERENCE

AVX Part Number	Cap (uF)	DC Rated Voltage (V)	ESR Max (ohms)	DC Leakage Max (uA)		Max Impedance (Ohms)	Maximum Capacitance Change* (%)			Max AC Ripple* (mA rms)
	25°C at 120Hz	85°C	120Hz	+25°C	+85 and 125°C	-55°C at 120 Hz	-55°C	+85°C	125°C	85°C at 40kHz
TW2D248*025CB@Z0S++	2400	25	0.33	10	40	14	-70	12	18	5200
TW2D368*025CB@Z0S++	3600	25	0.22	15	60	21	-70	12	18	7800
TW3E368*025CB@Z0S++	3600	25	0.25	12	50	14	-75	12	20	6200
TW2E448*025CB@Z0S++	4400	25	0.25	20	160	20	-90	30	50	6400
TW3E548*025CB@Z0S++	5400	25	0.17	18	75	21	-75	12	20	9300
TW3E668*025CB@Z0S++	6600	25	0.17	30	240	30	-90	30	50	9600
TW2D208*030CB@Z0S++	2000	30	0.35	14	50	14	-70	10	18	5000
TW2D308*030CB@Z0S++	3000	30	0.23	21	75	21	-70	10	18	7500
TW3E308*030CB@Z0S++	3000	30	0.30	24	70	12	-72	10	20	6000
TW3E458*030CB@Z0S++	4500	30	0.20	36	105	18	-72	10	20	9000
TW2D947*050CB@Z0S++	940	50	0.38	6	50	20	-50	8	15	4200
TW2E148*050CB@Z0S++	1360	50	0.35	10	80	16	-58	10	20	5500
TW3D148*050CB@Z0S++	1410	50	0.25	9	75	30	-50	8	15	6300
TW3E208*050CB@Z0S++	2040	50	0.23	15	120	24	-58	10	20	8250
TW2D787*060CB@Z0S++	780	60	0.45	6	50	30	-60	8	15	4200
TW2E118*060CB@Z0S++	1120	60	0.40	10	80	20	-58	8	15	5500
TW3D128*060CB@Z0S++	1170	60	0.30	9	75	45	-60	8	15	6300
TW3E178*060CB@Z0S++	1680	60	0.27	15	120	30	-58	8	15	8250
TW2E208*060CB@Z0S++	2000	60	0.50	24	180	40	-90	30	50	6400
TW3E308*060CB@Z0S++	3000	60	0.33	36	270	60	-90	30	50	9600
TW2D667*075CB@Z0S++	660	75	0.50	6	60	24	-45	6	10	4200
TW2E947*075CB@Z0S++	940	75	0.45	10	100	24	-55	6	10	5500
TW3D997*075CB@Z0S++	990	75	0.33	9	90	36	-45	6	10	6300
TW3E148*075CB@Z0S++	1410	75	0.30	15	150	36	-55	6	10	8250
TW2D307*100CB@Z0S++	300	100	0.80	6	50	44	-35	6	12	4200
TW2E447*100CB@Z0S++	440	100	0.60	10	100	30	-40	6	12	5500
TW3D457*100CB@Z0S++	450	100	0.53	9	75	66	-35	6	12	6300
TW3E667*100CB@Z0S++	660	100	0.40	15	150	45	-40	6	12	8250
TW2D207*125CB@Z0S++	200	125	0.90	6	50	70	-35	5	12	4200
TW2D307*125CB@Z0S++	300	125	0.60	9	75	105	-35	5	12	6300
TW3E307*125CB@Z0S++	300	125	0.80	10	100	40	-35	6	12	5500
TW3E457*125CB@Z0S++	450	125	0.53	15	150	60	-35	6	12	8250

*For reference only, contact factory for more details