




.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE



-X0XX
HEADER WITHOUT LATCH EJECTOR



-X2XX
HEADER WITH SHORT LATCH EJECTOR
FOR 3M SOCKETS WITHOUT STRAIN RELIEF



-X3XX
HEADER WITH LONG LATCH EJECTOR
FOR 3M SOCKETS WITH STRAIN RELIEF

X3XXX - XXXXXX

N= HIGH TEMP BLACK (PCT)/(RB PLATING REQ'D)

3M PART NUMBER: -
(SEE TABLE 1)

PIN CONFIGURATION: _____
1 = RIGHT ANGLE SOLDER TAILS
2 = STRAIGHT SOLDER TAILS

- PLATING:
RB = 200 μ " [5.08 μ m] MATTE TIN TAILS

```

- TAIL:
02 = FOR .062 [1.57] THICK BOARD
03 = FOR .094 TO .125 [2.39 TO 3.18] THICK BOARD

```

```
- LATCH/EJECTOR SYSTEM:
0 = NO LATCH/EJECTOR INSTALLED
2 = SHORT ROLL PIN LATCH/EJECTORS
3 = LONG ROLL PIN LATCH/EJECTORS
```

- * MILITARY (WITH 3M'S N3518 POLARIZING KEY) AND CENTERBUMP POLARIZATION.
- * LOW PROFILE.
- * OPTIONAL EJECTOR LATCHES.
- * MOUNTING HOLES FOR SECURING HEADER TO BOARD.
- * THREE WALL SHROUD PROVIDES DESIGN FLEXIBILITY.
- * STRAIGHT, RIGHT ANGLE.
- * SOLDER TAIL OPTIONS.
- * OPTIONAL POLARIZING POSTS AVAILABLE.
- * HIGH TEMPERATURE INSULATOR SUITABLE FOR "NO LEAD" SOLDERING OPERATIONS.
- * SUITABLE FOR REFLOW SOLDERING USING "PASTE IN HOLE" TECHNIQUES.

2 PHYSICAL :

INSULATOR: MATERIAL: HIGH TEMP GLASS FILLED POLYESTER (PCT)
FLAMMABILITY: UL94V-0
COLOR: BLACK
CONTACT: MATERIAL: COPPER ALLOY
PLATING:
UNDER PLATING: 50 μ "-150 μ " [1.27 μ m-3.81 μ m] NICKEL-OVERALL
WIPING AREA: 30 μ " [0.76 μ m] AVG. GOLD
SOLDER TAILS: (SEE ORDERING INFORMATION)
MARKINGS: 3M LOGO, PART IDENTIFICATION NUMBER AND
ORIENTATION TRIANGLE

2 ELECTRICAL :

CURRENT RATING: 5.00A, 1 CONTACT POWERED
3.00A, 6 CONTACTS POWERED
1.75A, ALL CONTACTS POWERED
RATING CONDITIONS: EIA-364-070 METHOD 2, 30°C MAXIMUM
TEMPERATURE RISE, 20% DERATED. REFERENCE APPROPRIATE
3M PRODUCT SPECIFICATION FOR DETAILED CURRENT DERATING
CURVES.

INSULATION RESISTANCE: $>1 \times 10^9 \Omega$ AT 500 V_{DC}
WITHSTANDING VOLTAGE: 1,000V_{RMS} AT SEA LEVEL

2 ENVIRONMENTAL :

TEMPERATURE RATING: -55°C TO 105°C
PROCESS RATING: 260°C, PER J-STD-020C, SINGLE PASS
MOISTURE SENSITIVITY LEVEL: 1 (PER J-STD-020C SINGLE PASS)

DIMENSIONS: INCHES [MM]
[MM] IS REF. ONLY

DESIGN REFERENCE		NEXT ASSEMBLY	
ACCESS CODES			
DIVISION		DIVISION CODE	
Interconnect Solutions		EMSD	
DO NOT SCALE	SCALE	TOLERANCE EXCEPT AS NOTED	
DRAWING		INCHES	
		.00 ± .1	
		.00 ± .01	
		.000 ± .005	
		.0000 ± .0003	
THIRD ANGLE PROJECTION		MILLIMETER	
INTERPRET PER ASME Y14.5 - 2018		.00 ±	
MAX. SURFACE ROUGHNESS		.000 ±	
☐ ALL SURFACES ☒ MARKED ONLY		ANGLES ±	

L	115955	MAY 08,2024	JNC	FJR
K	97909	REMOVE 05 WWT TAILS	JNC	SAN
J	93619	REVISED ORDERING INFO	JNC	SAN
H	60056	REMOVE TIN LEAD PLATE AND KINK TAILS	JNC	RS
G	56068	REVISED ORDERING NUMBER	JNC	RS
REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
DRFT	CAS TIGLIONE	DATE AUG 05,2014	MFG	DATE
CHKD		DATE	APPR. R. SCHERER	DATE SEP 05,2014
 3M Center St. Paul, MN 55144 © 3M COPYRIGHT 2014 This document and the information it contains are the property of 3M and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.				
TITLE				
HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA				
CAGE NUMBER	SIZE	DRAWING NO.		REV.
MODEL	340	D78-5100-0771-5		L
DATE		DET. ☐ DES. ☒ YES ☐ NO		SHT 1 OF 5

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

UL[®]
US
UL FILE NO: E68080

3M™ THREE-WALL HEADER, 3000 SERIES

.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE







TABLE 1							
PIN QTY.	3M PART NUMBER	DIM. "A"	DIM. "B"	DIM. "C"	DIM. "D"	POLARIZING NOTCHES	PIN QTY.
10	3793	1.26 [32.1]	1.105 [28.04]	.865 [21.97]	.71 [18.0]	BC	10
14	3314	1.46 [37.2]	1.305 [33.12]	1.065 [27.05]	.91 [23.1]	BC	14
16	3408	1.56 [39.7]	1.405 [35.66]	1.165 [29.59]	1.01 [25.6]	ABC	16
20	3428	1.76 [44.8]	1.604 [40.74]	1.365 [34.67]	1.21 [30.7]	ABC	20
26	3429	2.06 [52.4]	1.905 [48.36]	1.665 [42.29]	1.51 [38.3]	ABC	26
34	3431	2.46 [62.6]	2.305 [58.52]	2.065 [52.45]	1.91 [48.5]	ABC	34
40	3432	2.76 [70.2]	2.605 [66.14]	2.365 [60.07]	2.21 [56.1]	ABC	40
50	3433	3.26 [82.9]	3.105 [78.84]	2.865 [72.77]	2.71 [68.8]	ABC	50
60	3372	3.76 [95.6]	3.605 [91.54]	3.365 [85.47]	3.21 [81.5]	ABC	60
64	3764	3.96 [100.7]	3.805 [96.62]	3.565 [90.55]	3.41 [86.6]	ABC	64

TABLE 2						
3M PART NUMBER SUFFIX	CONTACT TAIL	DIM. "E"	PIN CROSS SECTION			DIM. "G"
-1XX2	.062 [1.57] THICK PC BOARD	.112 [2.84]	DIM. "F" .0245+/- .0005 [.622]	DIAGONALS .028+/- .001 [.71]	CORNER RADIUS .0075 REF. [.191]	.035+/- .003 [.89] SEE NOTE 5
-2XX2						
-1X03	.094 [2.39] TO .125 [3.18] THICK PC BOARD	.155 [3.94]	.0245+/- .0005 [.622]	.028+/- .001 [.71]	.0075 REF. [.191]	.035+/- .003 [.89]
-2X03						



3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

DESIGN REFERENCE		NEXT ASSEMBLY	
DRG CODES		DRG CODES	
DIVISION Interconnect Solutions		DIVISION CODE EMSD	
DO NOT SCALE DRAWING	SCALE	TOLERANCES EXCEPT AS NOTED	
THIRD ANGLE PROJECTION		INCHES 0 ±.1 .00 ±.01 .000 ±.005 .0000 ±.0002	
INTERPRET PER ASME Y14.5 - 2018		MILLIMETERS 0 ± .0 ± .00 ± .000 ±	
MAX. SURFACE ROUGHNESS ALL SURFACES ✓ MARKED ONLY		CAGE NUMBER D78-5100-0771-5	
		MODEL 3400	
		REV. L	
		SHT 2 OF 5	


L	115955	MAY 08,2024	JNC	FJR
K	97909	JUN 22,2021	JNC	SAN
J	93619	JAN 07,2021	JNC	SAN
H	60056	MAR 06,2015	JNC	RS
G	56068	AUG 05,2014	JNC	RS
REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
DRFT	CASTIGLIONE	DATE 05,2014	MFG	DATE
CHKD		DATE	APPR	DATE
			R. SCHERER	SEP 05,2014

3M Center
St. Paul,
MN 55144


© 3M COPYRIGHT 2024
This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.

TITLE
HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA

3M™ THREE-WALL HEADER, 3000 SERIES
.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE



RECOMMENDED MOUNTING HOLE PATTERN
(STRAIGHT VERSION)



RECOMMENDED MOUNTING HOLE PATTERN
(RIGHT ANGLE VERSION)

PART CUSTOMIZATION


THIS SPEC SHEET DETAILS OUR STANDARD OFFERING.

3M HAS SEVERAL CAPABILITIES THAT CAN PROVIDE A PART TAILORED TO YOUR SPECIFIC NEEDS. ASK YOUR 3M SALES REPRESENTATIVE OR CUSTOMER SERVICE FOR MORE DETAILS.


BOTH SNAP-IN AND ROLL PIN LATCHES MAY BE ORDERED SEPARATELY. SNAP-IN AND ROLL PIN STYLE LATCHES ARE DIMENSIONALLY AND FUNCTIONALLY EQUIVALENT. IF ORDERING SNAP-IN OR ROLL PIN STYLE LATCHES SEPARATELY, PLEASE USE THE BELOW CHART.

MATERIAL	SHORT LATCH	LONG LATCH	LATCH STYLE	COLOR
HIGH TEMP. (PCT)	N3505-2B	N3505-3B	ROLL PIN	BLACK
HIGH TEMP (PPA)	N3505-30B	N3505-31B	SNAP-IN	BLACK

- * SELECTIVE PIN REMOVAL (ATA OR OTHER COMPATABILITY)
- * WIRE WRAP TAILS STYLE




LONG




SHORT

SNAP-IN LATCHES



NOTE:
SNAP-IN LATCHES CAN ONLY BE ORDERED SEPARATELY AND ARE THE CUSTOMERS RESPONSIBILITY TO INSTALL.


POLARIZING POST



3M PART NO.	MATERIAL	COLOR
3201-4	LCP	BLACK

NOTE:
INSERT POST INTO ONE MOUNTING
HARDWARE HOLE ON BOTTOM OF HEADER.
SET POST TO PROTRUDE .115 [2.92]

POLARIZING KEY




3M PART NO.	MATERIAL	COLOR	DIM. "A"
N3518	LCP	BLACK	.02

NOTE:
#2216 B/A SCOTCHWELD CAN BE USED TO
ADHERE KEYS.


DESIGN REFERENCE	NEXT ASSEMBLY	REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	1	ECO	MAY 08, 2024 REMOVE 05 WWT TAILS	JNC	FJR
XXXXXX	XXXXXX	2	K	JUN 22, 2021 REVISED ORDERING INFO	JNC	SAN
XXXXXX	XXXXXX	3	J	JAN 07, 2021 REMOVE TIN LEAD PLATE AND KINK TAILS	JNC	SAN
XXXXXX	XXXXXX	4	H	MAR 06, 2015 REVISE ORDERING NUMBER	JNC	RS
XXXXXX	XXXXXX	5	G	AUG 05, 2014 REVISED AND REDRAWN	JNC	RS
XXXXXX	XXXXXX	6	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	7	ECO	AUG 05, 2014 MFG	DATE	DATE
XXXXXX	XXXXXX	8	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	9	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	10	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	11	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	12	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	13	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	14	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	15	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	16	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	17	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	18	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	19	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	20	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	21	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	22	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	23	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	24	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	25	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	26	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	27	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	28	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	29	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	30	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	31	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	32	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	33	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	34	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	35	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	36	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	37	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	38	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	39	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	40	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	41	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	42	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	43	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	44	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	45	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	46	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	47	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	48	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	49	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	50	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	51	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	52	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	53	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	54	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	55	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	56	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	57	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	58	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	59	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	60	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	61	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	62	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	63	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	64	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	65	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	66	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	67	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	68	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	69	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	70	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	71	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	72	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	73	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	74	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	75	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	76	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	77	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	78	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	79	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	80	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	81	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	82	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	83	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	84	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	85	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	86	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	87	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	88	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	89	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	90	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	91	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	92	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	93	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	94	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	95	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	96	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	97	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	98	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	99	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE
XXXXXX	XXXXXX	100	ECO	AUG 05, 2014 R. SCHERER	DATE	DATE

3M™ THREE-WALL HEADER, 3000 SERIES
.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE


MOUNTING HARDWARE



3341-5
(INSTALL FROM BOTTOM OF BOARD)
PANHEAD THREAD CUTTING SCREW:
#4-24 X 5/16"
TYPE: USA STD BT, FEDERAL B6
MATERIAL: STAINLESS STEEL




3341-6
HEX HEAD BOLT, NUT AND WASHER:
BOLT - #2-56 X 1/2"
MATERIAL: STAINLESS STEEL




STRAIGHT VERSION INSTALL
(MUST BE INSERTED PRIOR TO
LATCH INSTALL)


RIGHT ANGLE VERSION INSTALL




3341-6
#2-56 NUT AND BOLT



#4-24 TYPE BT SELF THREADING SCREW
WHEN USING LATCHES, MAXIMUM LENGTH
OF SCREW IS .250 INCHES PLUS
THICKNESS OF THE BOARD.




3341-5



3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

DESIGN REFERENCE		NEXT ASSEMBLY		REV		ECO		ISSUE DATE AND DESCRIPTION		DRFT		CHKD	
ACCESS CODES				DRFT		DATE		MFG		DATE			
				CHKD		DATE		APPR. R. SCHERER		DATE		SEP 05, 2014	
DIVISION		DIVISION CODE				3M Center St. Paul, MN 55144		© 3M COPYRIGHT 2024 This document contains the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.					
Interconnect Solutions		EMSD											
DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED											
				INCHES		TITLE HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA							
THIRD ANGLE PROJECTION				.0 ± .1 .00 ± .01 .000 ± .005 .0000 ± .0002									
INTERPRET PER ASME Y14.5 - 2018				MILLIMETERS 0 ± .0 ± .00 ± .000 ±									
MAX SURFACE ROUGHNESS				CAGE NUMBER		SIZE		DRAWING NO.				REV.	
				D		78-5100-0771-5		L					
✓ MARKED SURFACES				MODEL		3400		DET.		LISTS		YES ☒ NO ☐	
				ANGLES ±				SHT		4		OF 5	

3M™ THREE-WALL HEADER, 3000 SERIES
.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE

Regulatory: For regulatory information about this product, visit 3M.com/regs or contact your 3M representative.

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: For industrial use only. Not intended, labeled or packaged for consumer sale or use.

3M Company
Electronics Materials Solutions Division
13011 McCallen Pass, Bldg. C
Austin, TX 78753-5380
1-800-225-5373
www.3M.com/interconnect

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
http://www.3M.com/interconnect

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

L	115955	MAY 08,2024	JNC	FJR
K	97909	JUN 22,2021	JNC	SAN
J	93619	JAN 07,2021	JNC	SAN
H	60056	MAR 06,2015	JNC	RS
G	56068	AUG 05,2014	JNC	RS
REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
DRFT	C	ASTIGLIONE	DATE	DATE
CHKD		DATE	APPRV	DATE
			R. SCHERER	SEP 05,2014
DIVISION		DIVISION CODE		
Interconnect Solutions		EMSD		
DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		
		INCHES .0 ±.1 .00 ±.01 .000 ±.005 .0000 ±.0002		
THIRD ANGLE PROJECTION		MILLIMETERS 0 ± .0 ± .00 ± .000 ±		
INTERPRET PER ASME Y14.5 - 2018		ALL SURFACES UNLESS OTHERWISE SPECIFIED		
MAX. SURFACE ROUGHNESS Rz 1.6		CAGE NUMBER D78-5100-0771-5		
MARKED ONLY		DRAWING NO. 78-5100-0771-5		
		MODEL 3400		
		REV. L		
		SHT 5 OF 5		