







REV.	DATE	DESCRIPTION
A	01/12/02	MODIFY FERRULE LENGTH
B	01/06/08	MODIFY BODY SLOT DIMENSIONS AND BARREL LENGTH



RECOMMENDED CABLE
STRIPPING DIMENSIONS

NOTES:

1. CRIMPED FERRULE HEX CRIMP SIZE .128"
2. CONTACT PIN TO SOLDER.

QTY	FINISH	MATERIAL	DESCRIPTION
1	GOLD	BRASS	HOUSING
2	GOLD	BER. COPPER	BODY
3	NATURAL	TEFLON	INSULATOR
4	GOLD	BRASS	CONTACT PIN
5	NATURAL	DELTRIN	INSULATOR
6	GOLD	BRASS	COVER
7	COPPER	COPPER	FERRULE
8			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.			
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm			
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"			
DO NOT SCALE DRAWING			
APPROVALS			
DATE			
DRAWN G.R.S.			
01/06/07			
CHECKED			
ISSUED			
SHEET 1 OF 1			
CAD FILE			
C:/252/252135.DWG			
PART DESCRIPTION			
MCX R/A CRIMP PLUG (FOR RG-178B/U, 196A/U)			
PART NO.			
252135			
DWG. NO.			
252135.DWG			
REV.			
B			
SIZE			
A			
SCALE			
NA			