



SURFACE MOUNT TELECOMMUNICATION TRANSFORMER

- A. Electrical specifications (@ 25 ° C)
1. Pri source impedance; 600 Ω
 2. Sec load impedance; 346 Ω
 3. MAX output power; 3.6 dBm (2.3mW)
 4. Frequency response; +0.15, -0.35 dB 300 Hz to 3.5 KHz
 5. DC unbalance; 0 mA
 6. Return loss; 25 dB MIN @ 300 Hz to 3.5 KHz
 7. Insertion loss; 2.7 dB ±0.4 dB @ 1 KHz
 8. Longitudinal balance; 60 dB MIN @ 200 Hz to 4 KHz
 9. DC resistance;
(1-3) = 127 Ω ±15%
(4-6) = 150 Ω ±15%
 10. Turns ratio;
(1-3) : (4-6) = 1 : 1.00 ±2%
 11. Dielectric strength;
1000 Vrms 1 minute @ Pri to Sec, Pri to Core
500 Vrms 1 minute @ Sec to Core
 12. Total harmonic distortion; -82 dB TYP @ 600 Hz, -10 dBm

B. Marking; TTC-103SL, TAMURA, date code and country of origin
or TSL103, TAMURA and date code

C. Safety; CSA-C22.2 No. 950-M89 File No. 138028
UL1459, UL1950 File No. 138028


D. Schematic diagram



MOUNTING FOOTPRINT

E. Mechanical specifications

All dimensions shown are nominal unless otherwise specified



PREPARED BY:

D. Kelley

ENGINEER:

T. Shiozawa

APPROVED:

D. Kelley

DWG CONTROL NO.

P-A1-11082

ACAD\TTC\A1110821.DWG

REV

B

TELECOMMUNICATION SURFACE MOUNT
DRY COUPLING TRANSFORMER

TAMURA CORPORATION OF AMERICA

43352 BUSINESS PARK DRIVE, TEMECULA, CA. 92590-6624
(909) 699-1270 FAX 9096769482


TTC-103SL or TSL103

MODEL SPECIFICATION

DIM: mm(In) SCL: 4/1 SH: 1 OF 1

PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING.

TAMURA
FILE #E138028



MODEL NUMBER

TTC-103SL or TSL103