

NOTES:


- 1

FOR STRIP VERSION SEE DWG. 164155.
- 2

UNDERCOATING: 1,3µm Ni.
SELECTIVE : 0,8µm Au.
ZONE I : BRIGHT TIN/LEAD PLATED.
- 3

UNDERCOATING: 1,3µm Ni.
SELECTIVE : 0,8µm Au.
REMAINDER : GOLDFLASH.
- 4

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI



WIRE RANGE :
30-26 AWG 0,05-0,14 mm²
INSULATION RANGE :
1,22 DIA. MAX.

STAINLESS STEEL		SEE NOTE 2			BRASS		164170-4				
		PRETINNED					164170-3				
		POST TINPLATED					164170-2 4				
		SEE NOTE 3					164170-1				
MATERIAL OF SLEEVE		PLATING OF BODY			MATERIAL OF BODY		PARTNUMBER				
—	—	—	—	—	CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED © COPYRIGHT 19 — BY AMP HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED.AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING. THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION —,19— AMP AMP HOLLAND B.V. 's-Hertogenbosch, The Netherlands.						
—	—	—	—	—							
—	—	—	—	—							
—	—	—	—	—							
—	—	—	—	—							
E1	REVISED PER ECO-09-020689	KK	AEG	24AUG09	NAME						
E	EH-0077-92	JvL	CvT	04-03-94	HDR SOCKET CONTACT TYPE XI (CRIMP SNAP-IN) L.P.						
LTR.	REVISION RECORD	DR.	CHK.	DATE							
DR.: J.v.LIEMPT		CHK.: C.v.TILBURG		APP.: L.v.SOEST		DWG.No.			REV.LTR.	SHEET	A4
DATE: 6 JAN 1993		DATE: 08-02-93		DATE: 08-02-93		164170			E1	1 OF 1	