






PRODUCT NUMBER
89025-XYX
89025-XYXLF



mat'l code				--		tolerances unless otherwise specified				CUSTOMER				www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3				COPY			title			
CP	V06-0573	DCH	2006-06-14		0.XX ±0.13				projection			METRAL SIGNAL HEADER			
CR	DG09-0256	TER	2009-08-19		.XXX ±.051				1 MOD, 5 ROW PRESS-FIT						
-	-	-	-	angles	0° ±2°						product family		METRAL		code
CK	V03-0031	TAB	02/08/03	dr	T.BRUNGARD 11/19/99				scale	A	size	dwg no	213		
CL	V03-1321	DAI	01/15/04	enrg	M.STRAWSER 11/19/99								sheet		
CM	V04-0459	LP	5/25/04	chr	M.STRAWSER 11/19/99				2:1						1 of 8
CN	V05-0030	DAI	02/10/05	appd	M.STRAWSER 02/29/00										
sheet		revision		CR	CR	CR	CR	CR	CR	CR	CR	CR	CR	CR	CR
index		sheet		1	2	3	4	5	6	7	8				


cage code 22526

Pro/E



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-10



REQUIRED PC BOARD LAYOUT
COMPONENT SIDE
SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION

KEY		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
1	5.00	4.30
2	5.75	4.30
3	6.50	4.30
4	7.25	4.30
5	5.00	13.60
6	5.75	13.60
7	6.50	13.60
8	7.25	13.60
9	5.00	17.00
10	5.75	17.00
11	6.50	17.00
12	7.25	17.00
13	8.25	4.30
14	8.25	13.60
15	8.25	17.00
19	8.00	4.30
20	8.00	13.60
21	8.00	17.00
22	5.00	12.10
23	8.00	17.70
24	6.50	16.30
25	5.75	15.60
26	5.00	14.90
27	5.75	12.40
29	8.00	14.60

KEY		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
32	6.50	12.90
38	7.25	14.40
39	8.00	14.40
40	5.00	15.60
41	6.50	15.60
44	5.75	12.10
45	6.50	12.10
49	5.75	15.10
54	5.00	11.50

mat'l code				tolerances unless otherwise specified				CUSTOMER		www.fciconnect.com			
lfr	ecn no.	dr	date	linear	0.X ±0.3			projection		title METRAL SIGNAL HEADER 1 MOD, 5 ROW PRESS-FIT			
CR					0.XX ±0.13								
					.XXX ±.051								
				angles	0° ±2°				scale	product family		METRAL	code
				dr	T.BRUNGARD	11/19/99	size			dwg no	213		
				enrg	M.STRAWSE	11/19/99							
				chr	M.STRAWSE	11/19/99							
				appd	M.STRAWSE	02/29/00							
sheet index		revision sheet											

Pro/E

cage code 22526


PDM: Rev:CR

STATUS:Released

Printed: Sep 16, 2009



		1 2						3						4									
METRAL P/N	ROW	CONTACT CODE MOD. I						METRAL P/N	ROW	CONTACT CODE MOD. I						METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6			1	2	3	4	5	6			1	2	3	4	5	6
89025-X01 SEE NOTE 10 LEAD FREE OPTION	E	10	10	10	10	10	10	89025-X05 SEE NOTE 10 LEAD FREE OPTION	E	26	12	12	12	12	23	89025-X09 SEE NOTE 10 LEAD FREE OPTION	E	21	21	11	11	10	11
	D	10	10	10	10	10	10		D	26	12	12	12	12	23		D	21	21	11	11	11	11
	C	9	9	9	9	9	9		C	23	12	12	12	12	23		C	21	21	11	11	11	11
	B	10	10	10	10	10	10		B	24	12	12	12	12	23		B	21	21	11	11	11	11
	A	3	3	3	3	3	3		A	24	12	12	12	12	23		A	21	21	11	11	11	11
89025-X02 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	3	3	2	89025-X06 SEE NOTE 10 LEAD FREE OPTION	E	25	25	25	25	25	25	89025-X10 SEE NOTE 10 LEAD FREE OPTION	E	3	19	3	3	19	3
	D	2	2	2	3	2	2		D	25	25	25	25	25	25		D	19	3	3	19	3	3
	C	2	1	2	3	3	2		C	25	25	25	25	25	25		C	3	1	19	3	3	19
	B	2	2	2	3	2	2		B	25	25	25	25	25	25		B	3	19	3	3	19	3
	A	2	2	2	3	3	2		A	25	25	25	25	25	25		A	3	3	19	3	3	3
89025-X03 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	3	2	2	89025-X07 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	89025-X11 SEE NOTE 10 LEAD FREE OPTION	E	10	10	10	10	10	10
	D	2	2	2	3	2	2		D	6	6	6	6	6	6		D	10	10	10	10	10	10
	C	2	1	2	3	2	2		C	6	6	6	6	6	6		C	10	10	10	10	10	10
	B	2	2	2	3	2	2		B	6	6	6	6	6	6		B	10	10	10	10	10	10
	A	2	2	2	3	2	2		A	6	6	6	6	6	6		A	2	2	2	2	2	2
89025-X04 SEE NOTE 10 LEAD FREE OPTION	E	12	25	23	23	23	25	89025-X08 SEE NOTE 10 LEAD FREE OPTION	E	4	2	19	19	19	2	89025-X12 SEE NOTE 10 LEAD FREE OPTION	E	10	10	10	10	10	10
	D	12	25	23	23	23	25		D	4	2	19	19	19	2		D	9	9	9	9	9	9
	C	12	25	23	23	23	25		C	4	2	19	19	19	2		C	10	10	10	10	10	10
	B	12	25	23	23	23	25		B	4	2	19	19	19	2		B	10	10	10	10	10	10
	A	12	25	23	23	23	25		A	4	2	19	19	19	2		A	3	3	3	3	3	3
89025-X13 SEE NOTE 10 LEAD FREE OPTION	E	10	10	10	10	10	10	89025-X14 SEE NOTE 10 LEAD FREE OPTION	E	25	25	25	25	25	25	89025-X15 SEE NOTE 10 LEAD FREE OPTION	E	3	3	19	19	3	3
	D	9	9	9	9	9	9		D	25	25	25	25	25	25		D	3	3	19	19	3	3
	C	10	10	10	10	10	10		C	25	25	25	25	25	25		C	3	3	19	19	3	3
	B	10	10	10	10	10	10		B	25	25	25	25	25	25		B	3	3	19	19	3	3
	A	2	2	2	2	2	2		A	2	2	2	2	2	2		A	3	3	19	19	3	3
89025-X17 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	89025-X18 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	89025-X19 SEE NOTE 10 LEAD FREE OPTION	E	19	19	19	1	1	1
	D	2	2	2	2	2	2		D	6	6	6	6	6	6		D	3	3	3	3	3	3
	C	4	4	4	4	4	4		C	8	8	8	8	8	8		C	3	3	3	3	3	3
	B	2	2	2	2	2	1		B	6	6	6	6	6	5		B	3	3	3	3	3	3
	A	2	2	2	2	2	2		A	6	6	6	6	6	6		A	3	3	3	3	3	3
89025-X16 SEE NOTE 10 LEAD FREE OPTION	E	3	3	19	19	3	4	89025-X20 SEE NOTE 10 LEAD FREE OPTION	E	1	4	4	4	4	19		E	1	4	4	4	4	19
	D	3	3	19	19	3	4		D	1	4	4	4	4	19		D	1	4	4	4	4	19
	C	3	3	19	19	3	4		C	19	4	4	4	4	19		C	19	4	4	4	4	19
	B	3	3	19	19	3	4		B	3	4	4	4	4	19		B	3	4	4	4	4	19
	A	3	3	19	19	3	4		A	3	4	4	4	4	19		A	3	4	4	4	4	19

mat'l code				--		tolerances unless otherwise specified				CUSTOMER		 www.fcconnect.com																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																				
lfr	ecn no.	dr	date	linear	0 . X ±0.3				COPY			title																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																				
CR					0 . XX ±0.13				projection			METRAL SIGNAL HEADER																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																				
					. XXX ±.051							1 MOD, 5 ROW PRESS-FIT																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																				
					0° ±2°																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																											
				dr	T.BRUNGARD	11/19/99			product family		METRAL		code																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																			
				engr	M.STRAWSER	11/19/99			size		dwg no		213																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																			
				chr	M.STRAWSER	11/19/99			scale				sheet																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																			
				appd	M.STRAWSER	02/29/00			1 : 1		A		89025																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																			
sheet index	revision sheet																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																															

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCJ				
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY		www.fciconnect.com				
CR					0.XX ±0.13	projection	title		METRAL SIGNAL HEADER			
					.XXX ±.051		1 MOD, 5 ROW PRESS-FIT					
					0° ±2°							
				angles	dr	T.BRUNGARD	11/19/99	product family		METRAL	code	213
					enrg	M.STRAWSE	11/19/99	size		dwg no	sheet	3
					chr	M.STRAWSE	11/19/99	A		89025		
					appd	M.STRAWSE	02/29/00	scale		1:1		
sheet	revision							cage code		22526		
index	sheet											



1										2										3										4															
METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						
			1	2	3	4	5	6				1	2	3	4	5	6				1	2	3	4	5	6				1	2	3	4	5	6				1	2	3	4	5	6	
89025-X21 SEE NOTE 10 LEAD FREE OPTION		E	25	25	25	25	25	25	89025-X25 SEE NOTE 10 LEAD FREE OPTION		E	-	-	-	-	-	-	89025-X29 SEE NOTE 10 LEAD FREE OPTION		E	-	-	-	-	-	-	89025-X33 SEE NOTE 10 LEAD FREE OPTION		E	25	25	25	25	25	25	89025-X37 SEE NOTE 10 LEAD FREE OPTION		E	11	11	11	11	11	11	
		D	40	40	40	40	40	40			D	3	3	3	3	3	3			D	1	1	1	1	1	1			1																
		C	25	25	25	25	25	25			C	3	3	3	3	3	3			C	25	25	25	25	25	25			25																
		B	25	25	25	25	25	25			B	3	3	3	3	3	3			B	25	25	25	25	25	25			25																
		A	3	3	3	3	3	3			A	3	3	3	3	3	3			A	41	41	41	41	41	41			41																
89025-X22 SEE NOTE 10 LEAD FREE OPTION		E	1	1	1	1	1	1	89025-X26 SEE NOTE 10 LEAD FREE OPTION		E	-	-	-	-	-	-	89025-X30 SEE NOTE 10 LEAD FREE OPTION		E	1	4	1	1	1	1	89025-X34 SEE NOTE 10 LEAD FREE OPTION		E	4	4	4	13	13	13	89025-X38 SEE NOTE 10 LEAD FREE OPTION		E	49	49	49	49	49	49	
		D	1	1	1	1	1	1			D	3	3	-	-	-	-			D	1	1	1	1	1	4			D	4	4	4	13	13	13			D	49	49	49	49	49	49	
		C	1	1	1	1	1	1			C	3	3	-	-	-	-			C	1	1	1	4	1	1			C	4	4	4	13	13	13			C	49	49	49	49	49	49	
		B	19	4	4	4	4	4			B	3	3	-	-	-	-			B	1	4	1	1	1	1			B	4	4	4	13	13	13			B	49	49	49	49	49	49	
		A	1	1	1	1	1	1			A	3	3	-	-	-	-			A	1	1	1	1	1	4			A	4	4	4	13	13	13			A	49	49	49	49	49	49	
89025-X23 SEE NOTE 10 LEAD FREE OPTION		E	2	-	2	-	2	-	89025-X27 SEE NOTE 10 LEAD FREE OPTION		E	32	32	32	32	32	32	89025-X31 SEE NOTE 10 LEAD FREE OPTION		E	1	1	1	3	1	1	89025-X35 SEE NOTE 10 LEAD FREE OPTION		E	1	1	1	1	1	1	89025-X39 SEE NOTE 10 LEAD FREE OPTION		E	44	44	44	44	44	44	
		D	-	-	-	-	-	-			D	32	32	32	32	32	32			D	1	1	1	3	1	1			D	40	1	1	1	1	1			1	D	44	44	44	44	44	44
		C	2	-	2	-	2	-			C	32	32	32	32	32	32			C	3	3	1	3	1	1			C	1	1	1	1	1	1			1	C	44	44	44	44	44	44
		B	-	-	-	-	-	-			B	32	32	32	32	32	32			B	1	1	1	1	1	1			B	1	1	1	1	1	1			1	B	44	44	44	44	44	44
		A	2	-	2	-	2	-			A	32	32	32	32	32	32			A	4	4	4	4	4	4			A	1	1	1	1	1	1			1	A	44	44	44	44	44	44
89025-X24 SEE NOTE 10 LEAD FREE OPTION		E	4	2	2	2	2	2	89025-X28 SEE NOTE 10 LEAD FREE OPTION		E	-	-	-	-	-	-	89025-X32 SEE NOTE 10 LEAD FREE OPTION		E	45	45	45	45	45	45	89025-X36 SEE NOTE 10 LEAD FREE OPTION		E	8	8	8	14	14	14	89025-X40 SEE NOTE 10 LEAD FREE OPTION		E	12	12	12	15	15	15	
		D	4	2	2	2	2	2			D	1	1	1	1	1	1			D	45	45	45	45	45	45			D	8	8	8	14	14	14			D	12	12	12	15	15	15	
		C	4	2	2	2	2	2			C	1	1	1	1	1	1			C	45	45	45	45	45	45			C	8	8	8	14	14	14			C	12	12	12	15	15	15	
		B	4	2	2	2	2	2			B	1	1	1	1	1	1			B	45	45	45	45	45	45			B	8	8	8	14	14	14			B	12	12	12	15	15	15	
		A	4	2	2	2	2	2			A	1	1	1	1	1	1			A	45	45	45	45	45	45			A	8	8	8	14	14	14			A	12	12	12	15	15	15	

mat'l code

- -

tolerances unless otherwise specified

0. X ±0.3

0. XX ±0.13

.XXX ±.051

0° ±°

dr T.BRUNGARD 11/19/99

enrg M.STRAWSER 11/19/99

chr M.STRAWSER 11/19/99

appd M.STRAWSER 02/29/00

sheet index

revision sheet

CUSTOMER

COPY

projection

MM

scale 1:1

FCI

www.fciconnect.com

title

METRAL SIGNAL HEADER

1 MOD, 5 ROW PRESS-FIT

product family

METRAL

code

213

size

dwg no

89025

sheet

4

mat'l code				--		tolerances unless otherwise specified		CUSTOMER		FCJ www.fcjconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3		COPY		 title METRAL SIGNAL HEADER 1 MOD, 5 ROW PRESS-FIT		
CR					0.XX ±0.13		projection				
					.XXX ±.051						
					0° ±2°		 scale 1:1				
				angles	dr	T.BRUNGARD	11/19/99	product family		METRAL	code
					enrg	M.STRAWSE	11/19/99	size		dwg no	213
					chr	M.STRAWSE	11/19/99	A		89025	sheet
					appd	M.STRAWSE	02/29/00				4
sheet index		revision sheet									

1										2										3										4																																																	
METRAL P/N										CONTACT CODE MOD. I										METRAL P/N										CONTACT CODE MOD. I										METRAL P/N										CONTACT CODE MOD. I										METRAL P/N										CONTACT CODE MOD. I									
89025-X41 SEE NOTE 10 LEAD FREE OPTION										89025-X45 SEE NOTE 10 LEAD FREE OPTION										89025-X49 SEE NOTE 10 LEAD FREE OPTION										89025-X53 SEE NOTE 10 LEAD FREE OPTION										89025-X57 SEE NOTE 10 LEAD FREE OPTION																																							
89025-X42 SEE NOTE 10 LEAD FREE OPTION										89025-X46 SEE NOTE 10 LEAD FREE OPTION										89025-X50 SEE NOTE 10 LEAD FREE OPTION										89025-X54 SEE NOTE 10 LEAD FREE OPTION										89025-X58 SEE NOTE 10 LEAD FREE OPTION																																							
89025-X43 SEE NOTE 10 LEAD FREE OPTION										89025-X47 SEE NOTE 10 LEAD FREE OPTION										89025-X51 SEE NOTE 10 LEAD FREE OPTION										89025-X55 SEE NOTE 10 LEAD FREE OPTION										89025-X59 SEE NOTE 10 LEAD FREE OPTION																																							
89025-X44 SEE NOTE 10 LEAD FREE OPTION										89025-X48 SEE NOTE 10 LEAD FREE OPTION										89025-X52 SEE NOTE 10 LEAD FREE OPTION										89025-X56 SEE NOTE 10 LEAD FREE OPTION										89025-X60 SEE NOTE 10 LEAD FREE OPTION																																							



1						2						3						4																				
METRAL P/N		ROW	CONTACT CODE MOD. I					METRAL P/N		ROW	CONTACT CODE MOD. I					METRAL P/N		ROW	CONTACT CODE MOD. I					METRAL P/N		ROW	CONTACT CODE MOD. I											
89025-X61 SEE NOTE 10 LEAD FREE OPTION	E	1	19	3	3	3	89025-X65 SEE NOTE 10 LEAD FREE OPTION	E	1	19	3	3	3	19	89025-X69 SEE NOTE 10 LEAD FREE OPTION	E	14	6	8	8	8	89025-X73 SEE NOTE 10 LEAD FREE OPTION	E	-	2	-	2	-	2	89025-X77 SEE NOTE 10 LEAD FREE OPTION	E	7	7	5	20	7	7	
	D	3	19	3	3	3		D	3	3	3	3	3	19		D	14	7	8	8	8		D	2	-	2	-	2	-		D	7	7	7	7	7	7	
	C	3	19	3	3	3		C	3	3	3	3	3	19		C	14	7	8	8	8		C	-	2	-	2	-	2		C	7	7	7	7	7	7	
	B	19	19	3	3	3		B	3	3	3	3	3	19		B	14	7	8	8	8		B	2	-	2	-	2	-		B	7	7	7	7	7	7	
	A	19	19	3	3	3		A	3	3	3	3	3	19		A	14	7	5	8	8		8	A	-	2	-	2	-		2	A	7	7	7	7	7	7
METRAL P/N		ROW	CONTACT CODE MOD. I					METRAL P/N		ROW	CONTACT CODE MOD. I					METRAL P/N		ROW	CONTACT CODE MOD. I					METRAL P/N		ROW	CONTACT CODE MOD. I											
89025-X62 SEE NOTE 10 LEAD FREE OPTION	E	1	-	1	-	1	89025-X66 SEE NOTE 10 LEAD FREE OPTION	E	3	1	1	1	1	1	89025-X70 SEE NOTE 10 LEAD FREE OPTION	E	13	2	4	4	4	4	89025-X74 SEE NOTE 10 LEAD FREE OPTION	E	-	-	-	-	-	89025-X78 SEE NOTE 10 LEAD FREE OPTION	E	54	54	39	54	54	54	
	D	-	1	-	1	-		D	3	1	1	1	1	1		D	13	3	4	4	4	4		D	2	-	2	-	2		-	D	54	54	39	54	54	54
	C	1	-	1	-	1		C	3	1	1	1	1	1		C	13	3	4	4	4	4		C	-	2	-	2	-		2	C	54	54	39	54	54	54
	B	-	1	-	1	-		B	3	1	1	1	1	1		B	13	3	4	4	4	4		B	2	-	2	-	2		-	B	54	54	39	54	54	54
	A	1	-	1	-	1		A	3	1	1	1	1	1		A	13	3	1	4	4	4		A	-	2	-	2	-		2	A	54	54	39	54	54	54
METRAL P/N		ROW	CONTACT CODE MOD. I					METRAL P/N		ROW	CONTACT CODE MOD. I					METRAL P/N		ROW	CONTACT CODE MOD. I					METRAL P/N		ROW	CONTACT CODE MOD. I											
89025-X63 SEE NOTE 10 LEAD FREE OPTION	E	8	27	29	29	27	89025-X67 SEE NOTE 10 LEAD FREE OPTION	E	20	20	20	20	20	20	89025-X71 SEE NOTE 10 LEAD FREE OPTION	E	20	20	20	8	8	8	89025-X75 SEE NOTE 10 LEAD FREE OPTION	E	54	54	54	54	39	54	89025-X79 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1
	D	8	27	29	29	27		D	5	5	20	20	20	20		D	20	20	20	8	8	8		D	54	54	54	54	39	54		D	1	1	1	1	1	1
	C	8	27	29	29	27		C	5	5	20	20	20	20		C	20	20	20	8	8	8		C	54	54	54	54	39	54		C	2	2	2	2	1	1
	B	8	27	29	29	27		B	5	5	20	20	20	20		B	20	20	20	8	8	8		B	54	54	54	54	39	54		B	1	1	1	1	1	1
	A	8	27	29	29	27		A	5	5	20	20	20	20		A	20	20	20	8	8	8		A	54	54	54	54	39	54		A	1	1	1	1	1	1
METRAL P/N		ROW	CONTACT CODE MOD. I					METRAL P/N		ROW	CONTACT CODE MOD. I					METRAL P/N		ROW	CONTACT CODE MOD. I					METRAL P/N		ROW	CONTACT CODE MOD. I											
89025-X64 SEE NOTE 10 LEAD FREE OPTION	E	45	-	45	-	45	89025-X68 SEE NOTE 10 LEAD FREE OPTION	E	21	21	21	21	21	21	89025-X72 SEE NOTE 10 LEAD FREE OPTION	E	19	19	19	4	4	89025-X76 SEE NOTE 10 LEAD FREE OPTION	E	3	3	1	19	3	3	89025-X80 SEE NOTE 10 LEAD FREE OPTION	E	5	5	5	5	5	5	
	D	45	-	45	-	45		D	9	9	21	21	21	21		D	19	19	19	4	4		D	3	3	3	3	3	3		D	5	5	5	5	5	5	
	C	-	-	-	-	-		C	9	9	21	21	21	21		C	19	19	19	4	4		C	3	3	3	3	3	3		C	6	6	6	6	5	5	
	B	45	-	45	-	45		B	9	9	21	21	21	21		B	19	19	19	4	4		B	3	3	3	3	3	3		B	5	5	5	5	5	5	
	A	45	-	45	-	45		A	9	9	21	21	21	21		A	19	19	19	4	4		A	3	3	3	3	3	3		A	5	5	5	5	5	5	

mat'l code				tolerances unless otherwise specified				CUSTOMER		FCI					
lfr	ecn no.	dr	date	linear	0. X $\pm$ 0.3			COPY		www.fciconnect.com					
CR					0. XX $\pm$ 0.13			projection		title					
					.XXX $\pm$.051					METRAL SIGNAL HEADER					
					0° $\pm$ 2°					I MOD, 5 ROW PRESS-FIT					
				angles											
				dr	T.BRUNGARD	11/19/99			product family		METRAL		code		
				engr <td>M.STRAWSER</td> <td>11/19/99</td> <td colspan="2"></td> <td colspan="2">size</td> <td colspan="2">dwg no</td> <td colspan="2">213</td>	M.STRAWSER	11/19/99			size		dwg no		213		
				chr <td>M.STRAWSER</td> <td>11/19/99</td> <td colspan="2"></td> <td colspan="2">scale</td> <td colspan="2">A</td> <td colspan="2">89025</td>	M.STRAWSER	11/19/99			scale		A		89025		
				appd <td>M.STRAWSER</td> <td>02/29/00</td> <td colspan="2"></td> <td colspan="2"></td> <td colspan="2"></td> <td colspan="2">sheet</td>	M.STRAWSER	02/29/00							sheet		
sheet index		revision sheet												6	

mat'l code				tolerances unless otherwise specified				CUSTOMER		FCJ		www.fcjconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3			COPY		projection	title		
CR					0.XX ±0.13						METRAL SIGNAL HEADER		
					.XXX ±.051						1 MOD, 5 ROW PRESS-FIT		
					0° ±2°								
				angles	dr	T.BRUNGARD	11/19/99	MM	scale	1:1	product family		code
				enrg	M.STRAWSE	11/19/99	METRAL				213		
				chr	M.STRAWSE	11/19/99	size				6		
				appd	M.STRAWSE	02/29/00	dwg no				89025		
sheet index		revision sheet											



A

METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						
			1	2	3	4	5	6				1	2	3	4	5	6				1	2	3	4	5	6				1	2	3	4	5	6				1	2	3	4	5	6	
89025-X81 SEE NOTE 10 LEAD FREE OPTION		E	2	2	2	2	2	2	89025-X85 SEE NOTE 10 LEAD FREE OPTION		E	-	-	-	-	3	-	89025-X89 SEE NOTE 10 LEAD FREE OPTION		E	4	2	2	2	2	2	89025-X93 SEE NOTE 10 LEAD FREE OPTION		E	2	3	2	2	4	4	89025-X97 SEE NOTE 10 LEAD FREE OPTION		E	3	3	3	3	-	3	
		D	2	2	2	2	2	2			D	-	-	-	-	3	-			D	4	2	2	2	2	2			D	2	3	2	2	4	4			D	3	3	3	3	-	3	
		C	2	2	2	2	1	1			C	-	-	-	-	-	-			C	4	2	2	2	2	2			C	2	3	2	2	4	4			C	3	3	3	3	3	3	
		B	1	1	1	1	1	1			B	-	-	-	-	3	-			B	4	2	2	2	2	2			B	2	3	2	2	4	4			B	3	3	3	3	3	3	
		A	1	1	1	1	1	1			A	-	-	-	-	3	3			-	A	4	2	2	2	1			4	A	2	3	2	2	4			4	A	3	3	3	-	-	3
METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						
			1	2	3	4	5	6				1	2	3	4	5	6				1	2	3	4	5	6				1	2	3	4	5	6				1	2	3	4	5	6	
89025-X82 SEE NOTE 10 LEAD FREE OPTION		E	7	-	38	38	-	7	89025-X86 SEE NOTE 10 LEAD FREE OPTION		E	19	3	3	3	3	3	89025-X90 SEE NOTE 10 LEAD FREE OPTION		E	19	3	3	3	2	1	89025-X94 SEE NOTE 10 LEAD FREE OPTION		E	1	19	3	3	3	3	89025-X98 SEE NOTE 10 LEAD FREE OPTION		E	4	4	4	19	19	19	
		D	7	-	38	38	-	7			D	19	3	3	3	3	1			D	19	3	3	3	2	1			D	3	19	3	3	3	3			D	4	4	4	19	19	19	
		C	7	-	38	38	-	7			C	19	3	3	3	3	1			C	19	3	3	3	2	1			C	3	19	3	3	3	3			C	4	4	4	19	19	19	
		B	7	-	38	38	-	7			B	19	3	3	3	3	2			B	19	3	3	3	2	1			B	19	19	3	3	3	3			B	4	4	4	19	19	19	
		A	7	-	38	38	-	7			A	19	3	3	3	3	3			A	19	3	3	3	3	3			A	19	19	3	3	3	3			A	4	4	4	19	19	19	
METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						
			1	2	3	4	5	6				1	2	3	4	5	6				1	2	3	4	5	6				1	2	3	4	5	6				1	2	3	4	5	6	
89025-X83 SEE NOTE 10 LEAD FREE OPTION		E	1	1	1	-	1	1	89025-X87 SEE NOTE 10 LEAD FREE OPTION		E	2	2	2	2	1	2	89025-X91 SEE NOTE 10 LEAD FREE OPTION		E	20	7	7	7	6	5	89025-X95 SEE NOTE 10 LEAD FREE OPTION		E	2	2	2	2	2	2	89025-X99 SEE NOTE 10 LEAD FREE OPTION		E	8	8	8	20	20	20	
		D	1	1	1	-	1	1			D	2	2	2	2	2	2			D	20	7	7	7	6	5			D	2	2	2	2	2	2			D	8	8	8	20	20	20	
		C	1	1	1	-	1	1			C	3	3	3	3	3	3			C	20	7	7	7	6	5			C	1	2	2	2	2	2			C	8	8	8	20	20	20	
		B	1	1	1	-	-	-			B	2	2	2	2	2	2			B	20	7	7	7	6	5			B	2	2	2	2	2	2			B	8	8	8	20	20	20	
		A	1	1	1	1	1	1			A	2	2	2	2	2	2			A	20	7	7	7	6	5			A	2	2	2	2	2	2			A	8	8	8	20	20	20	
METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						METRAL P/N		ROW	CONTACT CODE MOD. I						
			1	2	3	4	5	6				1	2	3	4	5	6				1	2	3	4	5	6				1	2	3	4	5	6				1	2	3	4	5	6	
89025-X84 SEE NOTE 10 LEAD FREE OPTION		E	7	7	7	7	7	7	89025-X88 SEE NOTE 10 LEAD FREE OPTION		E	2	2	2	2	2	2	89025-X92 SEE NOTE 10 LEAD FREE OPTION		E	19	4	4	4	4	4	89025-X96 SEE NOTE 10 LEAD FREE OPTION		E	3	3	3	-	3	3			E	3	3	3	-	3	3	
		D	7	4	1	7	7	7			D	2	2	2	2	2	2			D	19	4	4	4	4	4			D	3	3	3	-	3	3			D	3	3	3	-	3	3	
		C	4	1	7	4	1	7			7	C	4	2	2	2	2			2	C	19	4	4	4	4			4	C	3	3	3	-	3			3	C	3	3	3	-	3	3
		B	7	7	4	1	7	7			7	B	2	2	2	2	2			2	B	19	4	4	4	4			4	B	3	3	3	-	-			-	B	3	3	3	-	-	-
		A	7	7	7	4	5	7			A	2	2	2	2	2	2			A	19	4	4	4	4	4			A	3	3	3	3	3	3			A	3	3	3	3	3	3	

mat'l code				--		tolerances unless otherwise specified				CUSTOMER		FCJ www.fcjconnect.com					
lfr	ecn no.	dr	date	linear	0.X ±0.3				COPY			title	product family size dwg no METRAL 89025			code 213 sheet 7	
CR					0.XX ±0.13				projection								
					.XXX ±.051												
					0° ±2°												
				angles													
				dr	T.BRUNGARD 11/19/99												
				enrg	M.STRAWSER 11/19/99												
				chr	M.STRAWSER 11/19/99												
				appd	M.STRAWSER 02/29/00												
sheet index		revision sheet															

PRODUCT NUMBER

89025-XYX

89025-XYXLF

NOTES:

1. FOR DIM A AND B SEE SHEET 2 AND UP.
2. BODY MATERIAL: LIQUID CRYSTAL
POLYMER 30 % GLASS.
FLAME RETARDANT ACC. UL 94-V0.
3. PIN MATERIAL:
PHOSPHOR BRONZE.
4. PLATING ON PRESS-FIT TAIL:
55422 -XYX IS SnPb
55422-XYXLF IS SN (LEAD FREE)
PLATING ON CONTACT AREA CONFORMS TO PERFORMANCE
LEVEL SHOWN IN TABLE.
5. PRODUCT MARKING:
PART NUMBER DESIGNATION & BATCH I.D.
6. ALL PRODUCTS WITH PART NUMBERS SHOWN IN
SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES.
IF TRAY PACKAGING IS REQUIRED, A SUFFIX "P"
WILL BE ADDED TO THE END OF THE PART NUMBER.
EXAMPLE: XXXXX-XXXP OR XXXXX-XXXPLF
7. PRODUCT SPECIFICATION GS-I2-180
APPLICATION SPECIFICATION BUS-20-073
8. AFTER INSERTION INTO CIRCUIT BOARD WITH
QUALIFIED TOOL.
9. THE PRODUCTS WHERE THE PART NUMBER ENDS IN LF MEET THE
EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS
AS DESCRIBED IN GS-22-008.

ALL PRODUCTS EXCEPT THOSE WITH PART NUMBERS CONTAINING
(DRAWING NO.)-N1--- OR (DRAWING NO.)-N5---WILL WITHSTAND EXPOSURE
TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR
VAPOR PHASE REFLOW OVEN. PART NUMBERS (DRAWING NO.)-N1---
AND (DRAWINGS NO.)-N5---WILL NOT WITHSTAND REFLOW AND Au CONTACT
SURFACE OF THE CONTACTS SHALL BE EXPOSED TO A MAXIMUM 140°C FOR
NO LONGER THAN 15 SECONDS IN A WAVE SOLDER APPLICATION.
10. FOR LEAD FREE PART NUMBERS, ADD AN "LF" SUFFIX.
EXAMPLE: 89025-X01LF

PLATING IN CONTACT AREA

DASH NUMBER	PERFORMANCE LEVEL	NOTES
-N1YY	TELCORDIA CO (NXT)	-
-N5YY	TELCORDIA UE (NXT)	-
-1YY	TELCORDIA CO	-
-2YY	TELECOM CLASS	-
-3YY	IEC CLASS I	-
-5YY	TELCORDIA UE	-
-N1YYLF	TELCORDIA CO (NXT) IEC CLASS I	SEE NOTE 9
-N5YYLF	TELCORDIA UE (NXT)	SEE NOTE 9
-1YYLF	TELCORDIA CO IEC CLASS I	SEE NOTE 9
-2YYLF	TELECOM CLASS	SEE NOTE 9
-5YYLF	TELCORDIA UE	SEE NOTE 9



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI www.fciconnect.com	
ltr	ecn no.	dr	date	linear	0.X ±0.3	COPY		title METRAL SIGNAL HEADER 1 MOD, 5 ROW PRESS-FIT	
CR					0.XX ±0.13	projection			
					.XXX ±.051				
				angles	0° ±2°				
				dr	T.BRUNGARD	11/19/99	MM		product family
				engr	M.STRAWSER	11/19/99			METRAL
				chr	M.STRAWSER	11/19/99	scale		code
				appd	M.STRAWSER	02/29/00	1:1		213
sheet	revision								sheet
index	sheet								8

cage code 22526

Pro/E