

6

5

4




3

2

1

PART NUMBER	ENGINEERING NO.	LENGTH ± TOLERANCE
1300610030	103000A46M020	6' 6.74' +3.50'/-0' [2M +88.9/-0 mm]

AUX VIEW
SCALE 1:4



FACE VIEW
FEMALE

NOTES:

- 1) MATERIAL: SEE TABLE
- 2) FINISHES: SEE TABLE
- 3) WRAP LABEL IS MARKED WITH P/N, DATE CODE, VOLTAGE & AMPERAGE
- 4) ELECTRICAL DATA:
INLINE CORDSET
FEMALE A-SIZE WITH FLYING LEADS
14AWG UNSHIELDED
POLES: 3
MAX. VOLTAGE: 600V
MAX. CURRENT 15A
PROTECTION IP67
TEMPERATURE RANGE: -20°C TO 90°C
- 5) PACKAGING:
CABLE ASSEMBLIES ARE BAGGED SEPARATELY
IN POLY BAGS WITH BAR CODE LABEL ATTACHED
TO OUTSIDE OF BAG.
- 6) ASSEMBLY IS RoHS COMPLIANT.
- 7) CERTIFICATION:
UL2237, FILE NO. E258922

P1

GREEN/YELLOW	1
BLACK	2
WHITE	3

WIRING DIAGRAM

9	1	DANGER LABEL	VINYL	BLACK
8	A/R	MOLDING COMPOUND	PVC	GRAY
7	1	WRAP LABEL	VINYL	YELLOW
6	1	FEMALE COUPLING NUT	ZINC ALLOY	BLACK E-COAT
5	1	FRICTION RING	NYLON	NATURAL
4	3	SOCKET SLEEVE	STAINLESS STEEL	
3	3	SOCKET CONTACT	BRASS	GOLD PLATE
2	1	3P FEMALE INSERT	PVC	BLACK
1	SEE TABLE	#14/3 CABLE	PVC JACKET	GRAY
ITEM	QTY	DESCRIPTION	MATERIAL	FINISH

SD RELEASE	EC NO: WNA2010-0426	DRWN: YOU	2010/01/12	CHKD: BWOODMAN	APPR: JFMURPHY	2010/01/20
1	REV	DESCRIPTION	REV	DESCRIPTION	REV	DESCRIPTION

QUALITY SYMBOLS		
$\nabla = 0$		
$\nabla C = 0$		
GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±.005
2 PLACES	±0.13	±.010
1 PLACE	±0.25	±.020
ANGULAR ±1/2°		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE INCH/MM		SCALE 1:2	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
DRAWN BY _____ DATE _____		TITLE MINI-CHANGE BRAD POWER 3P FP STRAIGHT #14/3 AWG PVC DROP CABLE			
CHECKED BY _____ DATE _____					
BWOODMAN 2010/01/15					
APPROVED BY _____ DATE _____		MOLEX INCORPORATED			
JFMURPHY 2010/01/20					
MATERIAL NO. SEE CHART		DOCUMENT NO. SD-130061-006		SHEET NO. 1 OF 1	
SIZE A	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

6

5

4

3

2

1