


 Close Window

Inductors (Coils)

Inductor Coils

Part Number : **MLG1608B2N7ST000**

Product Name : **Multilayer Inductor for Ultra High Frequency Range**

TDK Series Name : **MLG Series**

Application : **No Data Available.**

Function : **No Data Available.**

Description : **No Data Available.**

Submit Sample Request

Check Distributor Inventory

Print Page

Download Adobe PDF Viewer

MLG1608 TYPE APPEARANCE PHOTOGRAPH



< Prev | No PDF Available| Next >

Additional Search Tools:

Application

Catalog

SEAT

CCV

TVCL

Tech Notes

Property Name	Property Description
Product Lifecycle Stage	Production
Part Number Replacement	<i>No Data Available.</i>
Lead (Pb) Free	Yes
Surface Mount	Yes
Construction Type	multilayer type
Mounting	SMD
Body Length (L)	Nom 1.6 mm
Body Width (W)	Nom 0.8 mm
Body Height (T)	Max <i>No Data Available.</i>
Inductance	Nom 0.0027 μ H
Inductance Tolerance (%)	Min <i>No Data Available.</i> Max <i>No Data Available.</i>
Frequency of Inductance	Nom 100 MHz
Q	Min 10
Frequency of Q	Nom 100 MHz
Self Resonant Frequency	Min 7 GHz
D.C. Resistance	Nom 0.06 Ohm
D.C. Resistance	Max 0.12 Ohm
Rated Current	Max 0.6 A
Terminal Material	Ag(100%)/Sn plating
Polarity Marking	Yes
Magnetic Shielding	No
Soldering Method	Reflow, Iron Soldering
Measuring Equipment(Q)	HP4291A+16193A, or equivalent
Category Temperature Range	Min -55 Cel Max 125 Cel
Storage Temperature Range	Min -55 Cel Max 125 Cel
Country of Origin	JPN
Packing	Punched (Paper)Taping [180mm Reel]
Minimum Package Qty	Nom 4000 Pcs
Minimum Order Qty	Nom 4000 Pcs
Weight	Nom 0.004 g

Disclaimer: This information is to be used for reference purposes only and is subject to change by TDK without notice. It reflects an overview of the product characteristics/performance for the particular part number. For product specification information, please refer to TDK's general product specification. Please note that this standard part is not designed or warranted to meet any specifications of any

intermediate or end user different from or in addition to the specifications set forth in TDK's general product specification. Note also that this standard part has not been specially designed or manufactured for, nor is it intended or warranted for use in, or permitted to be resold for, specialized applications such as aviation, medical, and/or governmental/military applications (collectively, "Excluded Applications").

© TDK U.S.A. Corporation 2011. » [Privacy Statement](#) » [Careers](#) » [Site Map](#)
TDK Logo is a trademark or registered trademark of TDK Corporation.