



1825136-6 Product Details


[Share](#)

[Print](#)

[Email](#)


1825136-6

TE Internal Number: 1825136-6



Active

Toggle Switches



[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- A Series
- Single Pole - Double Throw Configuration (Pole-Throw)
- Current Rating = 5 A
- Mount Style = Through-Hole
- Termination Type = Right Angle

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)



[Add to My Part List](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [GEMINI A SERIES TOGGLE SWITCH, SINGLE POLE, 2 POSITI...](#) (PDF, English)

Catalog Pages/Data Sheets:

- [SWITCHES CORE PROGRAM CATALOG](#) (PDF, English)
- [GEMINI SERIES SWITCHES QUICK REF GUIDE 2-1773458-5](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Product Photo](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Series = A
- Configuration (Pole-Throw) = Single Pole - Double Throw
- Termination Type = Right Angle

Electrical Characteristics:

- Current Rating (A) = 5

Termination Features:

- Seal Type = Terminal Seal (epoxy)

Body Features:

- Mount Style = Through-Hole

Contact Features:

- Contact Plating = Silver

Housing Features:

- Toggle Actuation = Horizontal
- Toggle Style = Locking
- Toggle Length (mm [in]) = 16.28 [0.641]
- Process Sealed = No
- Bushing Style = Unthreaded
- Bushing Type = Plain

Configuration Features:

- [Operating Function](#) = On On

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Alcoswitch

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

