

(0,80 mm) .0315"

MECT SERIES

MECT-110-01-M-D-RA1

MECT-115-01-M-D-RA1

MECT-135-01-M-D-RA1

SFP & SFP+ TRANSCEIVER INTERFACES

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?MECT

Insulator Material:

Black LCP

Contact Material:

Phosphor Bronze

Plating:

Sn or Au over

100µ" (2,54 µm) Ni

Operating Temp Range:

-55°C to +125°C

Current Rating:

2A per contact

@ 80°C ambient

(see website for details)

Voltage Rating:

265 VAC

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0,10 mm) .004" max (10-35)




Mates with:
SFP, SFP+, XFP or
XENPAK transceivers

2x10 position for
Small Form Factor
Pluggable (SFP & SFP+)
Fiber Optic Transceivers





2x10, 2x15 and
2x35 position for
XENPAK and XFP
Transceivers

Alignment
Pin

Choice of
three standard
pin counts



APPLICATION



Note: Some sizes, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292
SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-6083 3766
SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683