


## Heyco® RDD Lockit™ Strain Relief Bushings – Straight-Thru

**Snap onto Round Cables for Faster Assembly into Double D Mounting Holes - Semi-Automatic Equipment Available**

- **Assembly friendly!** Independent of insertion into the panel, RDD Lockit™ Strain Reliefs **self-lock** onto the cable. Preassemble RDD Lockits off line for final assembly at a later time or remote location, for lower installed cost!
- Install easily with fingertip pressure into a standard round or Double D hole. No tools required, even for hand assembly.
- Protect the lifeline of your electric/electronic products by absorbing the forces of push and pull that may be exerted on the flexible power cord. Double D design eliminates the possibility of part rotation under forces of twist.
- Multiple panel locking steps secure Lockit Strain Reliefs into a wide range of panel thicknesses for a **flush, finished fit**.
- Heyco's automated Pre-Assembly Equipment speeds assembly of the RDD onto the cable and thus lowers costs while greatly reducing risk of carpal tunnel syndrome. See pages 4-15 & 4-16.
- Consult Heyco for other wire types and sizes.
- See page 4-38 for corresponding **Mounting Hole Plugs** which can be used to fill blank/unused Mounting Holes and thus allow for a single panel design for multiple applications.

UL Type	WILL FIT THESE CABLES			PANEL DIMENSIONS				RDD LOCKIT STRAIN RELIEF for Faster Assembly			Corresponding Mounting Hole Plug PART NO.	DESC.
	AWG/Conductors	Approximate Size in. mm.	Mounting Hole Size in. mm.	Thickness in. mm.	Black	White	Part No.	Desc.				
AWN SJTO & SJ	18/3	.130-.210 3,3-5,3	.625 w/.550 flats	15,9 w/14,0 flats	.032 .040 .048 .063 .099	0,8 1,1 1,2 1,6 2,5	1870 1871	RDD 101-A	2497	DD 625-550		
See table on page 4-10	various	.220-.290 5,6-7,4	.625 w/.550 flats	15,9 w/14,0 flats	.032 .040 .048 .063 .099	0,8 1,1 1,2 1,6 2,5	1852 1853	RDD 101	2497	DD 625-550		
SJT SJO	18/3	.300-.330 7,6-8,4	.625 w/.550 flats	15,9 w/14,0 flats	.062	1,6	1800 1801	RDD 6N-2	2497	DD 625-550		

Standard color black. Consult Heyco for white and other colors.



## Quick Specs

Material  
Certifications

Nylon 6/6

Recognized under UL File E15331

Certified by the Canadian Standards Association File 8919

Flammability Rating  
Temperature Range

94V-2

-.04°F (-18°C) to 221°F (105°C)