

Wiha Insulated T-handles

Insulation Test Standards:

Insulation according to EN/IEC 60900,
ASTM F-1505-01, New VDE 0682/part 201,
DIN 7437, NFPA70E


Responds to OSHA's use
specification 29 CFR1910

Each tool individually
tested to 10,000 volts
and certified to 1000
Volt ac or 1500 Volt dc

Insulation
molded directly onto blade
for permanent bonding

Blade
CVM tool steel, hardened
to average 58/60RC

 **1000V**



 **1000Volt**


SHOP

334 Inch T-handle, With Wiha-Molded Handle Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E,  up to 1000 Volt. Individually Tested.

Blade CVM steel, hardened. Insulation molded directly onto blade.

Wiha-SoftFinish® handle, multi-component.

Item						
No.	Inch	Inch	Inch	mm	lbs.	pkg.
334 81	5/32	5.9	6.9	176	.09	10
334 82	3/16	5.9	6.9	176	.15	10
334 83	7/32	5.9	6.9	176	.19	10
334 85	1/4	6.9	6.9	176	.20	10
334 86	5/16	6.9	6.9	176	.26	10
334 87	3/8	6.9	6.9	176	.44	10



 **1000Volt**

SHOP

334 Metric T-handle, With Wiha-Molded Handle Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E,  up to 1000 Volt. Individually Tested.

Blade CVM steel, hardened. Insulation molded directly onto blade.

Wiha-SoftFinish® handle, multi-component.

Item						
No.	mm	mm	Inch	mm	Inch	lbs.
334 41	4.0	150	5.9	176	6.9	.09
334 43	5.0	150	5.9	176	6.9	.15
334 45	6.0	150	5.9	176	6.9	.18
334 47	8.0	150	5.9	176	6.9	.26

PREVIOUS



 **1000Volt**

SHOP

334 90 Set 6 Pcs. Inch T-handle Hex

Item						
No.	Inch	Inch	Inch	Inch	Inch	lbs.
334 90	334 81	5/32	6.9	334 85	1/4	6.9
	334 82	3/16	6.9	334 86	5/16	6.9
	334 83	7/32	6.9	334 87	3/8	6.9



 **1000Volt**

SHOP

334 91 Set 4 Pcs. Metric T-handle Hex

Item						
No.	mm	mm	mm	mm	mm	.99 lbs.
334 91	334 41	4.0	150	334 45	6.0	150
	334 43	5.0	150	334 47	8.0	150

NEXT