





D

C



B

A



PC BOARD LAYOUT
RECOMMENDED PC BOARD THICKNESS 1.57[.062]

- 1 HOUSING MATERIAL: GLASS-FILLED POLYMER.
- 2 CONTACT MATERIAL: COPPER ALLOY.
- 3 CONTACT FINISH: DIN 41612 CLASS 2 IN CONTACT AREA. TIN PLATE ON POSTS.
- 4 RECOMMENDED HOLE SIZE FOR MANUAL APPLICATION OF CONNECTOR ONTO PC BOARD.
- 5 PART NUMBER, DATE CODE IDENTIFICATION, CSA LOGO THIS APPROXIMATE AREA.
- 6 CONTACT POINT.
- 7 MARKING ON THIS SIDE.



		1 THRU 50		X	X	X	150	5650959-5	
		POSITIONS LOADED		C	B	A	NO. OF LOADED POSITIONS	ASSY PART NUMBER	
				ROWS LOADED					
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWG	J. POLIGNONE		03JUN05	Tyco Electronics Corporation	
				CHK	A. SHARPE		03JUN05	Harriburg, Pa 17105-3608	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APP'D	A. SHARPE		03JUN05	NAME	
mm [INCHES]		0 PLC ± -		PRODUCT SPEC		ASSEMBLY, RECEPTACLE, EUROCARD, TYPE R, LEAD-FREE, 150 POSITION, 2.79[.110] SOLDER POSTS, WITH BOARD LOCKS			
		1 PLC ± 0.13[.005]		APPLICATION SPEC					
		2 PLC ± -							
		3 PLC ± -							
		4 PLC ± -							
ANGLES		± -							
MATERIAL		FINISH		WEIGHT		-		RESTRICTED TO	
						SIZE		CAGE CODE	
						DRAWING NO		DRAWING NO	
						A1		00779	
						C=5650959			
						SCALE		SHEET	
						4:1		1 OF 1	
						CUSTOMER DRAWING		REV	
								O	