



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D2	REVISED PER ECO-16-004986	20JUN2016	NK	DR

AMP WIRE RANGE	 E13288 Listed
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED




  LR7189 Certified	MILITARY P/N AND CLASS
22-16 AWG SOLID OR STRANDED	NOT APPLICABLE



- 1 STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPEC SAER AS7928
COMMERCIAL WIRE RANGE IS 22-16.
- 2 TIN PL 0.00254[.000100] MIN THK
PER ASTM B545.
- 3 GOLD PL 0.00127[.000050] MIN THK
PER MIL-G-45204 OVER NICKEL PL
0.00076[.000030] MIN THK PER SAE AMS QQ-N-290.
- 4 TIN LEAD PLATE 0.01016-0.02032
[.000400-.000080] THK PER MIL-P-81728.
- 5 PRE-PRODUCTION - FASR REQ.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 170°C[338°F] MAX
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: NOT APPLICABLE
FOR ORDER ENTRY	1-800-526-5142	WIRE CROSS SECTIONAL AREA RANGE: 0.26-1.65mm ² [509-3,260] CIR MILS SOLID OR STRANDED

6 7	4	1000	LOOSE PIECE	5 34108-2
	2	100	LOOSE PIECE, BOX	8-34108-1
6 7	2	5000	ON TAPE	2-34108-2
6 7	3	1000	LOOSE PIECE	1-34108-1
	2	1000	LOOSE PIECE	34108
	FINISH	QUANTITY	PACKAGING TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-10-93	 TE Connectivity		
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK DA PATTERSON 3-10-93			
	0 PLC ± -	APVD DE MILLER 3-10-93	NAME		
	1 PLC ± -	PRODUCT SPEC	TERMINAL, RING TONGUE, SOLISTRAND		
	2 PLC ± -	APPLICATION SPEC	SIZE		
	3 PLC ± -	—	CAGE CODE		
	4 PLC ± -	—	DRAWING NO		
	ANGLES ± -	—	RESTRICTED TO		
MATERIAL COPPER PER ASTM B-152 ANNEALED	FINISH	WEIGHT	A2 00779 C=34108		
SEE TABLE		CUSTOMER DRAWING	SCALE	SHEET	REV
			10:1	1 OF 1	D2