




MATERIAL NO. LOOSE PIECE	ENG. NO.	STUD SIZE	±.003 "S"	STOCK THICKNESS
191930237	E-359-14	1/4	.265	.050/(1.27) (B)
191930240	E-359-56	5/16	.328	
191930239	E-359-38	3/8	.390	
191930242	E-359-76	7/16	.453	
191930236	E-359-12	1/2	.515	
191930241	E-359-58	5/8	.656	
191930238	E-359-34	3/4	.781	

NOTE(S):
1. MATERIAL: COPPER
2. PLATING: ELECTROPLATE TIN
3. ALL DIMENSIONS IN INCHES/(MM).
4. WIRE SIZE: 6 AWG
16 MM²
(B) 5. PART IS ROHS COMPLIANT.

REVISED MATL THKNS EC NO: ET2007-0003 DRW: NEHLE 2006/07/12 CHKD: MACNEIL 2006/07/19 APPR: ROERSS 2006/07/26 B	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION
			mm	INCH	DRAWN BY DLM	DATE 03/07/28	RING TONGUE TERMINAL VERSAKRIMP SERIES 6 AWG MOLEX INCORPORATED		
			4 PLACES ±---	±---	CHECKED BY HEB	DATE 03/07/28			
			3 PLACES ±---	±.005	APPROVED BY RWD	DATE 03/07/28			
			2 PLACES ±0.13	±.01	MATERIAL NO. SEE CHART				
	1 PLACE ±0.25	±---	ANGULAR ±1/2°		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
REV			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE B				