





① HSG MATL: POLYPHENYLENE SULFIDE, COLOR—NATURAL (BROWN).
② POST MATL: PHOSPHOR BRONZE.
③ POST FINISH: .000050—.000100 NICKEL UNDERPLATE ALL OVER.
.000030 GOLD IN CONTACT AREA AND LOWER .200 OF POSTS.
GOLD FLASH ON REMAINDER.

4. FOR CONNECTORS USED IN STACKING APPLICATIONS, .125 NOMINAL THICK PRINTED CIRCUIT BOARD SHOULD BE USED.

⑤ ACTION PIN POSTS REQUIRE .093 MIN THK PC BOARD.
RECOMMENDED PC BOARD HOLES ARE .0453 DIA PLATED THROUGH WITH .001—.003 COPPER AND .0003 MIN TIN—LEAD PLATING.
FINISHED HOLE AFTER PLATING, .037—.043 DIA.


⑥ TE, PART NO. & DATE CODE MARKED IN THIS APPROXIMATE AREA.



RECOMMENDED PC BOARD LAYOUT

OBSOLETE

OBSOLETE	4.100	41	4.224	4.650	4.950	168	1-533656-3	
OBSOLETE	7.400	74	7.524	7.950	8.250	300	1-533656-2	
OBSOLETE	6.900	69	7.024	7.450	7.750	280	1-533656-1	
OBSOLETE	6.400	64	6.524	6.950	7.250	260	1-533656-0	
OBSOLETE	5.900	59	6.024	6.450	6.750	240	533656-9	
OBSOLETE	5.400	54	5.524	5.950	6.250	220	533656-8	
OBSOLETE	4.900	49	5.024	5.450	5.750	200	533656-7	
OBSOLETE	4.400	44	4.524	4.950	5.250	180	533656-6	
OBSOLETE	3.900	39	4.024	4.450	4.750	160	533656-5	
OBSOLETE	3.400	34	3.524	3.950	4.250	140	533656-4	
OBSOLETE	3.100	31	3.224	3.650	3.950	128	533656-3	
OBSOLETE	2.900	29	3.024	3.450	3.750	120	533656-2	
	2.400	24	2.524	2.950	3.250	100	533656-1	
	E	D	C	B	A	POSN	PART	NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. SEIFRIED CHK G. STEINHAUER APVD E. PARSONS 1/29/85 6/5/87 6/5/87		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		NAME RECEPTACLE CONNECTOR WITH .500 LONG ACTION PIN POSTS, 4-RW, SPECIAL PLATING	
MATERIAL		FINISH		SIZE	RESTRICTED TO
				CAGE CODE A2 00779	DRAWING NO C-533656
CUSTOMER DRAWING				SCALE	REV
				4:1	2 of 2