







SYMBOL DEFINITION			MISSING NUMBERS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON AN INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF SYMBOLS ON DRAWING	10	9,	
	LAST NO. USED	22		


DWG STATUS						ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG							
13JA00	R	005	-	-			CLEARED REV COLUMN, (35.54) WAS (35.53) AND REVISED GRAPHICS	198462	KBD	TLP	CSD
18DE00	R	005	AA	-			31.2±0.15 DIM REMOVED	205385	TLD	TLD	MB
16FE01	R	005	AB	-			REVISED PROCESS SENSITIVE DIM FROM 9 TO 1	206700	JMR	JMR	MB
22MR02	R	006	-	-			MAT'L WAS PM003571-018	222262	TLD	TLD	MB
24N004	R	06	AA	-			ADDED NOTES #3 & 4; FIXED MATERIAL SPEC	261518	END	END	ET
26MY05	R	06	AB	-			REVISED DIM (5 PLCS) AND ADDED NOTE 5	268591	HAM	HAM	MDM
09JN05	R	06	AC	-			UPDATED PDM ATTRIBUTES	268323	HAM	HAM	MDM
15JL05	R	06	AD	-			ADDED OPTIONAL CONSTRUCTION DESIGNATION TO NOTES 2 & 4	270028	TAI	TAI	MDM



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE PER ISO 11469. (1)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION IS NO RECYCLING CODE.
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
CONNECTOR 15317360
- (1)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED" OR NO LOGO.
- PART MUST BE FIXTURED WHEN MEASURING THESE DIMENSIONS.

DIMENSIONAL RANGE (MM)											
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400	CHART E1
TO	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400	
TOLERANCE UNLESS OTHERWISE SPECIFIED											
ANGULAR TOLERANCE ±2°											

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CM³)		DISTR CODE	
0.470		D	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION		DO NOT SCALE	
			

DELPHI											
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH											
DR										DATE	
APVD1 M. M. RUBERTO										14N096	
APVD2 M. M. RUBERTO										14N096	
APVD3 ED ARANGO										27N096	
APVD4											
APVD5											
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001											
MATERIAL M2279025 PA66-GF14 1M HS GRA MD											
DRAWING NAME											
LOCK TPA GT 150 GRA MD											
DRAWING NUMBER											
15317363											
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P					
A1	5:1	1 OF 1	1 OF 1	R	06	AD					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delphi Connection Systems:](#)

[15317363-B](#)