Voltage Regulators – Positive

1.0 A

MC7800, MC7800A, MC7800AE, NCV7800

These voltage regulators are monolithic integrated circuits designed as fixed−voltage regulators for a wide variety of applications including local, on−card regulation. These regulators employ internal current limiting, thermal shutdown, and safe−area compensation. With adequate heatsinking they can deliver output currents in excess of 1.0 A. Although designed primarily as a fixed voltage regulator, these devices can be used with external components to obtain adjustable voltages and currents.

Features

- Output Current in Excess of 1.0 A
- No External Components Required
- Internal Thermal Overload Protection
- Internal Short Circuit Current Limiting
- Output Transistor Safe−Area Compensation
- Output Voltage Offered in 1.5%, 2% and 4% Tolerance
- Available in Surface Mount D^2PAK−3, DPAK−3 and Standard 3−Lead Transistor Packages
- NCV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC−Q100 Qualified and PPAP Capable
- These are Pb−Free Devices

MAXIMUM RATINGS (T_A = 25°C, unless otherwise noted)

Rating	Symbol	Value			Unit
		369C	221A	936	
Input Voltage (5.0 – 18 V) (24 V)	V_I	35 40			Vdc
Power Dissipation	P_D	Internally Limited			W
Thermal Resistance, Junction−to−Ambient	$R_{\theta JA}$	92	65	Figure 15	°C/W
Thermal Resistance, Junction−to−Case	$R_{\theta JC}$	5.0	5.0	5.0	°C/W
Storage Junction Temperature Range	T_{stg}	−65 to +150			°C
Operating Junction Temperature	T_J	+150			°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

*This device series contains ESD protection and exceeds the following tests:
Human Body Model 2000 V per MIL_STD_883, Method 3015.
Machine Model Method 200 V.



TO−220
T SUFFIX
CASE 221AB

Heatsink surface connected to Pin 2.



Pin 1. Input
2. Ground
3. Output

D^2PAK−3
D2T SUFFIX
CASE 936

Heatsink surface (shown as terminal 4 in case outline drawing) is connected to Pin 2.



DPAK−3
DT SUFFIX
CASE 369C

STANDARD APPLICATION



A common ground is required between the input and the output voltages. The input voltage must remain typically 2.0 V above the output voltage even during the low point on the input ripple voltage.

XX, These two digits of the type number indicate nominal voltage.

* C_{in} is required if regulator is located an appreciable distance from power supply filter.

** C_O is not needed for stability; however, it does improve transient response. Values of less than 0.1 μF could cause instability.

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 21 of this data sheet.

DEVICE MARKING INFORMATION

See general marking information in the device marking section on page 24 of this data sheet.

© Semiconductor Components Industries, LLC, 2014



This device contains 22 active transistors.

Figure 1. Representative Schematic Diagram

Share Feedback
Your Opinion Matters

ELECTRICAL CHARACTERISTICS (V_{in} = 10 V, I_O = 500 mA, T_J = T_{low} to 125°C (Note 1), unless otherwise noted)

Characteristic	Symbol	MC7805B, NCV7805B			MC7805C			Unit
		Min	Typ	Max	Min	Typ	Max	
Output Voltage (T_J = 25°C)	V_O	4.8	5.0	5.2	4.8	5.0	5.2	Vdc
Output Voltage (5.0 mA ≤ I_O ≤ 1.0 A, P_D ≤ 15 W) 7.0 Vdc ≤ V_{in} ≤ 20 Vdc 8.0 Vdc ≤ V_{in} ≤ 20 Vdc	V_O	 – 4.75	 – 5.0	 – 5.25	 4.75 –	 5.0 –	 5.25 –	Vdc
Line Regulation (Note 4) 7.5 Vdc ≤ V_{in} ≤ 20 Vdc, 1.0 A 8.0 Vdc ≤ V_{in} ≤ 12 Vdc	Reg_{line}	 – –	 5.0 1.3	 100 50	 – –	 0.5 0.8	 20 10	mV
Load Regulation (Note 4) 5.0 mA ≤ I_O ≤ 1.0 A 5.0 mA ≤ I_O ≤ 1.5 A (T_A = 25°C)	Reg_{load}	 – –	 1.3 0.15	 100 50	 – –	 1.3 1.3	 25 25	mV
Quiescent Current	I_B	–	3.2	8.0	–	3.2	6.5	mA
Quiescent Current Change 7.0 Vdc ≤ V_{in} ≤ 25 Vdc 5.0 mA ≤ I_O ≤ 1.0 A (T_A = 25°C)	ΔI_B	 – –	 – –	 – 0.5	 – –	 0.3 0.08	 1.0 0.8	mA
Ripple Rejection 8.0 Vdc ≤ V_{in} ≤ 18 Vdc, f = 120 Hz	RR	 –	 68	 –	 62	 83	 –	dB
Dropout Voltage (I_O = 1.0 A, T_J = 25°C)	$V_I - V_O$	–	2.0	–	–	2.0	–	Vdc
Output Noise Voltage (T_A = 25°C) 10 Hz ≤ f ≤ 100 kHz	V_n	 –	 10	 –	 –	 10	 –	μV/V_O
Output Resistance f = 1.0 kHz	r_O	–	0.9	–	–	0.9	–	mΩ
Short Circuit Current Limit (T_A = 25°C) V_{in} = 35 Vdc	I_{SC}	 –	 0.2	 –	 –	 0.6	 –	A
Peak Output Current (T_J = 25°C)	I_{max}	–	2.2	–	–	2.2	–	A
Average Temperature Coefficient of Output Voltage	TCV_O	–	–0.3	–	–	–0.3	–	mV/°C

1. T_{low} = 0°C for MC78XXC, MC78XXAC,
   = −40°C for NCV78XX, MC78XXB, MC78XXAB, and MC78XXAEB
2. Load and line regulation are specified at constant junction temperature. Changes in V_O due to heating effects must be taken into account separately. Pulse testing with low duty cycle is used.

Share Feedback
Your Opinion Matters

ELECTRICAL CHARACTERISTICS (V_{in} = 10 V, I_O = 1.0 A, T_J = T_{low} to 125°C (Note 3), unless otherwise noted)

Characteristic	Symbol	MC7805AB/MC7805AC/NCV7805AB			Unit
		Min	Typ	Max	
Output Voltage (T_J = 25°C)	V_O	4.9	5.0	5.1	Vdc
Output Voltage (5.0 mA ≤ I_O ≤ 1.0 A, P_D ≤ 15 W) 7.5 Vdc ≤ V_{in} ≤ 20 Vdc	V_O	4.8	5.0	5.2	Vdc
Line Regulation (Note 4) 7.5 Vdc ≤ V_{in} ≤ 25 Vdc, I_O = 500 mA 8.0 Vdc ≤ V_{in} ≤ 12 Vdc, I_O = 1.0 A 8.0 Vdc ≤ V_{in} ≤ 12 Vdc, I_O = 1.0 A, T_J = 25°C 7.3 Vdc ≤ V_{in} ≤ 20 Vdc, I_O = 1.0 A, T_J = 25°C	Reg_{line}	 – – – –	 0.5 0.8 1.3 4.5	 10 12 4.0 10	mV
Load Regulation (Note 4) 5.0 mA ≤ I_O ≤ 1.5 A, T_J = 25°C 5.0 mA ≤ I_O ≤ 1.0 A 250 mA ≤ I_O ≤ 750 mA	Reg_{load}	 – – –	 1.3 0.8 0.53	 25 25 15	mV
Quiescent Current	I_B	–	3.2	6.0	mA
Quiescent Current Change 8.0 Vdc ≤ V_{in} ≤ 25 Vdc, I_O = 500 mA 7.5 Vdc ≤ V_{in} ≤ 20 Vdc, T_J = 25°C 5.0 mA ≤ I_O ≤ 1.0 A	ΔI_B	 – – –	 0.3 – 0.08	 0.8 0.8 0.5	mA
Ripple Rejection 8.0 Vdc ≤ V_{in} ≤ 18 Vdc, f = 120 Hz, I_O = 500 mA	RR	 68	 83	 –	dB
Dropout Voltage (I_O = 1.0 A, T_J = 25°C)	$V_I - V_O$	–	2.0	–	Vdc
Output Noise Voltage (T_A = 25°C) 10 Hz ≤ f ≤ 100 kHz	V_n	 –	 10	 –	μV/V_O
Output Resistance (f = 1.0 kHz)	r_O	–	0.9	–	mΩ
Short Circuit Current Limit (T_A = 25°C) V_{in} = 35 Vdc	I_{SC}	 –	 0.2	 –	A
Peak Output Current (T_J = 25°C)	I_{max}	–	2.2	–	A
Average Temperature Coefficient of Output Voltage	TCV_O	–	–0.3	–	mV/°C

3. T_{low} = 0°C for MC78XXC, MC78XXAC,
   = −40°C for NCV78XX, MC78XXB, MC78XXAB, and MC78XXAEB
4. Load and line regulation are specified at constant junction temperature. Changes in V_O due to heating effects must be taken into account separately. Pulse testing with low duty cycle is used.

Share Feedback
Your Opinion Matters

ELECTRICAL CHARACTERISTICS (V_{in} = 14 V, I_O = 500 mA, T_J = T_{low} to 125°C (Note 5), unless otherwise noted)

Characteristic	Symbol	MC7808B/NCV7808B			MC7808C			Unit
		Min	Typ	Max	Min	Typ	Max	
Output Voltage (T_J = 25°C)	V_O	7.7	8.0	8.3	7.7	8.0	8.3	Vdc
Output Voltage (5.0 mA ≤ I_O ≤ 1.0 A, P_D ≤ 15 W) 10.5 Vdc ≤ V_{in} ≤ 23 Vdc 11.5 Vdc ≤ V_{in} ≤ 23 Vdc	V_O	 – 7.6	 – 8.0	 – 8.4	 7.6 –	 8.0 –	 8.4 –	Vdc
Line Regulation, T_J = 25°C, (Note 6) 10.5 Vdc ≤ V_{in} ≤ 25 Vdc 11 Vdc ≤ V_{in} ≤ 17 Vdc	Reg_{line}	 – –	 6.0 1.7	 160 80	 – –	 6.0 1.7	 32 16	mV
Load Regulation, T_J = 25°C (Note 6) 5.0 mA ≤ I_O ≤ 1.5 A	Reg_{load}	 –	 1.4	 160	 –	 1.4	 35	mV
Quiescent Current	I_B	–	3.3	8.0	–	3.3	8.0	mA
Quiescent Current Change 10.5 Vdc ≤ V_{in} ≤ 25 Vdc 5.0 mA ≤ I_O ≤ 1.0 A	ΔI_B	 – –	 – –	 – 0.5	 – –	 – –	 1.0 0.5	mA
Ripple Rejection 11.5 Vdc ≤ V_{in} ≤ 18 Vdc, f = 120 Hz	RR	 –	 62	 –	 56	 62	 –	dB
Dropout Voltage (I_O = 1.0 A, T_J = 25°C)	$V_I - V_O$	–	2.0	–	–	2.0	–	Vdc
Output Noise Voltage (T_A = 25°C) 10 Hz ≤ f ≤ 100 kHz	V_n	 –	 10	 –	 –	 10	 –	μV/V_O
Output Resistance f = 1.0 kHz	r_O	–	0.9	–	–	0.9	–	mΩ
Short Circuit Current Limit (T_A = 25°C) V_{in} = 35 Vdc	I_{SC}	 –	 0.2	 –	 –	 0.2	 –	A
Peak Output Current (T_J = 25°C)	I_{max}	–	2.2	–	–	2.2	–	A
Average Temperature Coefficient of Output Voltage	TCV_O	–	–0.4	–	–	–0.4	–	mV/°C

5. T_{low} = 0°C for MC78XXC, MC78XXAC,
   = −40°C for NCV78XX, MC78XXB, MC78XXAB, and MC78XXAEB
6. Load and line regulation are specified at constant junction temperature. Changes in V_O due to heating effects must be taken into account separately. Pulse testing with low duty cycle is used.

Share Feedback
Your Opinion Matters

ELECTRICAL CHARACTERISTICS (V_{in} = 14 V, I_O = 1.0 A, T_J = T_{low} to 125°C (Note 7), unless otherwise noted)

Characteristic	Symbol	MC7808AB/MC7808AC/NCV7808AB			Unit
		Min	Typ	Max	
Output Voltage (T_J = 25°C)	V_O	7.84	8.0	8.16	Vdc
Output Voltage (5.0 mA ≤ I_O ≤ 1.0 A, P_D ≤ 15 W) 10.6 Vdc ≤ V_{in} ≤ 23 Vdc	V_O	7.7	8.0	8.3	Vdc
Line Regulation (Note 8) 10.6 Vdc ≤ V_{in} ≤ 25 Vdc, I_O = 500 mA 11 Vdc ≤ V_{in} ≤ 17 Vdc, I_O = 1.0 A 10.4 Vdc ≤ V_{in} ≤ 23 Vdc, T_J = 25°C	Reg_{line}	 – – –	 6.0 1.7 5.0	 15 18 15	mV
Load Regulation (Note 8) 5.0 mA ≤ I_O ≤ 1.5 A, T_J = 25°C 5.0 mA ≤ I_O ≤ 1.0 A 250 mA ≤ I_O ≤ 750 mA	Reg_{load}	 – – –	 1.4 1.0 0.22	 25 25 15	mV
Quiescent Current	I_B	–	3.3	6.0	mA
Quiescent Current Change 11 Vdc ≤ V_{in} ≤ 25 Vdc, I_O = 500 mA 10.6 Vdc ≤ V_{in} ≤ 23 Vdc, I_O = 1.0 A, T_J = 25°C 5.0 mA ≤ I_O ≤ 1.0 A	ΔI_B	 – – –	 – – –	 0.8 0.8 0.5	mA
Ripple Rejection 11.5 Vdc ≤ V_{in} ≤ 21.5 Vdc, f = 120 Hz, I_O = 500 mA	RR	56	62	–	dB
Dropout Voltage (I_O = 1.0 A, T_J = 25°C)	$V_I - V_O$	–	2.0	–	Vdc
Output Noise Voltage (T_A = 25°C) 10 Hz ≤ f ≤ 100 kHz	V_n	–	10	–	μV/V_O
Output Resistance f = 1.0 kHz	r_O	–	0.9	–	mΩ
Short Circuit Current Limit (T_A = 25°C) V_{in} = 35 Vdc	I_{SC}	–	0.2	–	A
Peak Output Current (T_J = 25°C)	I_{max}	–	2.2	–	A
Average Temperature Coefficient of Output Voltage	TCV_O	–	–0.4	–	mV/°C

7. T_{low} = 0°C for MC78XXC, MC78XXAC,
   = −40°C for NCV78XX, MC78XXB, MC78XXAB, and MC78XXAEB
8. Load and line regulation are specified at constant junction temperature. Changes in V_O due to heating effects must be taken into account separately. Pulse testing with low duty cycle is used.

Share Feedback
Your Opinion Matters

ELECTRICAL CHARACTERISTICS (V_{in} = 15 V, I_O = 500 mA, T_J = T_{low} to 125°C (Note 9), unless otherwise noted)

Characteristic	Symbol	MC7809B/NCV7809B			MC7809C			Unit
		Min	Typ	Max	Min	Typ	Max	
Output Voltage (T_J = 25°C)	V_O	8.65	9.0	9.35	8.65	9.0	9.35	Vdc
Output Voltage (5.0 mA ≤ I_O ≤ 1.0 A, P_D ≤ 15 W) 11.5 Vdc ≤ V_{in} ≤ 24 Vdc	V_O	8.55	9.0	9.45	8.55	9.0	9.45	Vdc
Line Regulation, T_J = 25°C (Note 10) 11 Vdc ≤ V_{in} ≤ 26 Vdc 11.5 Vdc ≤ V_{in} ≤ 17 Vdc	Reg_{line}	– –	6.2 1.8	32 16	– –	6.2 1.8	32 16	mV
Load Regulation, T_J = 25°C (Note 10) 5.0 mA ≤ I_O ≤ 1.5 A	Reg_{load}	–	1.5	35	–	1.5	35	mV
Quiescent Current	I_B	–	3.4	8.0	–	3.4	8.0	mA
Quiescent Current Change 11.5 Vdc ≤ V_{in} ≤ 26 Vdc 5.0 mA ≤ I_O ≤ 1.0 A	ΔI_B	– –	– –	1.0 0.5	– –	– –	1.0 0.5	mA
Ripple Rejection 11.5 Vdc ≤ V_{in} ≤ 21.5 Vdc, f = 120 Hz	RR	56	61	–	56	61	–	dB
Dropout Voltage (I_O = 1.0 A, T_J = 25°C)	$V_I - V_O$	–	2.0	–	–	2.0	–	Vdc
Output Noise Voltage (T_A = 25°C) 10 Hz ≤ f ≤ 100 kHz	V_n	–	10	–	–	10	–	μV/V_O
Output Resistance f = 1.0 kHz	r_O	–	1.0	–	–	1.0	–	mΩ
Short Circuit Current Limit (T_A = 25°C) V_{in} = 35 Vdc	I_{SC}	–	0.2	–	–	0.2	–	A
Peak Output Current (T_J = 25°C)	I_{max}	–	2.2	–	–	2.2	–	A
Average Temperature Coefficient of Output Voltage	TCV_O	–	−0.5	–	–	−0.5	–	mV/°C

9. T_{low} = 0°C for MC78XXC, MC78XXAC,
   = −40°C for NCV78XX, MC78XXB, MC78XXAB, and MC78XXAEB
10. Load and line regulation are specified at constant junction temperature. Changes in V_O due to heating effects must be taken into account separately. Pulse testing with low duty cycle is used.

Share Feedback
Your Opinion Matters

ELECTRICAL CHARACTERISTICS (V_{in} = 15 V, I_O = 1.0 A, T_J = T_{low} to 125°C (Note 11), unless otherwise noted)

Characteristic	Symbol	MC7809AB/MC7809AC			Unit
		Min	Typ	Max	
Output Voltage (T_J = 25°C)	V_O	8.82	9.0	9.18	Vdc
Output Voltage (5.0 mA ≤ I_O ≤ 1.0 A, P_D ≤ 15 W) 11.5 Vdc ≤ V_{in} ≤ 24 Vdc	V_O	8.65	9.0	9.35	Vdc
Line Regulation (Note 12) 11.5 Vdc ≤ V_{in} ≤ 26 Vdc, I_O = 500 mA 12 Vdc ≤ V_{in} ≤ 17 Vdc, I_O = 1.0 A 11.5 Vdc ≤ V_{in} ≤ 24 Vdc, T_J = 25°C	Reg_{line}	 – – –	 6.2 1.8 5.2	 16 7.0 16	mV
Load Regulation (Note 12) 5.0 mA ≤ I_O ≤ 1.5 A, T_J = 25°C 5.0 mA ≤ I_O ≤ 1.0 A 250 mA ≤ I_O ≤ 750 mA	Reg_{load}	 – – –	 – – –	 25 25 15	mV
Quiescent Current	I_B	–	3.3	6.0	mA
Quiescent Current Change 11.5 Vdc ≤ V_{in} ≤ 26 Vdc, I_O = 500 mA 11.5 Vdc ≤ V_{in} ≤ 24 Vdc, I_O = 1.0 A, T_J = 25°C 5.0 mA ≤ I_O ≤ 1.0 A	ΔI_B	 – – –	 – – –	 0.8 0.8 0.5	mA
Ripple Rejection 11.5 Vdc ≤ V_{in} ≤ 21.5 Vdc, f = 120 Hz, I_O = 500 mA	RR	56	61	–	dB
Dropout Voltage (I_O = 1.0 A, T_J = 25°C)	V_I _ V_O		2.0		Vdc
Output Noise Voltage (T_A = 25°C) 10 Hz ≤ f ≤ 100 kHz	Vn	–	10	–	μV/V_O
Output Resistance f = 1.0 kHz	r_O	–	1.0	–	mΩ
Short Circuit Current Limit (T_A = 25°C) V_{in} = 35 Vdc	I_{SC}	–	0.2	–	A
Peak Output Current (T_J = 25°C)	I_{max}	–	2.2	–	A
Average Temperature Coefficient of Output Voltage	TCV_O	–	–0.5	–	mV/°C

11. T_{low} = 0°C for MC78XXC, MC78XXAC,
= −40°C for NCV78XX, MC78XXB, MC78XXAB.
12. Load and line regulation are specified at constant junction temperature. Changes in V_O due to heating effects must be taken into account separately. Pulse testing with low duty cycle is used.

Share Feedback
Your Opinion Matters

ELECTRICAL CHARACTERISTICS (V_{in} = 19 V, I_O = 500 mA, T_J = T_{low} to 125°C (Note 13), unless otherwise noted)

Characteristic	Symbol	MC7812B/NCV7812B			MC7812C			Unit
		Min	Typ	Max	Min	Typ	Max	
Output Voltage (T_J = 25°C)	V_O	11.5	12	12.5	11.5	12	12.5	Vdc
Output Voltage (5.0 mA ≤ I_O ≤ 1.0 A, P_D ≤ 15 W) 14.5 Vdc ≤ V_{in} ≤ 27 Vdc 15.5 Vdc ≤ V_{in} ≤ 27 Vdc	V_O	 – 11.4	 – 12	 – 12.6	 11.4 –	 12 –	 12.6 –	Vdc
Line Regulation, T_J = 25°C (Note 14) 14.5 Vdc ≤ V_{in} ≤ 30 Vdc 16 Vdc ≤ V_{in} ≤ 22 Vdc 14.8 Vdc ≤ V_{in} ≤ 27 Vdc, I_O = 1.0 A	Reg_{line}	 – – –	 7.5 2.2 –	 240 120 –	 – – –	 3.8 0.3 –	 24 24 48	mV
Load Regulation, T_J = 25°C (Note 14) 5.0 mA ≤ I_O ≤ 1.5 A	Reg_{load}	 –	 1.6	 240	 –	 8.1	 60	mV
Quiescent Current	I_B	–	3.4	8.0	–	3.4	6.5	mA
Quiescent Current Change 14.5 Vdc ≤ V_{in} ≤ 30 Vdc, I_O = 1.0 A, T_J = 25°C 15 Vdc ≤ V_{in} ≤ 30 Vdc 5.0 mA ≤ I_O ≤ 1.0 A	ΔI_B	 – – –	 – – –	 – 1.0 0.5	 – – –	 – – –	 0.7 0.8 0.5	mA
Ripple Rejection 15 Vdc ≤ V_{in} ≤ 25 Vdc, f = 120 Hz	RR	 –	 60	 –	 55	 60	 –	dB
Dropout Voltage (I_O = 1.0 A, T_J = 25°C)	$V_I - V_O$	–	2.0	–	–	2.0	–	Vdc
Output Noise Voltage (T_A = 25°C) 10 Hz ≤ f ≤ 100 kHz	V_n	 –	 10	 –	 –	 10	 –	$\mu V/V_O$
Output Resistance f = 1.0 kHz	r_O	–	1.1	–	–	1.1	–	mΩ
Short Circuit Current Limit (T_A = 25°C) V_{in} = 35 Vdc	I_{SC}	 –	 0.2	 –	 –	 0.2	 –	A
Peak Output Current (T_J = 25°C)	I_{max}	–	2.2	–	–	2.2	–	A
Average Temperature Coefficient of Output Voltage	TCV_O	–	–0.8	–	–	–0.8	–	mV/°C

13. T_{low} = 0°C for MC78XXC, MC78XXAC,
= −40°C for NCV78XX, MC78XXB, MC78XXAB, and MC78XXAEB
14. Load and line regulation are specified at constant junction temperature. Changes in V_O due to heating effects must be taken into account separately. Pulse testing with low duty cycle is used.

Share Feedback
Your Opinion Matters

ELECTRICAL CHARACTERISTICS (V_{in} = 19 V, I_O = 1.0 A, T_J = T_{low} to 125°C (Note 15), unless otherwise noted)

Characteristic	Symbol	MC7812AB/MC7812AC/NCV7812AB			Unit
		Min	Typ	Max	
Output Voltage (T_J = 25°C)	V_O	11.75	12	12.25	Vdc
Output Voltage (5.0 mA ≤ I_O ≤ 1.0 A, P_D ≤ 15 W) 14.8 Vdc ≤ V_{in} ≤ 27 Vdc	V_O	11.5	12	12.5	Vdc
Line Regulation (Note 16) 14.8 Vdc ≤ V_{in} ≤ 30 Vdc, I_O = 500 mA 16 Vdc ≤ V_{in} ≤ 22 Vdc, I_O = 1.0 A 14.5 Vdc ≤ V_{in} ≤ 27 Vdc, T_J = 25°C	Reg_{line}	 – – –	 3.8 2.2 6.0	 18 20 120	mV
Load Regulation (Note 16) 5.0 mA ≤ I_O ≤ 1.5 A, T_J = 25°C 5.0 mA ≤ I_O ≤ 1.0 A	Reg_{load}	 – –	 – –	 25 25	mV
Quiescent Current	I_B	–	3.4	6.0	mA
Quiescent Current Change 15 Vdc ≤ V_{in} ≤ 30 Vdc, I_O = 500 mA 14.8 Vdc ≤ V_{in} ≤ 27 Vdc, T_J = 25°C 5.0 mA ≤ I_O ≤ 1.0 A, T_J = 25°C	ΔI_B	 – – –	 – – –	 0.8 0.8 0.5	mA
Ripple Rejection 15 Vdc ≤ V_{in} ≤ 25 Vdc, f = 120 Hz, I_O = 500 mA	RR	55	60	–	dB
Dropout Voltage (I_O = 1.0 A, T_J = 25°C)	$V_I - V_O$	–	2.0	–	Vdc
Output Noise Voltage (T_A = 25°C) 10 Hz ≤ f ≤ 100 kHz	V_n	–	10	–	μV/V_O
Output Resistance (f = 1.0 kHz)	r_O	–	1.1	–	mΩ
Short Circuit Current Limit (T_A = 25°C) V_{in} = 35 Vdc	I_{SC}	–	0.2	–	A
Peak Output Current (T_J = 25°C)	I_{max}	–	2.2	–	A
Average Temperature Coefficient of Output Voltage	TCV_O	–	−0.8	–	mV/°C

15. T_{low} = 0°C for MC78XXC, MC78XXAC,
= −40°C for NCV78XX, MC78XXB, MC78XXAB, and MC78XXAEB
16. Load and line regulation are specified at constant junction temperature. Changes in V_O due to heating effects must be taken into account separately. Pulse testing with low duty cycle is used.

Share Feedback
Your Opinion Matters

ELECTRICAL CHARACTERISTICS (V_{in} = 23 V, I_O = 500 mA, T_J = T_{low} to 125°C (Note 17), unless otherwise noted)

Characteristic	Symbol	MC7815B/NCV7815B			MC7815C			Unit
		Min	Typ	Max	Min	Typ	Max	
Output Voltage (T_J = 25°C)	V_O	14.4	15	15.6	14.4	15	15.6	Vdc
Output Voltage (5.0 mA ≤ I_O ≤ 1.0 A, P_D ≤ 15 W) 17.5 Vdc ≤ V_{in} ≤ 30 Vdc 18.5 Vdc ≤ V_{in} ≤ 30 Vdc	V_O	 – 14.25	 – 15	 – 15.75	 14.25 –	 15 –	 15.75 –	Vdc
Line Regulation, T_J = 25°C (Note 18) 17.9 Vdc ≤ V_{in} ≤ 30 Vdc 20 Vdc ≤ V_{in} ≤ 26 Vdc	Reg_{line}	 – –	 8.5 3.0	 300 150	 – –	 8.5 3.0	 30 28	mV
Load Regulation, T_J = 25°C (Note 18) 5.0 mA ≤ I_O ≤ 1.5 A	Reg_{load}	 –	 1.8	 300	 –	 1.8	 55	mV
Quiescent Current	I_B	–	3.5	8.0	–	3.5	6.5	mA
Quiescent Current Change 17.5 Vdc ≤ V_{in} ≤ 30 Vdc 17.5 Vdc ≤ V_{in} ≤ 30 Vdc, I_O = 1.0 A, T_J = 25°C 5.0 mA ≤ I_O ≤ 1.0 A	ΔI_B	 – – –	 – – –	 – 1.0 0.5	 – – –	 – – –	 0.8 0.7 0.5	mA
Ripple Rejection 18.5 Vdc ≤ V_{in} ≤ 28.5 Vdc, f = 120 Hz	RR	 –	 58	 –	 54	 58	 –	dB
Dropout Voltage (I_O = 1.0 A, T_J = 25°C)	$V_I - V_O$	–	2.0	–	–	2.0	–	Vdc
Output Noise Voltage (T_A = 25°C) 10 Hz ≤ f ≤ 100 kHz	V_n	 –	 10	 –	 –	 10	 –	$\mu V/V_O$
Output Resistance f = 1.0 kHz	r_O	–	1.2	–	–	1.2	–	mΩ
Short Circuit Current Limit (T_A = 25°C) V_{in} = 35 Vdc	I_{SC}	 –	 0.2	 –	 –	 0.2	 –	A
Peak Output Current (T_J = 25°C)	I_{max}	–	2.2	–	–	2.2	–	A
Average Temperature Coefficient of Output Voltage	TCV_O	–	–1.0	–	–	–1.0	–	mV/°C

17. T_{low} = 0°C for MC78XXC, MC78XXAC,
= −40°C for NCV78XX, MC78XXB, MC78XXAB, and MC78XXAEB
18. Load and line regulation are specified at constant junction temperature. Changes in V_O due to heating effects must be taken into account separately. Pulse testing with low duty cycle is used.

Share Feedback
Your Opinion Matters

ELECTRICAL CHARACTERISTICS (V_{in} = 23 V, I_O = 1.0 A, T_J = T_{low} to 125°C (Note 19), unless otherwise noted)

Characteristic	Symbol	MC7815AB/MC7815AC			Unit
		Min	Typ	Max	
Output Voltage (T_J = 25°C)	V_O	14.7	15	15.3	Vdc
Output Voltage (5.0 mA ≤ I_O ≤ 1.0 A, P_D ≤ 15 W) 17.9 Vdc ≤ V_{in} ≤ 30 Vdc	V_O	14.4	15	15.6	Vdc
Line Regulation (Note 20) 17.9 Vdc ≤ V_{in} ≤ 30 Vdc, I_O = 500 mA 20 Vdc ≤ V_{in} ≤ 26 Vdc 17.5 Vdc ≤ V_{in} ≤ 30 Vdc, I_O = 1.0 A, T_J = 25°C	Reg_{line}	 – – –	 8.5 3.0 7.0	 20 22 20	mV
Load Regulation (Note 20) 5.0 mA ≤ I_O ≤ 1.5 A, T_J = 25°C 5.0 mA ≤ I_O ≤ 1.0 A 250 mA ≤ I_O ≤ 750 mA	Reg_{load}	 – – –	 1.8 1.5 1.2	 25 25 15	mV
Quiescent Current	I_B	–	3.5	6.0	mA
Quiescent Current Change 17.5 Vdc ≤ V_{in} ≤ 30 Vdc, I_O = 500 mA 17.5 Vdc ≤ V_{in} ≤ 30 Vdc, I_O = 1.0 A, T_J = 25°C 5.0 mA ≤ I_O ≤ 1.0 A	ΔI_B	 – – –	 – – –	 0.8 0.8 0.5	mA
Ripple Rejection 18.5 Vdc ≤ V_{in} ≤ 28.5 Vdc, f = 120 Hz, I_O = 500 mA	RR	60	80	–	dB
Dropout Voltage (I_O = 1.0 A, T_J = 25°C)	$V_I - V_O$	–	2.0	–	Vdc
Output Noise Voltage (T_A = 25°C) 10 Hz ≤ f ≤ 100 kHz	V_n	–	10	–	μV/V_O
Output Resistance f = 1.0 kHz	r_O	–	1.2	–	mΩ
Short Circuit Current Limit (T_A = 25°C) V_{in} = 35 Vdc	I_{SC}	–	0.2	–	A
Peak Output Current (T_J = 25°C)	I_{max}	–	2.2	–	A
Average Temperature Coefficient of Output Voltage	TCV_O	–	–1.0	–	mV/°C

19. T_{low} = 0°C for MC78XXC, MC78XXAC,
= −40°C for NCV78XX, MC78XXB, MC78XXAB, and MC78XXAEB
20. Load and line regulation are specified at constant junction temperature. Changes in V_O due to heating effects must be taken into account separately. Pulse testing with low duty cycle is used.

Share Feedback
Your Opinion Matters

ELECTRICAL CHARACTERISTICS (V_{in} = 27 V, I_O = 500 mA, T_J = T_{low} to 125°C (Note 21), unless otherwise noted)

Characteristic	Symbol	MC7818B			MC7818C			Unit
		Min	Typ	Max	Min	Typ	Max	
Output Voltage (T_J = 25°C)	V_O	17.3	18	18.7	17.3	18	18.7	Vdc
Output Voltage (5.0 mA ≤ I_O ≤ 1.0 A, P_D ≤ 15 W) 21 Vdc ≤ V_{in} ≤ 33 Vdc 22 Vdc ≤ V_{in} ≤ 33 Vdc	V_O	 – 17.1	 – 18	 – 18.9	 17.1 –	 18 –	 18.9 –	Vdc
Line Regulation, (Note 22) 21 Vdc ≤ V_{in} ≤ 33 Vdc 24 Vdc ≤ V_{in} ≤ 30 Vdc	Reg_{line}	 – –	 9.5 3.2	 360 180	 – –	 9.5 3.2	 50 25	mV
Load Regulation, (Note 22) 5.0 mA ≤ I_O ≤ 1.5 A	Reg_{load}	 –	 2.0	 360	 –	 2.0	 55	mV
Quiescent Current	I_B	–	3.5	8.0	–	3.5	6.5	mA
Quiescent Current Change 21 Vdc ≤ V_{in} ≤ 33 Vdc 5.0 mA ≤ I_O ≤ 1.0 A	ΔI_B	 – –	 – –	 – 0.5	 – –	 – –	 1.0 0.5	mA
Ripple Rejection 22 Vdc ≤ V_{in} ≤ 33 Vdc, f = 120 Hz	RR	 –	 57	 –	 53	 57	 –	dB
Dropout Voltage (I_O = 1.0 A, T_J = 25°C)	$V_{il} - V_O$	–	2.0	–	–	2.0	–	Vdc
Output Noise Voltage (T_A = 25°C) 10 Hz ≤ f ≤ 100 kHz	V_n	 –	 10	 –	 –	 10	 –	$\mu V/V_O$
Output Resistance f = 1.0 kHz	r_O	–	1.3	–	–	1.3	–	mΩ
Short Circuit Current Limit (T_A = 25°C) V_{in} = 35 Vdc	I_{SC}	 –	 0.2	 –	 –	 0.2	 –	A
Peak Output Current (T_J = 25°C)	I_{max}	–	2.2	–	–	2.2	–	A
Average Temperature Coefficient of Output Voltage	TCV_O	–	–1.5	–	–	–1.5	–	mV/°C

21. T_{low} = 0°C for MC78XXC, MC78XXAC,
= −40°C for NCV78XX, MC78XXB, MC78XXAB, and MC78XXAEB
22. Load and line regulation are specified at constant junction temperature. Changes in V_O due to heating effects must be taken into account separately. Pulse testing with low duty cycle is used.

Share Feedback
Your Opinion Matters

ELECTRICAL CHARACTERISTICS (V_{in} = 27 V, I_O = 1.0 A, T_J = T_{low} to 125°C (Note 23), unless otherwise noted)

Characteristic	Symbol	MC7818AC			Unit
		Min	Typ	Max	
Output Voltage (T_J = 25°C)	V_O	17.64	18	18.36	Vdc
Output Voltage (5.0 mA ≤ I_O ≤ 1.0 A, P_D ≤ 15 W) 21 Vdc ≤ V_{in} ≤ 33 Vdc	V_O	17.3	18	18.7	Vdc
Line Regulation (Note 24) 21 Vdc ≤ V_{in} ≤ 33 Vdc, I_O = 500 mA 24 Vdc ≤ V_{in} ≤ 30 Vdc, I_O = 1.0 A 24 Vdc ≤ V_{in} ≤ 30 Vdc, I_O = 1.0 A, T_J = 25°C 20.6 Vdc ≤ V_{in} ≤ 33 Vdc, I_O = 1.0 A, T_J = 25°C	Reg_{line}	 – – – –	 9.5 3.2 3.2 8.0	 22 25 10.5 22	mV
Load Regulation (Note 24) 5.0 mA ≤ I_O ≤ 1.5 A, T_J = 25°C 5.0 mA ≤ I_O ≤ 1.0 A 250 mA ≤ I_O ≤ 750 mA	Reg_{load}	 – – –	 2.0 1.8 1.5	 25 25 15	mV
Quiescent Current	I_B	–	3.5	6.0	mA
Quiescent Current Change 21 Vdc ≤ V_{in} ≤ 33 Vdc, I_O = 500 mA 21.5 Vdc ≤ V_{in} ≤ 30 Vdc, T_J = 25°C 5.0 mA ≤ I_O ≤ 1.0 A	ΔI_B	 – – –	 – – –	 0.8 0.8 0.5	mA
Ripple Rejection 22 Vdc ≤ V_{in} ≤ 32 Vdc, f = 120 Hz, I_O = 500 mA	RR	53	57	–	dB
Dropout Voltage (I_O = 1.0 A, T_J = 25°C)	$V_I - V_O$	–	2.0	–	Vdc
Output Noise Voltage (T_A = 25°C) 10 Hz ≤ f ≤ 100 kHz	V_n	–	10	–	μV/V_O
Output Resistance f = 1.0 kHz	r_O	–	1.3	–	mΩ
Short Circuit Current Limit (T_A = 25°C) V_{in} = 35 Vdc	I_{SC}	–	0.2	–	A
Peak Output Current (T_J = 25°C)	I_{max}	–	2.2	–	A
Average Temperature Coefficient of Output Voltage	TCV_O	–	–1.5	–	mV/°C

23. T_{low} = 0°C for MC78XXC, MC78XXAC,
= −40°C for NCV78XX, MC78XXB, MC78XXAB, and MC78XXAEB
24. Load and line regulation are specified at constant junction temperature. Changes in V_O due to heating effects must be taken into account separately. Pulse testing with low duty cycle is used.

Share Feedback
Your Opinion Matters

ELECTRICAL CHARACTERISTICS (V_{in} = 33 V, I_O = 500 mA, T_J = T_{low} to 125°C (Note 25), unless otherwise noted)

Characteristic	Symbol	MC7824B			MC7824C			Unit
		Min	Typ	Max	Min	Typ	Max	
Output Voltage (T_J = 25°C)	V_O	23	24	25	23	24	25	Vdc
Output Voltage (5.0 mA ≤ I_O ≤ 1.0 A, P_D ≤ 15 W) 27 Vdc ≤ V_{in} ≤ 38 Vdc 28 Vdc ≤ V_{in} ≤ 38 Vdc	V_O	 – 22.8	 – 24	 – 25.2	 22.8 –	 24 –	 25.2 –	Vdc
Line Regulation, (Note 26) 27 Vdc ≤ V_{in} ≤ 38 Vdc 30 Vdc ≤ V_{in} ≤ 36 Vdc	Reg_{line}	 – –	 11.5 3.8	 480 240	 – –	 2.7 2.7	 60 48	mV
Load Regulation, (Note 26) 5.0 mA ≤ I_O ≤ 1.5 A	Reg_{load}	 –	 2.1	 480	 –	 4.4	 65	mV
Quiescent Current	I_B	–	3.6	8.0	–	3.6	6.5	mA
Quiescent Current Change 27 Vdc ≤ V_{in} ≤ 38 Vdc 5.0 mA ≤ I_O ≤ 1.0 A	ΔI_B	 – –	 – –	 – 0.5	 – –	 – –	 1.0 0.5	mA
Ripple Rejection 28 Vdc ≤ V_{in} ≤ 38 Vdc, f = 120 Hz	RR	 –	 54	 –	 50	 54	 –	dB
Dropout Voltage (I_O = 1.0 A, T_J = 25°C)	$V_I - V_O$	–	2.0	–	–	2.0	–	Vdc
Output Noise Voltage (T_A = 25°C) 10 Hz ≤ f ≤ 100 kHz	V_n	 –	 10	 –	 –	 10	 –	μV/V_O
Output Resistance f = 1.0 kHz	r_O	–	1.4	–	–	1.4	–	mΩ
Short Circuit Current Limit (T_A = 25°C) V_{in} = 35 Vdc	I_{SC}	 –	 0.2	 –	 –	 0.2	 –	A
Peak Output Current (T_J = 25°C)	I_{max}	–	2.2	–	–	2.2	–	A
Average Temperature Coefficient of Output Voltage	TCV_O	–	–2.0	–	–	–2.0	–	mV/°C

25. T_{low} = 0°C for MC78XXC, MC78XXAC,
= −40°C for NCV78XX, MC78XXB, MC78XXAB, and MC78XXAEB
26. Load and line regulation are specified at constant junction temperature. Changes in V_O due to heating effects must be taken into account separately. Pulse testing with low duty cycle is used.

Share Feedback
Your Opinion Matters

ELECTRICAL CHARACTERISTICS (V_{in} = 33 V, I_O = 1.0 A, T_J = T_{low} to 125°C (Note 27), unless otherwise noted)

Characteristic	Symbol	MC7824AC			Unit
		Min	Typ	Max	
Output Voltage (T_J = 25°C)	V_O	23.5	24	24.5	Vdc
Output Voltage (5.0 mA ≤ I_O ≤ 1.0 A, P_D ≤ 15 W) 27.3 Vdc ≤ V_{in} ≤ 38 Vdc	V_O	23.2	24	25.8	Vdc
Line Regulation (Note 28) 27 Vdc ≤ V_{in} ≤ 38 Vdc, I_O = 500 mA 30 Vdc ≤ V_{in} ≤ 36 Vdc, I_O = 1.0 A 30 Vdc ≤ V_{in} ≤ 36 Vdc, T_J = 25°C 26.7 Vdc ≤ V_{in} ≤ 38 Vdc, I_O = 1.0 A, T_J = 25°C	Reg_{line}	 – – – –	 11.5 3.8 3.8 10	 25 28 12 25	mV
Load Regulation (Note 28) 5.0 mA ≤ I_O ≤ 1.5 A, T_J = 25°C 5.0 mA ≤ I_O ≤ 1.0 A 250 mA ≤ I_O ≤ 750 mA	Reg_{load}	 – – –	 2.1 2.0 1.8	 15 25 15	mV
Quiescent Current	I_B	–	3.6	6.0	mA
Quiescent Current Change 27.3 Vdc ≤ V_{in} ≤ 38 Vdc, I_O = 500 mA 27 Vdc ≤ V_{in} ≤ 38 Vdc, T_J = 25°C 5.0 mA ≤ I_O ≤ 1.0 A	ΔI_B	 – – –	 – – –	 0.8 0.8 0.5	mA
Ripple Rejection 28 Vdc ≤ V_{in} ≤ 38 Vdc, f = 120 Hz, I_O = 500 mA	RR	45	54	–	dB
Dropout Voltage (I_O = 1.0 A, T_J = 25°C)	$V_I - V_O$	–	2.0	–	Vdc
Output Noise Voltage (T_A = 25°C) 10 Hz ≤ f ≤ 100 kHz	V_n	–	10	–	μV/V_O
Output Resistance (f = 1.0 kHz)	r_O	–	1.4	–	mΩ
Short Circuit Current Limit (T_A = 25°C) V_{in} = 35 Vdc	I_{SC}	–	0.2	–	A
Peak Output Current (T_J = 25°C)	I_{max}	–	2.2	–	A
Average Temperature Coefficient of Output Voltage	TCV_O	–	–2.0	–	mV/°C

27. T_{low} = 0°C for MC78XXC, MC78XXAC,
= −40°C for NCV78XX, MC78XXB, MC78XXAB, and MC78XXAEB
28. Load and line regulation are specified at constant junction temperature. Changes in V_O due to heating effects must be taken into account separately. Pulse testing with low duty cycle is used.

Share Feedback
Your Opinion Matters



Figure 2. Peak Output Current as a Function of Input/Output Differential Voltage (MC78XXC, AC, B)



Figure 3. Ripple Rejection as a Function of Output Voltages (MC78XXC, AC, B)



Figure 4. Ripple Rejection as a Function of Frequency (MC78XXC, AC, B)



Figure 5. Output Voltage as a Function of Junction Temperature (MC7805C, AC, B)



Figure 6. Output Voltage as a Function of Junction Temperature (MC7808AE)

Share Feedback
Your Opinion Matters



Figure 7. Output Impedance as a Function of Output Voltage (MC78XXC, AC, B)



Figure 8. Quiescent Current as a Function of Temperature (MC78XXC, AC, B)

Share Feedback
Your Opinion Matters

APPLICATIONS INFORMATION

Design Considerations

The MC7800 Series of fixed voltage regulators are designed with Thermal Overload Protection that shuts down the circuit when subjected to an excessive power overload condition, Internal Short Circuit Protection that limits the maximum current the circuit will pass, and Output Transistor Safe−Area Compensation that reduces the output short circuit current as the voltage across the pass transistor is increased.

In many low current applications, compensation capacitors are not required. However, it is recommended that the regulator input be bypassed with a capacitor if the regulator is connected to the power supply filter with long wire lengths, or if the output load capacitance is large. An input bypass capacitor should be selected to provide good high−frequency characteristics to insure stable operation under all load conditions. A 0.33 μF or larger tantalum, mylar, or other capacitor having low internal impedance at high frequencies should be chosen. The bypass capacitor should be mounted with the shortest possible leads directly across the regulators input terminals. Normally good construction techniques should be used to minimize ground loops and lead resistance drops since the regulator has no external sense lead.



The MC7800 regulators can also be used as a current source when connected as above. In order to minimize dissipation the MC7805C is chosen in this application. Resistor R determines the current as follows:

$$I_O = \frac{5.0\ V}{R} + I_B$$

$I_B \cong 3.2$ mA over line and load changes.

For example, a 1.0 A current source would require R to be a 5.0 Ω, 10 W resistor and the output voltage compliance would be the input voltage less 7.0 V.

Figure 9. Current Regulator



The addition of an operational amplifier allows adjustment to higher or intermediate values while retaining regulation characteristics. The minimum voltage obtainable with this arrangement is 2.0 V greater than the regulator voltage.

Figure 10. Adjustable Output Regulator



XX = 2 digits of type number indicating voltage.

The MC7800 series can be current boosted with a PNP transistor. The MJ2955 provides current to 5.0 A. Resistor R in conjunction with the V_{BE} of the PNP determines when the pass transistor begins conducting; this circuit is not short circuit proof. Input/output differential voltage minimum is increased by V_{BE} of the pass transistor.

Figure 11. Current Boost Regulator



XX = 2 digits of type number indicating voltage.

The circuit of Figure 11 can be modified to provide supply protection against short circuits by adding a short circuit sense resistor, R_{SC}, and an additional PNP transistor. The current sensing PNP must be able to handle the short circuit current of the three−terminal regulator. Therefore, a four−ampere plastic power transistor is specified.

Figure 12. Short Circuit Protection

Share Feedback
Your Opinion Matters



Figure 13. Worst Case Power Dissipation versus Ambient Temperature (Case 221A)



Figure 14. Input Output Differential as a Function of Junction Temperature (MC78XXC, AC, B)



Figure 15. D²PAK Thermal Resistance and Maximum Power Dissipation versus P.C.B. Copper Length



Figure 16. DPAK Thermal Resistance and Maximum Power Dissipation versus P.C.B. Copper Length

Share Feedback
Your Opinion Matters

DEFINITIONS

Line Regulation – The change in output voltage for a change in the input voltage. The measurement is made under conditions of low dissipation or by using pulse techniques such that the average chip temperature is not significantly affected.

Load Regulation – The change in output voltage for a change in load current at constant chip temperature.

Maximum Power Dissipation – The maximum total device dissipation for which the regulator will operate within specifications.

Quiescent Current – That part of the input current that is not delivered to the load.

Output Noise Voltage – The rms ac voltage at the output, with constant load and no input ripple, measured over a specified frequency range.

Long Term Stability – Output voltage stability under accelerated life test conditions with the maximum rated voltage listed in the devices' electrical characteristics and maximum power dissipation.

ORDERING INFORMATION

Device	Nominal Voltage	Operating Temperature Range	Package	Shipping†
MC7805ABD2TR4G	5.0 V	T_J = −40°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
NCV7805ABD2TR4G*	5.0 V	T_J = −40°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
MC7805ABTG	5.0 V	T_J = −40°C to +125°C	TO−220 (Pb−free)	50 Units /Rail
MC7805ACD2TG	5.0 V	T_J = 0°C to +125°C	D^2PAK (Pb−free)	50 Units /Rail
MC7805ACD2TR4G	5.0 V	T_J = 0°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
MC7805ACTG	5.0 V	T_J = 0°C to +125°C	TO−220 (Pb−free)	50 Units /Rail
MC7805BD2TG	5.0 V	T_J = −40°C to +125°C	D^2PAK (Pb−free)	50 Units /Rail
MC7805BD2TR4G	5.0 V	T_J = −40°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
MC7805BDTG	5.0 V	T_J = −40°C to +125°C	DPAK (Pb−free)	75 Units / Rail
MC7805BDTRKG	5.0 V	T_J = −40°C to +125°C	DPAK (Pb−free)	2500 / Tape & Reel
NCV7805BDTRKG*	5.0 V	T_J = −40°C to +125°C	DPAK (Pb−free)	2500 / Tape & Reel
MC7805BTG	5.0 V	T_J = −40°C to +125°C	TO−220 (Pb−free)	50 Units /Rail
NCV7805BTG*	5.0 V	T_J = −40°C to +125°C	TO−220 (Pb−free)	50 Units /Rail
NCV7805BD2TG*	5.0 V	T_J = −40°C to +125°C	D^2PAK (Pb−free)	50 Units /Rail
NCV7805BD2TR4G*	5.0 V	T_J = −40°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
MC7805CD2TG	5.0 V	T_J = 0°C to +125°C	D^2PAK (Pb−free)	50 Units /Rail
MC7805CD2TR4G	5.0 V	T_J = 0°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
MC7805CDTG	5.0 V	T_J = 0°C to +125°C	DPAK (Pb−free)	75 Units / Rail

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

*NCV devices: T_{low} = −40°C, T_{high} = +125°C. Guaranteed by design. NCV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC−Q100 Qualified and PPAP Capable.

Share Feedback
Your Opinion Matters

ORDERING INFORMATION (continued)

Device	Nominal Voltage	Operating Temperature Range	Package	Shipping†
MC7805CDTRKG	5.0 V	T_J = 0°C to +125°C	DPAK (Pb−free)	2500 / Tape & Reel
MC7805CTG	5.0 V	T_J = 0°C to +125°C	TO−220 (Pb−free)	50 Units /Rail
NCV7808ABD2TR4G*	8.0 V	T_J = −40°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
MC7808AEBTG	8.0 V	T_J = −40°C to +125°C	TO−220 (Pb−free)	50 Units / Rail
NCV7808BD2TR4G*	8.0 V	T_J = −40°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
NCV7808BDTG*	8.0 V	T_J = −40°C to +125°C	DPAK (Pb−free)	75 Units / Rail
NCV7808BDTRKG*	8.0 V	T_J = −40°C to +125°C	DPAK (Pb−free)	2500 / Tape & Reel
NCV7808BTG*	8.0 V	T_J = −40°C to +125°C	TO−220 (Pb−free)	50 Units / Rail
MC7808CDTRKG	8.0 V	T_J = 0°C to +125°C	DPAK (Pb−free)	2500 / Tape & Reel
MC7808CTG	8.0 V	T_J = 0°C to +125°C	TO−220 (Pb−free)	50 Units /Rail
MC7809ABTG	9.0 V	T_J = −40°C to +125°C	TO−220 (Pb−free)	50 Units /Rail
NCV7809BD2TR4G*	9.0 V	T_J = −40°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
NCV7809BTG*	9.0 V	T_J = −40°C to +125°C	TO−220 (Pb−free)	50 Units /Rail
MC7809CTG	9.0 V	T_J = 0°C to +125°C	TO−220 (Pb−free)	50 Units /Rail
MC7812ABD2TR4G	12 V	T_J = −40°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
NCV7812ABTG*	12 V	T_J = −40°C to +125°C	TO−220 (Pb−free)	50 Units / Rail
MC7812ACD2TR4G	12 V	T_J = 0°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
MC7812ACTG	12 V	T_J = 0°C to +125°C	TO−220 (Pb−free)	50 Units /Rail
MC7812BD2TR4G	12 V	T_J = −40°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
NCV7812BD2TR4G*	12 V	T_J = −40°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
MC7812BDTG	12 V	T_J = −40°C to +125°C	DPAK (Pb−free)	75 Units / Rail
MC7812BDTRKG	12 V	T_J = −40°C to +125°C	DPAK (Pb−free)	2500 / Tape & Reel
MC7812BTG	12 V	T_J = −40°C to +125°C	TO−220 (Pb−free)	50 Units / Rail
NCV7812BTG*	12 V	T_J = −40°C to +125°C	TO−220 (Pb−free)	50 Units /Rail

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

*NCV devices: T_{low} = −40°C, T_{high} = +125°C. Guaranteed by design. NCV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC−Q100 Qualified and PPAP Capable.

Share Feedback
Your Opinion Matters

ORDERING INFORMATION (continued)

Device	Nominal Voltage	Operating Temperature Range	Package	Shipping†
MC7812CD2TR4G	12 V	T_J = 0°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
MC7812CDTRKG	12 V	T_J = 0°C to +125°C	DPAK (Pb−free)	2500 / Tape & Reel
MC7812CTG	12 V	T_J = 0°C to +125°C	TO−220 (Pb−free)	50 Units / Rail
MC7815ABD2TR4G	15 V	T_J = −40°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
MC7815ABTG	15 V	T_J = −40°C to +125°C	TO−220 (Pb−free)	50 Units /Rail
MC7815ACTG	15 V	T_J = 0°C to +125°C	TO−220 (Pb−free)	50 Units / Rail
MC7815BD2TR4G	15 V	T_J = −40°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
MC7815BDTRKG	15 V	T_J = −40°C to +125°C	DPAK (Pb−free)	2500 / Tape & Reel
MC7815BTG	15 V	T_J = −40°C to +125°C	TO−220 (Pb−free)	50 Units / Rail
NCV7815BTG*	15 V	T_J = −40°C to +125°C	TO−220 (Pb−free)	50 Units / Rail
MC7815CD2TG	15 V	T_J = 0°C to +125°C	D^2PAK (Pb−free)	50 Units /Rail
MC7815CD2TR4G	15 V	T_J = 0°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
MC7815CDTRKG	15 V	T_J = 0°C to +125°C	DPAK (Pb−free)	2500 / Tape & Reel
MC7815CTG	15 V	T_J = 0°C to +125°C	TO−220 (Pb−free)	50 Units /Rail
MC7818BTG	18 V	T_J = −40°C to +125°C	TO−220 (Pb−free)	50 Units /Rail
MC7818CD2TR4G	18 V	T_J = 0°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
MC7818CTG	18 V	T_J = 0°C to +125°C	TO−220 (Pb−free)	50 Units /Rail
MC7824ACTG	24 V	T_J = 0°C to +125°C	TO−220 (Pb−free)	50 Units /Rail
MC7824BTG	24 V	T_J = −40°C to +125°C	TO−220 (Pb−free)	50 Units /Rail
MC7824CD2TR4G	24 V	T_J = 0°C to +125°C	D^2PAK (Pb−free)	800 / Tape & Reel
MC7824CTG	24 V	T_J = 0°C to +125°C	TO−220 (Pb−free)	50 Units /Rail

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

*NCV devices: T_{low} = −40°C, T_{high} = +125°C. Guaranteed by design. NCV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC−Q100 Qualified and PPAP Capable.

Share Feedback
Your Opinion Matters

MARKING DIAGRAMS



TO−220−3
T SUFFIX
CASE 221A



D^{2}PAK−3
D2T SUFFIX
CASE 936



DPAK−3
DT SUFFIX
CASE 369C

*This marking diagram also applies to NCV78xx family.

xx	= 05, 06, 08, 09, 12, 15, 18, or 24
y	= B or C
A	= Assembly Location
WL, L	= Wafer Lot
Y	= Year
WW	= Work Week
G	= Pb−Free Device

Share Feedback
Your Opinion Matters

TO−220, SINGLE GAUGE

CASE 221AB
ISSUE A

DATE 16 NOV 2010



SCALE 1:1



NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCHES.
3. DIMENSION Z DEFINES A ZONE WHERE ALL BODY AND LEAD IRREGULARITIES ARE ALLOWED.
4. PRODUCT SHIPPED PRIOR TO 2008 HAD DIMENSIONS S = 0.045 − 0.055 INCHES (1.143 − 1.397 MM)

	INCHES		MILLIMETERS	
DIM	MIN	MAX	MIN	MAX
A	0.570	0.620	14.48	15.75
B	0.380	0.405	9.66	10.28
C	0.160	0.190	4.07	4.82
D	0.025	0.035	0.64	0.88
F	0.142	0.147	3.61	3.73
G	0.095	0.105	2.42	2.66
H	0.110	0.155	2.80	3.93
J	0.018	0.025	0.46	0.64
K	0.500	0.562	12.70	14.27
L	0.045	0.060	1.15	1.52
N	0.190	0.210	4.83	5.33
Q	0.100	0.120	2.54	3.04
R	0.080	0.110	2.04	2.79
S	0.020	0.024	0.508	0.61
T	0.235	0.255	5.97	6.47
U	0.000	0.050	0.00	1.27
V	0.045	---	1.15	---
Z	---	0.080	---	2.04

STYLE 1:
PIN 1. BASE
2. COLLECTOR
3. EMITTER
4. COLLECTOR

STYLE 2:
PIN 1. BASE
2. EMITTER
3. COLLECTOR
4. EMITTER

STYLE 3:
PIN 1. CATHODE
2. ANODE
3. GATE
4. ANODE

STYLE 4:
PIN 1. MAIN TERMINAL 1
2. MAIN TERMINAL 2
3. GATE
4. MAIN TERMINAL 2

STYLE 5:
PIN 1. GATE
2. DRAIN
3. SOURCE
4. DRAIN

STYLE 6:
PIN 1. ANODE
2. CATHODE
3. ANODE
4. CATHODE

STYLE 7:
PIN 1. CATHODE
2. ANODE
3. CATHODE
4. ANODE

STYLE 8:
PIN 1. CATHODE
2. ANODE
3. EXTERNAL TRIP/DELAY
4. ANODE

STYLE 9:
PIN 1. GATE
2. COLLECTOR
3. EMITTER
4. COLLECTOR

STYLE 10:
PIN 1. GATE
2. SOURCE
3. DRAIN
4. SOURCE

STYLE 11:
PIN 1. DRAIN
2. SOURCE
3. GATE
4. SOURCE

DOCUMENT NUMBER:	**98AON23085D**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	**TO−220, SINGLE GAUGE**	**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

© Semiconductor Components Industries, LLC, 2006



SCALE 1:1

DPAK3 6.10x6.54x2.28, 2.29P
CASE 369C
ISSUE J

DATE 12 AUG 2025



TOP VIEW



SIDE VIEW

MILLIMETERS			
DIM	MIN	NOM	MAX
A	2.18	2.28	2.38
A1	0.00	---	0.13
b	0.63	0.76	0.89
b2	0.72	0.93	1.14
b3	4.57	5.02	5.46
c	0.46	0.54	0.61
c2	0.46	0.54	0.61
D	5.97	6.10	6.22
E	6.35	6.54	6.73
e	2.29 BSC		
H	9.40	9.91	10.41
L	1.40	1.59	1.78
L1	2.90 REF		
L2	0.51 BSC		
L3	0.89	---	1.27
L4	---	---	1.01
Z	3.93	---	---



BOTTOM VIEW

ALTERNATE CONSTRUCTIONS

NOTES:

1. DIMENSIONING AND TOLERANCING ASME Y14.5M, 2018.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSIONS b3, L3, AND Z.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.15mm PER SIDE.
5. DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
6. DATUMS A AND B ARE DETERMINED AT DATUM PLANE H.
7. OPTIONAL MOLD FEATURE.



DETAIL A
ROTATED 90° CW



RECOMMENDED MOUNTING FOOTPRINT*

*FOR ADDITIONAL INFORMATION ON OUR PB–FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ONSEMI SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

DOCUMENT NUMBER:	**98AON10527D**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	**DPAK3 6.10x6.54x2.28, 2.29P**	**PAGE 1 OF 2**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

DPAK3 6.10x6.54x2.28, 2.29P
CASE 369C
ISSUE J

DATE 12 AUG 2025

GENERIC MARKING DIAGRAM*



IC **Discrete**

XXXXXX	= Device Code
A	= Assembly Location
L	= Wafer Lot
Y	= Year
WW	= Work Week
G	= Pb−Free Package

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, “G” or microdot “▪”, may or may not be present. Some products may not follow the Generic Marking.

STYLE 1:
PIN 1. BASE
2. COLLECTOR
3. EMITTER
4. COLLECTOR

STYLE 2:
PIN 1. GATE
2. DRAIN
3. SOURCE
4. DRAIN

STYLE 3:
PIN 1. ANODE
2. CATHODE
3. ANODE
4. CATHODE

STYLE 4:
PIN 1. CATHODE
2. ANODE
3. GATE
4. ANODE

STYLE 5:
PIN 1. GATE
2. ANODE
3. CATHODE
4. ANODE

STYLE 6:
PIN 1. MT1
2. MT2
3. GATE
4. MT2

STYLE 7:
PIN 1. GATE
2. COLLECTOR
3. EMITTER
4. COLLECTOR

STYLE 8:
PIN 1. N/C
2. CATHODE
3. ANODE
4. CATHODE

STYLE 9:
PIN 1. ANODE
2. CATHODE
3. RESISTOR ADJUST
4. CATHODE

STYLE 10:
PIN 1. CATHODE
2. ANODE
3. CATHODE
4. ANODE

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

© Semiconductor Components Industries, LLC, 2011

D²PAK
CASE 936−03
ISSUE E

DATE 29 SEP 2015



SCALE 1:1







BOTTOM VIEW
OPTIONAL CONSTRUCTIONS

NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCHES.
3. TAB CONTOUR OPTIONAL WITHIN DIMENSIONS A AND K.
4. DIMENSIONS U AND V ESTABLISH A MINIMUM MOUNTING SURFACE FOR TERMINAL 4.
5. DIMENSIONS A AND B DO NOT INCLUDE MOLD FLASH OR GATE PROTRUSIONS. MOLD FLASH AND GATE PROTRUSIONS NOT TO EXCEED 0.025 (0.635) MAXIMUM.
6. SINGLE GAUGE DESIGN WILL BE SHIPPED AFTER FPCN EXPIRATION IN OCTOBER 2011.

	INCHES		MILLIMETERS	
DIM	MIN	MAX	MIN	MAX
A	0.386	0.403	9.804	10.236
B	0.356	0.368	9.042	9.347
C	0.170	0.180	4.318	4.572
D	0.026	0.036	0.660	0.914
E_D	0.045	0.055	1.143	1.397
E_S	0.018	0.026	0.457	0.660
F	0.051 REF		1.295 REF	
G	0.100 BSC		2.540 BSC	
H	0.539	0.579	13.691	14.707
J	0.125 MAX		3.175 MAX	
K	0.050 REF		1.270 REF	
L	0.000	0.010	0.000	0.254
M	0.088	0.102	2.235	2.591
N	0.018	0.026	0.457	0.660
P	0.058	0.078	1.473	1.981
R	0°	8°	0°	8°
S	0.116 REF		2.946 REF	
U	0.200 MIN		5.080 MIN	
V	0.250 MIN		6.350 MIN	

RECOMMENDED SOLDERING FOOTPRINT*



DIMENSIONS: MILLIMETERS

*For additional information on our Pb−Free strategy and soldering details, please download the **onsemi** Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

GENERIC MARKING DIAGRAM*



XXXXXX = Specific Device Code
A = Assembly Location
L = Wafer Lot
Y = Year
WW = Work Week
G = Pb−Free Package

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	**98ASH01005A**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	**D²PAK**	**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales