




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	ECR-15-008603	24JUN2015	KG	DW

NICKEL ALUMINUM BRONZE	3 7.5mm	1-1918931-6
	6.7mm	1-1918931-5
	6.0mm	1-1918931-4
	5.5mm	1-1918931-3
	5.0mm	1-1918931-2
	4.2mm	1-1918931-1
	3.6mm	1-1918931-0
	3.2mm	1918931-9
ALUMINUM	3 7.5mm	1918931-8
	6.7mm	1918931-7
	6.0mm	1918931-6
	5.5mm	1918931-5
	5.0mm	1918931-4
	4.2mm	1918931-3
	3.6mm	1918931-2
	3.2mm	1918931-1
EXTENSION MATERIAL	MAXIMUM CABLE DIAMETER	PART NUMBER

1. PACKAGED LOOSE PIECE.
2. DIMENSIONS ARE FOR REFERENCE ONLY.
- 3

 FOR USE WITH Ø7.5mm BREAKOUT CABLE WITH Ø2.15mm MAXIMUM JACKETED SUBUNITS.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
AS LISTED
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH
HARD ANODIZE (AL ONLY)

DWN
K. GLATFELTER
27OCT2006

CHK
D. WERTMAN
02JUN2008

APVD
D. WERTMAN
02JUN2008

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

Customer Drawing

TE Connectivity

NAME
CABLE ADAPTER KIT, PLUG, PRO BEAM JR.

SIZE
A200779

CAGE CODE
C-1918931

DRAWING NO
-

RESTRICTED TO
-

SCALE
3:1

SHEET
1

OF
1

REV
C

1471-9 (3/13)