

In most applications, a signal booster ([B120-000-SL](#)) should be used with this cable to ensure a signal strong enough for your display. An alternate solution is to use a Tripp Lite DVI over Cat5 Extender ([B140-101X](#)) in place of a 75 ft. DVI cable and signal booster.

DVI Single Link Cable, Digital TMDS Monitor Cable (DVI-D M/M) 75-ft.

MODEL NUMBER: **P561-075**



Highlights

- For use with Single Link TMDS specified equipment
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 1920 x 1200
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection

System Requirements

- DVI monitor and computer

Package Includes

- 75-ft. DVI Single Link TMDS Cable (DVI-D M/M)

Description

Tripp Lite's 75-ft. DVI Single Link TMDS cable delivers the high performance, high bandwidth needed for today's digital video displays. Gold plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Use in conjunction with DVI video cards that are specified as Single Link. Both DVI connectors are molded, have integral strain relief for long life reliability, and ferrite collars to drain off extraneous electrical interference. In most applications, a signal booster ([B120-000-SL](#)) will need to be used with this cable to ensure a signal strong enough for your display.

Features



- For use with Single Link TMDS specified equipment
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 1920 x 1200
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- In most applications, a signal booster ([B120-000-SL](#)) will need to be used with this cable to ensure a signal strong enough for your display

Specifications

OVERVIEW	
Intended Application	Connecting Peripherals
Cable Type	DVI
Model Type	DVI



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT	
Cable Length (ft.)	75
Cable Length (m)	22.86
UPC ASSIGNMENT	
Unit Carton UPC#	037332168580
PHYSICAL	
Color	Black
Style	DVI
CONNECTIONS	
Connector A	 DVI-D SINGLE LINK (MALE)
Connector B	 DVI-D SINGLE LINK (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

Related Items

Optional Products

Model Number	Description	Qty.
P561-006	6-ft. DVI Single Link TMDS Cable (DVI-D M/M)	1
P561-010	10-ft. DVI Single Link TMDS Cable (DVI-D M/M)	1
P561-050	50-ft. DVI Single Link TMDS Cable (DVI-D M/M)	1
P561-100	100-ft. DVI Single Link TMDS Cable (DVI-D M/M)	1
B120-000-SL	DVI Single Link Signal Extender (DVI F/F)	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at:
<http://www.tripplite.com/sku/P561-075>.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com