




.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE



-X0XX
HEADER WITHOUT LATCH EJECTOR



-X2XX
HEADER WITH SHORT LATCH EJECTOR
FOR 3M SOCKETS WITHOUT STRAIN RELIEF



-X3XX
HEADER WITH LONG LATCH EJECTOR
FOR 3M SOCKETS WITH STRAIN RELIEF

X3XXX-XXXXXX

3M PART NUMBER:
(SEE TABLE 1)

PLATING:
RB = 30μ" [0.76μm] GOLD AND 200μ" [5.08μm] MATTE TIN
(APP. E1 & C1 APPLY)
UB = 30μ" [0.76μm] GOLD AND 200μ" [5.08μm]
TIN LEAD (APP. E3 & C2 APPLY)

```

-TAIL:
O2 = FOR .062 [1.57] THICK BOARD
O3 = FOR .094 TO .125 [2.39 TO 3.18] THICK BOARD
K2 = KINKED FOR .062 [1.57] THICK BOARD

```

LATCH/EJECTOR SYSTEM:
0 = NO LATCH/EJECTOR INSTALLED
2 = SHORT ROLL PIN LATCH/EJECTORS
3 = LONG ROLL PIN LATCH/EJECTORS

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

- * MILITARY (WITH 3M'S N3518 POLARIZING KEY) AND CENTERBUMP POLARIZATION.
- * OPTIONAL EJECTOR LATCHES.
- * MOUNTING HOLES FOR SECURING HEADER TO BOARD.
- * OPTIONAL POLARIZING POSTS AVAILABLE.
- * HIGH TEMPERATURE INSULATOR SUITABLE FOR "NO LEAD" SOLDERING OPERATIONS.
- * SUITABLE FOR REFLOW SOLDERING USING "PASTE IN HOLE" TECHNIQUES.
- * SOLDER TAIL OPTION.

2 PHYSICAL :

```

INSULATOR:
  MATERIAL: GLASS FILLED POLYESTER (PCT)
FLAMMABILITY: UL94V-0
  COLOR: BLACK
  CONTACT:
    MATERIAL: COPPER ALLOY
    PLATING:
      UNDER PLATING: 100μ" [ 2.54μm ] NICKEL-OVERALL
      WIPING AREA: 30μ" [ 0.76μm ] AVG. GOLD
      SOLDER TAILS: TIN LEAD OR MATTE TIN (SEE ORDERING INFORMATION)
      MARKINGS: 3M LOGO, PART IDENTIFICATION NUMBER AND ORIENTATION TRIANGLE

```


2 ELECTRICAL :

CURRENT RATING: 5.00A, 1 CONTACT POWERED
3.00A, 6 CONTACTS POWERED
1.75A, ALL CONTACTS POWERED
RATING CONDITIONS: EIA-364-070 METHOD 2, 30°C MAXIMUM
TEMPERATURE RISE, 20% DERATED. REFERENCE APPROPRIATE
3M PRODUCT SPECIFICATION FOR DETAILED CURRENT DERATING
CURVES.
INSULATION RESISTANCE: $>1 \times 10^9 \Omega$ AT 500 V_{DC}
WITHSTANDING VOLTAGE: 1,000V_{RMS} AT SEA LEVEL

2 ENVIRONMENTAL :

TEMPERATURE RATING: -55°C TO 105°C
PROCESS RATING: 260°C, PER J-STD-020C, SINGLE PASS
MOISTURE SENSITIVITY LEVEL: 1 (PER J-STD-020C)

DIMENSIONS: INCHES [MM]
[MM] IS REF. ONLY

DESIGN REFERENCE		NEXT ASSEMBLY		REV	ECO	ISSUE DATE AND DESCRIPTION		DRFT	CHKD
ACCESS CODES				DRFT	CASTIGLIONE		DATE	JUL 25, 2014	
				CHKD			DATE		
						APPR	R. SCHERER	DATE	SEP 05, 2014
DIVISION		DIVISION CODE		3M 3M Center St. Paul, MN 55144 © 3M COPYRIGHT 2015 This document and the information it contains are 3M property and may not be reproduced or further distributed without written permission or used or disclosed other than for 3M authorized purposes. All rights reserved.					
Interconnect Solutions		EMSD							
DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED							
SCALE $\frac{2}{1}$									
		INCHES		TITLE HEADER, 4-WALL, 100 X 100 LATCH/EJECTOR, STRAIGHT & RA					
THIRD ANGLE PROJECTION		.0 ± .00 ± .01 .000 ± .005 .0000 ±							
INTERPRET PER ASME Y14.5 - 2009		MILLIMETERS							
☒ MAX. SURFACE ROUGHNESS ☐ MAX. SURFACES ☒ MARKED ONLY		.00 ± .13 .0 ± .000 ±							
		ANGLES		CAGE NUMBER		SIZE		DRAWING NO.	
				D		D78-100-0772-3		REV. S	
				MODEL		3000 SERIES		DET. ☐ LISTS ☒ YES ☒ NO SHT 1 OF 4	

cUL[®] US
UL FILE NO: E68080

1. REGULATORY INFORMATION:
ROHS COMPLIANT. SEE THE
REGULATORY INFORMATION
APPENDIX (RIA) IN THE
"ROHS COMPLIANCE" SECTION
OF WWW.3MCONNECTORS.COM FOR
COMPLIANCE INFORMATION.

2 IN THE EVENT OF CONFLICT
BETWEEN THIS DATA AND THAT
CONTAINED IN THE PRODUCT
SPECIFICATION, THE PRODUCT
SPECIFICATION TAKES PRECEDENT

3 NOTCHES A & C WILL ACCOMODATE
3M POLARIZING KEY: N3518.

4 MOUNTING HARDWARE:
FROM SOLDER SIDE OF PC BOARD
USE #4-24 THREAD CUTTING SCREW
(3M PART #3341-5) WITH
Ø.116 [2.95] MOUNTING HOLE.
FOR RIGHT ANGLE VERSION ONLY:
#2-56 BOLT AND NUT (3M PART
#3341-6) WITH Ø.106 [2.69]
MOUNTING HOLE MAY BE USED.

5 THE RECOMMENDED PCB HOLE SIZE
FOR THE KINKED TAIL POSITIONS
ON THE .112 SOLDER TAIL
CONNECTOR IS $\varnothing .035 \pm .002$.
(SEE K2 VERSION).

Imaged: S.1 3/6/2015 12:54 PM UTC-06:00

3M™ FOUR-WALL HEADER, 3000 SERIES
.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE





TABLE 1							
PIN QTY.	3M PART NUMBER	DIM. "A"	DIM. "B"	DIM. "C"	DIM. "D"	POLARIZING NOTCHES	PIN QTY.
06	3869	1.06 [27.0]	.905 [22.99]	.665 [16.89]	.51 [12.9]	B*	06
08	3889	1.16 [29.5]	1.005 [25.53]	.765 [19.43]	.61 [15.5]	B*	08
10	3793	1.26 [32.1]	1.105 [28.04]	.865 [21.97]	.71 [18.0]	BC	10
14	3314	1.46 [37.2]	1.305 [33.12]	1.065 [27.05]	.91 [23.1]	BC	14
16	3408	1.56 [39.7]	1.405 [35.66]	1.165 [29.59]	1.01 [25.6]	ABC	16
20	3428	1.76 [44.8]	1.604 [40.74]	1.365 [34.67]	1.21 [30.7]	ABC	20
24	3627	1.96 [49.9]	1.805 [45.82]	1.565 [39.75]	1.41 [35.8]	ABC	24
26	3429	2.06 [52.4]	1.905 [48.36]	1.665 [42.29]	1.51 [38.3]	ABC	26
30	3440	2.26 [57.5]	2.105 [53.44]	1.865 [47.37]	1.71 [43.4]	ABC	30
34	3431	2.46 [62.6]	2.305 [58.52]	2.065 [52.45]	1.91 [48.5]	ABC	34
40	3432	2.76 [70.2]	2.605 [66.14]	2.365 [60.07]	2.21 [56.1]	ABC	40
50	3433	3.26 [82.9]	3.105 [78.84]	2.865 [72.77]	2.71 [68.8]	ABC	50
60	3372	3.76 [95.6]	3.605 [91.54]	3.365 [85.47]	3.21 [81.5]	ABC	60
64	3764	3.96 [100.7]	3.805 [96.62]	3.565 [90.55]	3.41 [86.6]	ABC	64


* AVAILABLE WITHOUT CENTER NOTCH B. CONTACT 3M

TABLE 2						
3M PART NUMBER SUFFIX	CONTACT TAIL	DIM. "E"	PIN CROSS SECTION			DIM. "G"
-5XX2	.062 [1.57] THICK PC BOARD	.112 [2.84]	DIM. "F" .0245+/- .0005 [.622]	DIAGONALS .028+/- .001 [.71]	CORNER RADIUS .0075 REF. [.191]	.035+/- .003 [.89] SEE NOTE 5
-6XX2						
-5X03	.094 [2.39] TO .125 [3.18] THICK PC BOARD	.155 [3.94]	.0245+/- .0005 [.622]	.028+/- .001 [.71]	.0075 REF. [.191]	.035+/- .003 [.89]
-6X03						




DESIGN REFERENCE	NEXT ASSEMBLY	REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
3M CODES		DR	CASTIGLIONE	DATE JUL 25, 2014	MFG	DATE
		CHKD		DATE	APPR	DATE
					R. SCHERER	SEP 05, 2014
DIVISION	Interconnect Solutions	DIVISION CODE	EMSD	© 3M COPYRIGHT 2015		
DO NOT SCALE DRAWING	SCALE 4/1	TOLERANCES EXCEPT AS NOTED		3M Center St. Paul, MN 55144		
THIRD ANGLE PROJECTION		INCHES		This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.		
INTERPRET PER ASME Y14.5 - 2009		MILLIMETERS		TITLE		
MAX SURFACE ROUGHNESS				HEADER, 4-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT & RA		
MARKED ONLY				CAGE NUMBER		
				D 78-5100-0772-3		
				MODEL 3000 SERIES		
				REV. S		

3M™ FOUR-WALL HEADER, 3000 SERIES
.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE



RECOMMENDED MOUNTING HOLE PATTERN
(STRAIGHT VERSION)



RECOMMENDED MOUNTING HOLE PATTERN
(RIGHT ANGLE VERSION)

PART CUSTOMIZATION



THIS SPEC SHEET DETAILS OUR STANDARD OFFERING.

3M HAS SEVERAL CAPABILITIES THAT CAN PROVIDE A PART TAILORED TO YOUR SPECIFIC NEEDS. ASK YOUR 3M SALES REPRESENTATIVE OR CUSTOMER SERVICE FOR MORE DETAILS.

BOTH SNAP-IN AND ROLL PIN LATCHES MAY BE ORDERED SEPARATELY. SNAP-IN AND ROLL PIN STYLE LATCHES ARE DIMENSIONALLY AND FUNCTIONALLY EQUIVALENT. IF ORDERING SNAP-IN OR ROLL PIN STYLE LATCHES SEPARATELY, PLEASE USE THE BELOW CHART.

MATERIAL	SHORT LATCH	LONG LATCH	LATCH STYLE	COLOR
HIGH TEMP. (PCT)	N3505-2B	N3505-3B	ROLL PIN	BLACK
HIGH TEMP (PPA)	N3505-30B	N3505-31B	SNAP-IN	BLACK

- * SELECTIVE PIN REMOVAL (ATA OR OTHER COMPATABILITY)
- * WIRE WRAP TAILS STYLE




LONG SHORT

SNAP-IN LATCHES

NOTE:
SNAP-IN LATCHES CAN ONLY BE ORDERED SEPARATELY AND ARE THE CUSTOMERS RESPONSIBILITY TO INSTALL.

POLARIZING POST



3M PART NO.	MATERIAL	COLOR
3201-4	LCP	BLACK


NOTE:
INSERT POST INTO ONE MOUNTING HARDWARE HOLE ON BOTTOM OF HEADER. SET POST TO PROTRUDE .115 [2.92]

K2 OPTION

2500 & 3000 SERIES SHROUDED HEADER						
TOTAL NO. OF PINS	NO. OF TAILS KINKED	POSITIONS KINKED				
10	4	3	4	7	8	
14	4	3	4	11	12	
16	4	3	4	13	14	
20	4	3	4	17	18	
24	4	3	4	21	22	
26	4	3	4	23	24	
30	4	5	6	25	26	
34	4	7	8	27	28	
36	4	7	8	27	28	
40	4	7	8	33	34	
50	4	7	8	43	44	
60	4	11	12	49	50	
64	4	11	12	53	54	

KINKED TAIL DETAIL:
- KINK IS LOCATED .05" BELOW BOTTOM SURFACE OF PLASTIC.
- EXTERNAL RADIUS OF KINK TOWARD PART CENTERLINE.

POLARIZING KEYS




3M PART NO.	MATERIAL	COLOR	DIM. 'A'
N3518	LCP	BLACK	.02

NOTE:
#2216 B/A SCOTCHWELD CAN BE USED TO ADHERE KEYS.


DESIGN REFERENCE	NEXT ASSEMBLY	REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
DO NOT SCALE DRAWING	SCALE 4 1	TOLERANCES EXCEPT AS NOTED	INCHES .00 ±.01 .000 ±.005 .0000 ±	MILLIMETERS 0 ±.3 .00 ±.13 .000 ±	MARKED ONLY	ANGLES
INTERPRET PER ASME Y14.5 - 2009	MAX SURFACE ROUGHNESS	DET	LISTS	YES	NO	SHT 3 OF 4
3M	3M Center St. Paul, MN 55144	© 3M COPYRIGHT 2015	This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.	HEADER, 4-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT & RA	CAGE NUMBER	SIZE
78-5100-0772-3	S	REV.	REV.	REV.	REV.	REV.
78-5100-0772-3	S	REV.	REV.	REV.	REV.	REV.

3M™ FOUR-WALL HEADER, 3000 SERIES
.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE


MOUNTING HARDWARE




3341-5
(INSTALL FROM BOTTOM OF BOARD)
PANHEAD THREAD CUTTING SCREW:
#4-24 X 5/16"
TYPE: USA STD BT, FEDERAL BG
MATERIAL: STAINLESS STEEL




3341-6
HEX HEAD BOLT, NUT AND WASHER:
BOLT - #2-56 X 1/2"
MATERIAL: STAINLESS STEEL



3341-6
#2-56 NUT AND BOLT
TORQUE FOR EACH BOLT: 1.25 - 3.125 INCH LBS.



#4-24 TYPE BT SELF THREADING SCREW
WHEN USING LATCHES, MAXIMUM LENGTH
OF SCREW IS .250 INCHES PLUS
THICKNESS OF THE BOARD.
TORQUE FOR EACH SCREW IS 3-5 INCH LBS.



3341-5

S		60056		MAR 06, 2015		JNC		RS	
R		56068		JUL 25, 2014		JNC		RS	
REV		ECO		ISSUE DATE AND DESCRIPTION				DRFT CHKD	
DRFT		CASTIGLIONE		DATE		MFG		DATE	
CHKD				DATE		APPR		DATE	
				JUL 25, 2014		R. SCHERER		SEP 05, 2014	
DIVISION		DIVISION CODE		© 3M COPYRIGHT 2015					
Interconnect Solutions		EMSD		This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.					
DO NOT SCALE DRAWING		SCALE 4 1		TOLERANCES EXCEPT AS NOTED		TITLE			
		INCHES		.0000 ± .01		HEADER, 4-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT & RA			
THIRD ANGLE PROJECTION		MILLIMETERS		.0000 ± .005					
INTERPRET PER ASME Y14.5 - 2009		.0000 ± .0005		.0000 ± .0005					
MAX SURFACE ROUGHNESS		.0000 ± .0005		.0000 ± .0005					
✓ □ MARKED ONLY		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005		.0000 ± .0005					
		.0000 ± .0005							