



TRG30R V SERIES

30W SWITCHING ADAPTER



Features

- * Universal Input Range 90-264VAC
 - * Interchangeable AC Plugs
 - * Meets EN61204-3 Class B and CISPR/FCC Class B
 - * Continuous Short Circuit Protection
 - * Over Voltage Protection
 - * Meet CEC & ErP Level V
- (Output Cable Length $\leq$ 1800mm)
 (TRG30R050V、TRG30R090V : Output Cable Length $\leq$ 1220mm)



Ordering information

TRG30RXXXV - XX	E	XX	-	XX	-BK
Model No.	DC Plug Type	DC Cable Length and Type		Color of Overmold Case	
		01: 720mm		BE: Blue	
		02: 1220mm		GY: Gray	
		03: 1800mm		RD: Red	
		11: 720mm with Ferrite Core		PE: Purple	
		12: 1220mm with Ferrite Core		OR: Orange	
		13: 1800mm with Ferrite Core			
		* 18AWG / UL1185			
		* 16AWG / UL1185 for 5V、9V			

MODEL	OUTPUT VOLTAGE	MAX. LOAD	MIN. LOAD	RIPPLE & NOISE	VOLTAGE ACCURACY	LINE REGULATION	LOAD REGULATION	%EFF. (Typ)
TRG30R050V	5V	4.0A	0A	1%	$\pm 2\%$	$\pm 1\%$	$\pm 6\%$	80%
TRG30R090V	9V	3.0A	0A	1%	$\pm 2\%$	$\pm 1\%$	$\pm 3\%$	84%
TRG30R120V	12V	2.5A	0A	1%	$\pm 2\%$	$\pm 1\%$	$\pm 2\%$	84%
TRG30R150V	15V	2.0A	0A	1%	$\pm 2\%$	$\pm 1\%$	$\pm 2\%$	85%
TRG30R180V	18V	1.67A	0A	1%	$\pm 2\%$	$\pm 1\%$	$\pm 2\%$	85%
TRG30R240V	24V	1.25A	0A	1%	$\pm 2\%$	$\pm 1\%$	$\pm 2\%$	86%

Specifications

INPUT SPECIFICATIONS:

Voltage 90~264Vac
 Frequency 47 to 63Hz
 Input Current 100Vac/0.8A max., 240Vac/0.4A max.
 Inrush Current Cold start@25°C 100A max. @240Vac
 Leakage Current 0.25mA max.

OUTPUT SPECIFICATIONS:

Holdup Time 10ms typ. @115Vac
 Short Circuit Protection Hiccup Mode (Auto Recovery)
 Over Voltage Protection TVS Component to Clamp

GENERAL SPECIFICATIONS:


Isolation Input to output = 4,242VDC
 Operating Temperature 0 ~ 60°C (see Drating Curve)
 Storage Temperature -20~85°C
 Humidity 93% RH max. Non condensing
 Cooling Natural Convection
 Switching Frequency 70KHz Typical
 MTBF MIL-HDBK-217F, GB, 25°C/115VAC 200K hrs min.
 Altitude 2000m
 Dimensions 4.243x2.267x1.319Inches (107.77x57.60x33.50mm)
 Weight 300g(0.66 Pounds)

SAFETY AND EMC:


Emission and Immunity EN61204-3, EN61000-3-2, EN61000-3-3
 FCC CFR Title 47 Part 15 Subpart B
 Safety IEC60950-1, UL60950-1, EN60950-1

Mechanical Specification

All Dimensions are in inches(mm)
 Tolerance: Inches: X.XXX±0.02
 Millimeters: X.XX±0.5




TRG30R-V Series Derating Curve



NOTE:

- Voltage setpoint at 60% full load
- Add a 0.1uF ceramic capacitor and a 10uF E.L. capacitor to output for Ripple & Noise measuring @20MHz BW.
- Line regulation is measured from 100Vac to 240Vac with full load.
- Load regulation is measured from 60% to full load and from 60% to 20% load (60% +/- 40% load)
- "Various TR Series adapters are PSE certified. PSE certification alone is not sufficient for importation into Japan. A valid PSE mark must contain the name of the importer as shown in the example below. If PSE mark is required, the name of the registered importer must be supplied to Cincon on order placement. Product labels will not contain PSE mark if importer name is not supplied. Consult factory or local representative for details"



Typical at 25°C, nominal line and 75% load, unless otherwise Specified

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

<u>TRG30R050V-11E02-GY-BK-Level-V</u>	<u>TRG30R050V-12E02-GY-BK-Level-V</u>	<u>TRG30R090V-11E02-GY-BK-Level-V</u>
<u>TRG30R090V-12E02-GY-BK-Level-V</u>	<u>TRG30R120V-11E03-GY-BK-Level-V</u>	<u>TRG30R120V-12E03-GY-BK-Level-V</u>
<u>TRG30R150V-11E03-GY-BK-Level-V</u>	<u>TRG30R150V-12E03-GY-BK-Level-V</u>	<u>TRG30R180V-11E03-GY-BK-Level-V</u>
<u>TRG30R180V-12E03-GY-BK-Level-V</u>	<u>TRG30R240V-11E03-GY-BK-Level-V</u>	<u>TRG30R240V-12E03-GY-BK-Level-V</u>
<u>TRG30R050V-35E02-GY-BK-Level-V</u>	<u>TRG30R050V-36E02-GY-BK-Level-V</u>	<u>TRG30R050V-39E02-GY-BK-Level-V</u>
<u>TRG30R050V-40E02-GY-BK-Level-V</u>	<u>TRG30R050V-48E02-GY-BK-Level-V</u>	<u>TRG30R050V-49E02-GY-BK-Level-V</u>
<u>TRG30R120V-35E03-GY-BK-Level-V</u>	<u>TRG30R120V-36E03-GY-BK-Level-V</u>	<u>TRG30R120V-39E03-GY-BK-Level-V</u>
<u>TRG30R120V-40E03-GY-BK-Level-V</u>	<u>TRG30R120V-48E03-GY-BK-Level-V</u>	<u>TRG30R120V-49E03-GY-BK-Level-V</u>
<u>TRG30R240V-35E03-GY-BK-Level-V</u>	<u>TRG30R240V-36E03-GY-BK-Level-V</u>	<u>TRG30R240V-39E03-GY-BK-Level-V</u>
<u>TRG30R240V-40E03-GY-BK-Level-V</u>	<u>TRG30R240V-48E03-GY-BK-Level-V</u>	<u>TRG30R240V-49E03-GY-BK-Level-V</u>
<u>TRG30R240-11E03-BE-BK W/4 PLUG KIT-LVL V</u>	<u>TRG30R050V-01E02-GY-BK-Level-V</u>	<u>TRG30R050V-02E02-GY-BK-</u>
<u>Level-V</u>	<u>TRG30R090V-01E02-GY-BK-Level-V</u>	<u>TRG30R090V-02E02-GY-BK-Level-V</u>
<u>TRG30R120V-01E03-GY-BK-</u>	<u>TRG30R120V-02E03-GY-BK-Level-V</u>	<u>TRG30R150V-01E03-GY-BK-Level-V</u>
<u>Level-V</u>	<u>TRG30R150V-02E03-GY-BK-</u>	<u>TRG30R180V-01E03-GY-BK-Level-V</u>
<u>Level-V</u>	<u>TRG30R180V-02E03-GY-BK-Level-V</u>	<u>TRG30R240V-01E03-GY-BK-</u>
<u>Level-V</u>	<u>TRG30R240V-02E03-GY-BK-Level-V</u>	