

POWER SPLITTERS/COMBINERS

50 & 75Ω

2 WAY-0° 2 kHz to 10 GHz



ZESC-2



ZFSC-2



ZMSC-2



ZSC-2

MODEL NO.	FREQ. RANGE MHz f_L - f_U	ISOLATION dB						INSERTION LOSS, dB Above 3dB						PHASE UNBAL. Degrees			AMPLITUDE UNBAL. dB			VSWR (:1)			CASE STYLE	CONNECTION	PRICE \$ Qty. (1-9)
		L	M*	U				L	M*	U				L	M*	U	L	M*	U	S	OUT				
ZESC-2-11	10-2000	19	10	18	13	20	11	0.5	0.9	0.5	1.0	0.6	1.2	1	3	6	0.20	0.30	0.50				V37	ar	71.95
ZFSC-2-1	5-500	30	25	28	20	25	20	0.2	0.5	0.3	0.6	0.6	0.8	2	4	4	0.15	0.15	0.30				K18	ar	44.95
■ ZFSC-2-1-75	0.25-300	20	15	30	25	25	20	0.4	0.75	0.4	0.75	0.4	1.0	2	3	5	0.15	0.20	0.30				K18	ar	45.95
■ ZFSC-2-1W-75	5-600	44	26	45	30	31	20	0.22	0.6	0.27	0.7	0.46	0.9	1	2	3	0.20	0.30	0.40				K18	ar	50.95
ZFSC-2-1W	1-750	30	20	28	20	25	20	0.2	0.5	0.4	0.8	0.8	1.0	2	4	4	0.15	0.15	0.30				K18	ar	48.95
ZFSC-2-2	10-1000	30	20	25	20	23	18	0.2	0.5	0.5	1.0	0.9	1.2	2	4	4	0.15	0.15	0.30				K18	ar	51.95
ZFSC-2-9G	3500-9000	18	12	20	12			0.5	1.5	0.6	1.2			7	10		0.30	0.50					JJJ142	as	59.95
ZFSC-2-10G	2000-10000	15	9	20	12			0.5	1.5	0.6	1.6			7	12		0.60	0.50					JJJ142	as	69.95
ZFSC-2-4	0.2-1000	20	15	25	20	23	18	0.2	0.8	0.5	1.0	0.9	1.2	2	4	4	0.15	0.15	0.30	see Yoni for Performance			K18	ar	55.95
ZFSC-2-5	10-1500	25	15	30	20	25	18	0.25	0.6	0.5	1.0	0.8	1.5	2	3	4	0.15	0.20	0.50				K18	ar	59.95
❖ ZFSC-2-6*	0.002-60	27	20	30	20	27	20	0.3	0.6	0.3	0.6	0.6	1.0	2	3	4	0.15	0.20	0.30				K18	ar	49.95
❖ ZFSC-2-6-75	0.004-60	30	20	35	20	25	20	0.5	0.8	0.4	0.8	0.7	1.0	1	2	3	0.15	0.20	0.30				K18	ar	51.95
ZFSC-2-11	10-2000	14	10	16	14	20	15	1.2	1.5	1.2	1.5	1.0	2.2	1	2	4	0.20	0.30	0.50	Data and curves			K18	ar	64.95
▲ ZFSC-2-2500	10-2500	16	11	17	14	17	14	0.5	0.8	0.6	1.4	0.8	1.5	1	4	8	0.20	0.30	0.40				K18	ar	74.95
ZMSC-2-1	0.1-400	20	15	25	20	25	20	0.2	0.5	0.4	0.75	0.6	1.0	2	3	4	0.15	0.20	0.30				M21	at	49.95
ZMSC-2-1W	1-650	25	20	35	20	25	20	0.3	0.5	0.5	0.8	0.7	1.0	2	3	4	0.15	0.20	0.30				M21	at	54.95
❖ ZMSC-2-2*	0.002-60	27	20	30	20	27	20	0.3	0.6	0.3	0.6	0.6	1.0	2	3	4	0.15	0.25	0.30				M21	at	59.95
ZSC-2-1	0.1-400	20	15	25	20	25	20	0.2	0.5	0.4	0.75	0.6	1.0	2	3	4	0.15	0.20	0.30				M22	at	47.95
ZSC-2-1W	1-650	25	20	35	25	25	20	0.3	0.5	0.5	0.8	0.7	1.0	2	3	4	0.15	0.20	0.30				M22	at	49.95
❖ ZSC-2-2*	0.002-60	25	20	30	20	27	20	0.3	0.6	0.3	0.6	0.6	1.0	2	3	4	0.15	0.25	0.30				M22	at	52.95
❖ ZSC-2-2-75**	0.002-60	25	20	30	20	27	20	0.3	0.6	0.3	0.6	0.6	1.0	2	3	4	0.15	0.25	0.30				M22	at	53.95
ZSC-2-4	10-1000	25	20	35	20	25	20	0.2	0.5	0.5	0.8	0.7	1.3	2	4	6	0.15	0.20	0.30				M22	at	52.95
■ ZSC-2375	55-85			35	25					0.3	0.5			1			0.10						M22	at	52.95
■ ZSC-2-1-75	0.25-300	20	15	30	20	20	15	0.4	0.75	0.4	0.75	0.4	1.0	2	3	5	0.15	0.20	0.30				M22	at	49.95

NOTES:

- * Isolation specified to 0.004 MHz
- ** Insertion loss, Isolation specified to -20°C from 0.002 to 0.004 MHz
- ⊕ When only specification for M range given, specification applies to entire frequency range.
- ❖ At low range frequency band (f_L to $10 f_L$), linearly derate maximum input power by 13 dB.
- Denotes 75 Ohm model, for coax connector models 75 Ohm BNC connectors are standard.
- ▲ Available only with SMA connectors
- A. General Quality Control Procedures, Environmental Specifications, Hi-Rel and MIL description are given in "Mini-Circuits Guarantees Quality" article.
- B. For details on Connector types, case mounted options, case finishes see "Case styles & Outline Drawings".
- C. Prices and specifications subject to change without notice.
- 1. Absolute maximum power, voltage and current ratings:
 - 1a. Matched power rating:
 - Models ZAPD, ZN2PD, ZC2PD 10 Watt
 - ZAPD-900-5W, ZN2PD-20 5W(as a splitter)
 - ZAPD-30 and other models 1 Watt
 - 1b. Internal load dissipation:
 - ZAPD-900-5W 1W max.
 - ZN2PD-20 0.725W max.
 - ZN2PD-9G, ZAPD-2-22-75 0.25W max.
 - All other models 0.125 Watt

coaxial connections

see case style outline drawing for pin locations

PORT	ar	as	at
SUM PORT	3	5	2
PORT 1	1	1	1
PORT 2	2	2	3
GND EXT.	—	—	—
CASE GND	—	—	—
NOT USED	—	—	—

Mini-Circuits®

Distribution Centers NORTH AMERICA 800-654-7949 • 417 335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

ISO 9001 CERTIFIED

Coaxial



	MODEL NO.	FREQ. RANGE MHz f_L - f_U	ISOLATION dB			INSERTION LOSS, dB Above 3dB			PHASE UNBAL. Degrees			AMPLITUDE UNBAL. dB			VSWR (:1)		CASE STYLE	CONNECTION	PRICE \$ Qty. (1-9)				
			L	M ⁰	U	L	M ⁰	U	L	M ⁰	U	L	M ⁰	U	S	OUT							
			Typ. Min.	Typ. Min.	Typ. Min.	Typ. Max.	Typ. Max.	Typ. Max.	Max.	Max.	Max.	Max.	Max.	Max.	Typ. Max.	Typ. Max.				Note B			
NEW	ZC2PD-900	800-900		30	20		0.1	0.4		2		0.20		1.10	1.30	1.10	1.30	F183	as	64.95			
	ZN2PD-20	750-2000	18 ^L 15	25	20	18 ^U 15		0.2	0.5		4		0.30		1.16	1.5	1.10	1.35	VVV180	as	67.95		
	ZN2PD-920	800-920		30	20		0.15	0.4		2		0.20		1.10	1.20	1.04	1.20	VVV180	as	59.95			
	ZN2PD-920W	700-1050		22	15		0.15	0.5		3		0.30		1.20	1.50	1.04	1.20	VVV180	as	54.95			
	ZN2PD-1900	1600-1900		30	20		0.18	0.4		2		0.20		1.20	1.35	1.04	1.20	VVV180	as	69.95			
	ZN2PD-1900W	1500-2000		24	15		0.2	0.5		3		0.30		1.20	1.50	1.04	1.20	VVV180	as	64.95			
	ZN2PD-9G	1700-9000		22	15		0.5	1.4		4		0.60						VVV180	as	69.95			
	ZN2PD2-50	500-5000		25	15		0.8	1.4		4		0.5		1.20	—	1.10	—	VVV845	as	74.95			
		600-1600		24	17		0.7	1.1		2		0.3		1.20	—	1.10	—						
		1600-2700		26	18		0.8	1.2		3		0.3		1.20	—	1.10	—						
		2700-3600		28	19		0.9	1.3		3		0.4		1.20	—	1.10	—						
		3700-4800		22	18		0.9	1.4		4		0.5		1.20	—	1.10	—						
		GHz																					
		IZY2PD-64	5.8-6.4		35	24		0.2	0.5		5		0.30		1.05	1.30	1.20	1.35	JJJ245	as	89.95		
		IZY2PD-86	7.0-8.6		30	18		0.1	0.5		6		0.25		1.10	1.45	1.10	1.40	JJJ245	as	94.95		
	ZAPD-1	0.5-1.0		25	19		0.25	0.6		2		0.20						F14	as	54.95			
	ZAPD-2	1.0-2.0		25	19		0.25	0.6		2		0.20						F14	as	54.95			
	■ ZAPD-2-22-75	0.91-2.15		30	20		0.2	0.7		2		0.40		1.15	1.60	1.10	1.30	F14	as	58.95			
	ZAPD-20	0.7-2.0		30	20		0.30	0.7		3		0.40		1.15	1.35	1.10	1.30	F53	as	59.95			
	ZAPD-21	0.5-2.0		25	18		0.25	1.0		3		0.20						F53	as	59.95			
	▲ ZAPD-30	0.02-3.0	14	12	16	12	20	14	1.1	1.5	1.1	1.8	1.4	2.3	3	5	9	0.30	0.40	0.80	F14	as	79.95
	ZAPD-4	2.0-4.2		25	19		0.4	0.8		6		0.40		see Yoni for Performance Data and curves				F14	as	59.95			
	ZAPD-50	4.4-5.0		26	20		0.3	0.8		5		0.50					F14	as	54.95				
	ZAPD-50W	4.2-6.0		26	16		0.3	0.8		5		0.70					F14	as	64.95				
	ZAPD-900-5W	0.1-0.9		23	18		0.3	1.0		3		0.30					F14	as	59.95				
	ZAPD-1750	0.95-1.75		30	22		0.2	0.4		4		0.50		1.15	1.50	1.22	1.50	F14	as	54.95			

L = low range [f_L to $10 f_L$]
 $L^1 = f_L$ to 6 GHz
 $L^0 = 750$ to 875 MHz

M = mid range [$10 f_L$ to $f_U/2$]
 $U^1 = 6$ GHz to f_U
 $U^0 = 1850$ to 2000 MHz

U = upper range [$f_U/2$ to f_U]

NSN GUIDE

MCL NO.	NSN	MCL NO.	NSN	MCL NO.	NSN
ZAPD-1(TNC)	5985-01-250-4883	ZFSC-2-2(SMA)	6625-01-333-1127	ZSC-2-1(TNC)	6625-01-310-2129
ZAPD-2 (BNC)	5895-01-476-0831	ZFSC-2-2B	5895-01-330-4416	ZSC-2-1	5895-01-214-6032
ZAPD-2(SMA)	5895-01-229-7431	ZFSC-2-4	6625-01-291-3346	ZSC-2-1B	6625-01-018-1066
ZAPD-4	6625-01-173-1887	ZFSC-2-4(TNC)	5985-01-250-4882	ZSC-2-1B(TNC)	6625-01-109-3706
ZAPD-4(SMA)	5985-01-383-0636	ZFSC-2-5	6625-01-253-2444	ZSC-2-1(BNC)	5895-01-036-6254
ZESC-2-11	5985-01-381-9081	ZFSC-2-6	6625-01-419-4241	ZSC-2-1B(BNC)	6625-00-270-3055
ZFSC-2-1	6625-01-139-3499	ZFSC-2-6(BNC)	5895-01-408-6857	ZSC-2-1W	5895-01-283-0850
ZFSC-2-1(SMA)	6625-01-213-6490	ZFSC-2-6B	5985-01-315-2869	ZSC-2-1WB	6625-01-264-8985
ZFSC-2-1(BNC)	5985-01-176-4551	ZFSC-2-10G	5895-01-467-5372	ZSC-2-1-75B	5895-01-136-8182
ZFSC-2-1-75	5895-01-325-4795	ZFSC-2-11(SMA)	6625-01-415-2183	ZSC-2-2B	5820-01-136-7245
ZFSC-2-1W(SMA)	6625-01-200-5094	ZMSC-2-1	5985-01-333-1128	ZSC-2-2-75B	5915-01-012-8162
ZFSC-2-1W	5895-01-348-3534	ZMSC-2-1B	5895-01-253-2445	ZSC-2375	5895-01-229-0157
ZFSC-2-2B(SMA)	6625-01-362-1801	ZMSC-2-1BR	5985-01-338-9329		
		ZMSC-2-1W	5895-01-127-0232		



The Design Engineers Search Engine
 Provides Actual Data Instantly
 At: <http://www.minicircuits.com>

In Stock... Immediate Delivery
 For Custom Versions Of Standard Models
 Consult Our Applications Dept.

