

Home: Solid State Lighting >

Need Assistance?

- Contact Us
- Find a Distributor
- eLearning
- ecocare | EHS Info

Part Number: 180150-0001

LED Array Holder for Bridgelux ES, with Lens Cover



Series image - Reference only

Status: New Business Not Supported

Replacement: Contact Molex

Series: 180150

Category: Solid State Lighting

Overview: LED Array Holders for Bridgelux and Similar COB Arrays

CHECK DISTRIBUTOR INVENTORY

Add to My Parts

Email this page

Go to Part Detail

Product Environmental Compliance

- EU ELV: Not Relevant
- EU RoHS: Compliant
- EU RoHS Phthalates: Not Contained
- China RoHS: Compliant
- REACH SVHC: Not Contained Per - ED/21/2016 (20 June 2016)
- Low-Halogen Status: Not Low-Halogen

- EU RoHS Certificate of Compliance (PDF)
- Multiple Part Product Compliance Statements
EU RoHS, REACH SVHC, & Low-Halogen
- Multiple Part Industry Compliance Documents
*IPC 1752A Class C
*IPC 1752A Class D
*Molex Product Compliance Declaration
*IEC-62474
*chemSHERPA (xml)

Application Tooling FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

Check our list of old tooling that used to be available for this part

Questions on Product Environmental Compliance? Email Product.Compliance@molex.com

Request Molex's CMRT from conflictminerals@molex.com

Part Detail COLLAPSE ALL

General

Status	New Business Not Supported
Category	Solid State Lighting
Series	180150
Array Type	Bridgelux
Beam Angle	N/A
Overview	LED Array Holders for Bridgelux and Similar COB Arrays
Product Name	Wire Trap Holder
Type	LED COB Array Holder
UPC	884982498839

Physical

Base Type	N/A
Color Rendering Index (CRI)	N/A
Correlated Color Temp (CCT)	N/A
Flammability	94V-0

Lamp Type	N/A
Mounting Style	Screws
Net Weight	7.378/g
Packaging Type	Tray

▼ ▼ Electrical

(Please review the Product Specification for specific details.)	
Lamp Wattage - Maximum	N/A
Lumens	N/A
Voltage (Fixture) - Maximum	300V DC
Wiring Style	Poke In Wire Traps

▼ ▼ Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number. Click here to visit the UL Database	
UL	E345583

PRODUCTS++

- Product Categories
- Product Index
- Industries


QUICK LINKS++

- Company Information
- Contact Molex
- Cross-Reference
- Koch Industries
- Investor Relations
- Literature
- Press Room / Press Releases
- Sitemap
- Terms & Conditions

RESOURCES++

- Supply Chain Transparency
- Business Continuity
- Compliance
- ecocare
- Help
- Jobs
- Legal | Trademarks
- Supplier Portal
- Privacy Policy
- Tradeshows

STAY CONNECTED



Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2018