



NOTES:

1. ADAPTER TO BE PERMANENTLY MARKED WITH P/N AND CODE IDENT. NO (06090).
2. ADAPTER MATES TO: MIL-C-5015, 3400 SERIES, CLASS D, L, U & W, MS3476 SHELL SIZE 10


REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
N/C	INITIAL RELEASE PER ECN NO. 15513	12-21-90	G.D



HOLES FOR .020 MAX. DIA.
SAFETY WIRE, 3 PLACES,
EQUALLY SPACED



SPACER RING
(SR05X)



TINELL-LOCK RING
(TR05XX)

PART NUMBER

HCA6 A C 0187-05 A I

PRODUCT DESIGNATOR

MATERIAL: ALUMINUM ALLOY
6061-T6 PER QQ-A-225/B.

FINISH: ELECTROLESS NICKEL
PER MIL-C-28074, CLASS
3 OR 4, GRADE B

(SEE S-CH00-0157-002
FOR ADDITIONAL FINISHES)

CONDUIT I.D.

TINELL AND SPACER RING SIZE

BRAID DESIGNATOR

A: SINGLE LAYER 36 AWG BRAID
B: SINGLE LAYER 30 AWG OR DOUBLE
LAYER 36 AWG BRAID

TINELL-LOCK RING WITH INSULATING LINING

If this document is printed it becomes uncontrolled.
Check with the web for latest revision.

SPECIFICATION CONTROL DRAWING

© Raychem Corporation 1988

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. METRIC DIMENSIONS ARE IN BRACKETS.	DRAWN	G.Bul	10-21-90	Raychem RAYCHEM CORPORATION 3500 CONSTITUTION DRIVE SUNLAND PARK, CALIFORNIA 94068	
	CHECKED	G.Dibble	12-20-90		
	APPROVED	G.Dibble	12-21-90	TITLE 90° CONDUIT ADAPTER	
	APPROVED	N.Dydo	12-21-90		
DECIMALS .XXX ± .XX ± ANGLES .X ±	CAD NAME		HCA6	SIZE	CODE IDENT. NO.
WEIGHT	THIRD ANGLE PROJECTION			C	06090
lbs [g]				DWG. NO.	HCA 6
				DO NOT SCALE THIS DRAWING	REV N/C