

# E1SJA30-15.72864M TR

[Click part number to visit Part Number Details page](#)

## REGULATORY COMPLIANCE (Data Sheet downloaded on Sep 9, 2018)


[Click badges to download compliance docs](#)

Regulatory Compliance standards are subject to updates by governing bodies. Click the badges to download the latest compliance docs for this part number directly from Ecliptek.



## ITEM DESCRIPTION

Quartz Crystal Resonator HC49/UP Short 2 Pad Surface Mount (SMD) 3.2mm Height Metal Resistance Weld Seal 15.72864MHz  $\pm 15$ ppm at 25°C,  $\pm 30$ ppm over -40°C to +85°C 30pF Parallel Resonant

## ELECTRICAL SPECIFICATIONS

|                               |                                                        |
|-------------------------------|--------------------------------------------------------|
| Nominal Frequency             | 15.72864MHz                                            |
| Frequency Tolerance/Stability | $\pm 15$ ppm at 25°C, $\pm 30$ ppm over -40°C to +85°C |
| Aging at 25°C                 | $\pm 5$ ppm/year Maximum                               |
| Load Capacitance              | 30pF Parallel Resonant                                 |
| Shunt Capacitance             | 7pF Maximum                                            |
| Equivalent Series Resistance  | 60 Ohms Maximum                                        |
| Mode of Operation             | AT-Cut Fundamental                                     |
| Drive Level                   | 1mWatt Maximum                                         |
| Storage Temperature Range     | -55°C to +125°C                                        |
| Insulation Resistance         | 500 Megaohms Minimum (Measured at 100Vdc)              |

## ENVIRONMENTAL & MECHANICAL SPECIFICATIONS


|                              |                                               |
|------------------------------|-----------------------------------------------|
| ESD Susceptibility           | MIL-STD-883, Method 3015, Class 1, HBM: 1500V |
| Fine Leak Test               | MIL-STD-883, Method 1014, Condition A         |
| Flammability                 | UL94-V0                                       |
| Gross Leak Test              | MIL-STD-883, Method 1014, Condition C         |
| Mechanical Shock             | MIL-STD-202, Method 213, Condition C          |
| Moisture Resistance          | MIL-STD-883, Method 1004                      |
| Moisture Sensitivity         | J-STD-020, MSL1                               |
| Resistance to Soldering Heat | MIL-STD-202, Method 210, Condition K          |
| Resistance to Solvents       | MIL-STD-202, Method 215                       |
| Solderability                | MIL-STD-883, Method 2003                      |
| Temperature Cycling          | MIL-STD-883, Method 1010, Condition B         |
| Vibration                    | MIL-STD-883, Method 2007, Condition A         |

E1SJA30-15.72864M TR

 Click part number to visit  
Part Number Details page


MECHANICAL DIMENSIONS (all dimensions in millimeters)

| LINE | MARKING                                         |
|------|-------------------------------------------------|
| 1    | <b>E15.728M</b><br><i>E=Ecliptek Designator</i> |



Suggested Solder Pad Layout

All Dimensions in Millimeters



All Tolerances are ±0.1



# E1SJA30-15.72864M TR

## Tape & Reel Dimensions

Quantity Per Reel: 1,000 units

All Dimensions in Millimeters

Compliant to EIA-481



E1SJA30-15.72864M TR

[Click part number to visit Part Number Details page](#)

Recommended Solder Reflow Methods




High Temperature Infrared/Convection

|                                     |                                                   |
|-------------------------------------|---------------------------------------------------|
| Ts MAX to TL (Ramp-up Rate)         | 3°C/Second Maximum                                |
| Preheat                             |                                                   |
| - Temperature Minimum (Ts MIN)      | 150°C                                             |
| - Temperature Typical (Ts TYP)      | 175°C                                             |
| - Temperature Maximum (Ts MAX)      | 200°C                                             |
| - Time (ts MIN)                     | 60 - 180 Seconds                                  |
| Ramp-up Rate (TL to TP)             | 3°C/Second Maximum                                |
| Time Maintained Above:              |                                                   |
| - Temperature (TL)                  | 217°C                                             |
| - Time (tL)                         | 60 - 150 Seconds                                  |
| Peak Temperature (TP)               | 260°C Maximum for 10 Seconds Maximum              |
| Target Peak Temperature (TP Target) | 250°C +0/-5°C                                     |
| Time within 5°C of actual peak (tp) | 20 - 40 Seconds                                   |
| Ramp-down Rate                      | 6°C/Second Maximum                                |
| Time 25°C to Peak Temperature (t)   | 8 Minutes Maximum                                 |
| Moisture Sensitivity Level          | Level 1                                           |
| Additional Notes                    | Temperatures shown are applied to body of device. |

# E1SJA30-15.72864M TR

[Click part number to visit Part Number Details page](#)

## Recommended Solder Reflow Methods



## Low Temperature Infrared/Convection 245°C

|                                   |                    |
|-----------------------------------|--------------------|
| $T_S$ MAX to $T_L$ (Ramp-up Rate) | 5°C/Second Maximum |
|-----------------------------------|--------------------|

### Preheat

|                                    |                 |
|------------------------------------|-----------------|
| - Temperature Minimum ( $T_S$ MIN) | N/A             |
| - Temperature Typical ( $T_S$ TYP) | 150°C           |
| - Temperature Maximum ( $T_S$ MAX) | N/A             |
| - Time ( $t_s$ MIN)                | 30 - 60 Seconds |

|                                 |                    |
|---------------------------------|--------------------|
| Ramp-up Rate ( $T_L$ to $T_P$ ) | 5°C/Second Maximum |
|---------------------------------|--------------------|

### Time Maintained Above:

|                         |                     |
|-------------------------|---------------------|
| - Temperature ( $T_L$ ) | 150°C               |
| - Time ( $t_L$ )        | 200 Seconds Maximum |

|                            |               |
|----------------------------|---------------|
| Peak Temperature ( $T_P$ ) | 245°C Maximum |
|----------------------------|---------------|

|                                         |                                              |
|-----------------------------------------|----------------------------------------------|
| Target Peak Temperature ( $T_P$ Target) | 245°C Maximum 2 Times / 230°C Maximum 1 Time |
|-----------------------------------------|----------------------------------------------|

|                                          |                                                        |
|------------------------------------------|--------------------------------------------------------|
| Time within 5°C of actual peak ( $t_P$ ) | 10 Seconds Maximum 2 Times / 80 Seconds Maximum 1 Time |
|------------------------------------------|--------------------------------------------------------|

|                |                    |
|----------------|--------------------|
| Ramp-down Rate | 5°C/Second Maximum |
|----------------|--------------------|

|                                   |     |
|-----------------------------------|-----|
| Time 25°C to Peak Temperature (t) | N/A |
|-----------------------------------|-----|

|                            |         |
|----------------------------|---------|
| Moisture Sensitivity Level | Level 1 |
|----------------------------|---------|

|                  |                                                   |
|------------------|---------------------------------------------------|
| Additional Notes | Temperatures shown are applied to body of device. |
|------------------|---------------------------------------------------|

## Low Temperature Manual Soldering

185°C Maximum for 10 Seconds Maximum, 2 times Maximum. (Temperatures shown are applied to body of device.)

## High Temperature Manual Soldering

260°C Maximum for 5 Seconds Maximum, 2 times Maximum. (Temperatures shown are applied to body of device.)