

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [03-09-1126](#)
Status: **Active**
Overview: [Standard .093" Pin and Socket Connectors](#)
Description: 2.36mm Diameter Standard .093" Pin and Socket Receptacle Housing, 12 Circuits, 3 Rows

Documents:
[3D Model](#) [Product Specification PS-43660-9999 \(PDF\)](#)
[Drawing \(PDF\)](#) [Packaging Specification PK-1360-001 \(PDF\)](#)
[Product Specification PS-02-09 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [1360](#)
Application Power, Wire-to-Wire
Comments 12.5A max. can be achieved when housing is used with 42477 or 42478 terminals
Overview [Standard .093" Pin and Socket Connectors](#)
Product Name Standard .093"
UPC 800753614741

Physical

Circuits (maximum) 12
Color - Resin Natural
Flammability 94V-2
Gender Receptacle
Glow-Wire Compliant No
Material - Resin Nylon
Net Weight 5.386/g
Number of Rows 3
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 5.03mm
Stackable No
Temperature Range - Operating -40°C to +105°C

Electrical

Current - Maximum per Contact 9.5A

Material Info

Old Part Number 1360-R3

Reference - Drawing Numbers

Packaging Specification PK-1360-001
Product Specification PS-02-09, PS-43660-9999
Sales Drawing SD-1360-*




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[1360Series](#)

Mates With
[03-09-2121](#) , [03-09-2122](#) , [3099](#)

Use With
[1189](#) Crimp Terminals, [1190](#) Crimp Terminals, [1376](#) Male PC Tail Terminals, [1377](#) Female PC Tail Terminals, [1380](#) Male Crimp Terminals, [1381](#) Female Crimp Terminals, [1433](#) Crimp Terminals, [1434](#) Male Crimp Terminals, [1973](#)