

REV. Status

ISSUE 1
3/13/91 TSISSUE 2
TEMECULA
WAS CARSON.
UPDATED LABELS
12/15/92 TSISSUE 3
REFORMATTED
6/18/93 TS

A. Electrical Specifications (@ 25 ° C)

1. Input Voltage and Frequency; 115V 60 Hz
2. Output Voltage; 20V $\pm 5\%$ @ 0.125A load, series
10V $\pm 5\%$ @ 0.25A load, parallel
3. Output Power; 2.5 VA
4. Insulation Resistance;
100 M Ω MIN @ 500VDC, Pri to Sec, Pri to Core, Sec to Core
5. Hi-Pot;
1500 Vrms 1 minute @ Pri to Sec, Pri to Core
1500 Vrms 1 minute @ Sec to Core
6. Temperature Rating; 130°C (UL Class "B")

B. Marking; 3FL20-125-115, TAMURA TEMECULA CA, date code, country of origin, Input and output ratings, terminal numbers, safety symbols and "130B".



C. Safety:

UL approved, file E145619.




Insulation Class B (130° C) File E92957

CSA Certified, file LR81383-7

D. Schematic Diagram:



E. Mechanical Specifications:



PREPARED:

K. Georgeson
ENGINEER:

T. Sasaki
APPROVED:

D. Suzuki

DWG CONTROL NO.
P-A1-10509
ACAD\3FL\A1105091.DWG

REV
B

3 FLANGE BOBBIN
POWER TRANSFORMER

CONTENTS OF THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT
PRIOR NOTICE

TAMURA CORPORATION OF AMERICA
43352 BUSINESS PARK DRIVE, TEMECULA CA., 92590-6624
(909) 699-1270 FAX 9096769482

3FL20-125-115

MODEL SPECIFICATION

DIM: mm(In) SCL: NONE SH: 1 OF 1

PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING.

MODEL NUMBER

3FL20-125-115