


Technical drawing of a mechanical part, likely a bracket or connector, showing dimensions in inches and millimeters.

Dimensions:

- Top horizontal dimension: .60 (15.24) (REF)
- Right horizontal dimension: 0.58 (14.7) (REF)
- Bottom horizontal dimension: 0.20 (5.1) (REF)
- Left vertical dimension: .23 (5.8) (REF)

PANDUIT PART NUMBER	MAXIMUM CABLE DIAMETER	PANEL DIMENSIONS		WEIGHT LBS./100 PCS (g)
		THICKNESS	HOLE SIZE	
VWS4218	0.18 (4.6)	0.03/0.08 (0.8/2.0)	0.187/0.192 (4.7/4.9)	0.10 (46.6)



1. SEE CURRENT PRICE SHEET FOR PART NUMBER
SUFFIX DESIGNATION FOR PACKAGE SIZE
AND PART COLOR.

										(DIMENSIONS IN PARENTHESES ARE METRIC)	
										G00239JA_VWS4218_01	
										 PANDUIT CORP. TINLEY PARK, ILLINOIS	
										VERTICAL WIRE SADDLE VWS4218	
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± N/A (.XXX) ± .010 (.25) (.XX) ± .02 (.5) ANGLES ± N/A	
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
I	5/20/03	JAD		REMOVED 5 DIMS, ADDED 0.60 DIM	G80239JA	I				DRAWN BY LGG	MAT'L: NYLON 6/6
R	3-13-02	LGG		INITIAL RELEASE REPLACED 8-00844. UPDATE W/REP'S TOOK 1 DIM OFF.	G80239JA	R				DATE 3/13/02	SCALE 2/1
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		CHK'D 	DRAWING NO. G80239JA
										DIS A	SIZE