

DATE

REVISIONS

REV

DRAWING NUMBER
SSL-LXA227GC-TR11

REV

LIMITS OF SAFE OPERATION AT 25°C



PARAMETER	MAX	UNITS
PEAK FORWARD CURRENT*	160	mA
STEADY CURRENT	30	mA
POWER DISSIPATION	100	mW
DERATE FROM 25°C	-1.2	mW/°C
OPERATING, STORAGE TEMP	-40 TO +85	°C
LEAD SOLDERING TEMP	+280	°C
		3 SEC. MAX

* $t < 10\mu s$ ELECTRO-OPTICAL CHARACTERISTICS $T_A = 25^\circ C$ $I_f = 20mA$

PARAMETER	MIN	TYP	MAX	UNITS	TEST COND
PEAK WAVELENGTH		565 (GREEN)		nm	
FORWARD VOLTAGE		2.1	2.8	V_f	
REVERSE VOLTAGE	5.0			V_r	$I_r = 100\mu A$
AXIAL INTENSITY		30		mcd	$I_f = 20mA$
VIEWING ANGLE		25		2x theta	
EMITTED COLOR	GREEN				
EPOXY LENS FINISH	WATER CLEAR				

RELIABILITY NOTE

OUR MANY YEARS OF EXPERIENCE DATA ACCUMULATION INDICATE THAT SOLDER HEAT IS A MAJOR CAUSE OF EARLY AND FUTURE FAILURE. PLEASE PAY ATTENTION TO YOUR SOLDERING PROCESS.



TAPE DIRECTION

TOP TAPE

LUMEX
INCORPORATED

 290 E. HELLEN ROAD
PALATINE, ILLINOIS 60067
(847) 359-2790

CONFIDENTIAL INFORMATION
THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INCORPORATED. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INCORPORATED, THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

DATE: 8-15-96

DWN:

CHK'D:

APPD:

SCALE: N/A

 AXIAL LED, GREEN, WATER CLEAR LENS
GULL WING, TAPE AND REEL

PAGE 1 OF 1

DRAWING NUMBER
SSL-LXA227GC-TR11

REV

WS/GK/DN