






A	1	2	3	4
	recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	wall thickness	length of cut-out	width of cut-out
		0.75 to 1.25	19.2-0.1	12.9+0.1
		1.25 to 2	19.4-0.1	12.9+0.1
B		2 to 3	19.8-0.1	12.9+0.1
C				
				
				
	SPDT With centre-off Suitable for appliances of class II Biased from both side 			
D	Marking © 1808. µ 6(2)/250~T100/55 			
	6A 125-250V AC 1/8HP R58 Code of manufacture: place/year/week			
E				

-	-	-	1808.1302-XX
Figure	Type	Customer Part No.	Art.No.-PI
Shape and location 	Angle ± 2 ° Edge tolerance 	Sheet 01 Format DIN A4 Projection  Scale 1:1 All dimensions are in millimetres	
		Ident.	Document number
		K	18081302
		Appliance Switch	
h	137894	2021-06-09	JOSHIO
g	64492	2009-10-20	MUT
f	29392	2000-05-04	SIG
e	16107	1984-08-30	RIE
Index	MEC-No.	Date (YYYY-MM-DD)	Edited by
		System NX V1872 Replacement of Zg.gl.Nr.v.04.05.2000	
		 MARQUARDT	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Marquardt:

<u>1808.1302</u>	<u>1801.1132</u>	<u>1829.1301</u>	<u>1807.1103</u>	<u>1806.1402</u>	<u>1801.6109</u>	<u>1804.2402</u>	<u>1800.1106</u>	<u>1804.6124</u>	<u>1803.2404</u>
<u>1801.1916</u>	<u>1804.1202</u>	<u>1801.2151</u>	<u>1801.1905</u>	<u>1801.2102</u>	<u>1806.1404</u>	<u>1804.1110</u>	<u>1808.1307</u>	<u>1801.1164</u>	<u>1808.6602</u>
<u>1802.6103</u>	<u>1801.6113</u>	<u>1804.2202</u>	<u>1809.1105</u>	<u>1807.1104</u>	<u>1801.5429</u>	<u>1801.1139</u>	<u>1806.1407</u>	<u>1801.5105</u>	<u>1806.1408</u>
<u>1806.1502</u>	<u>1822.1401</u>	<u>1801.6158</u>	<u>1821.1401</u>	<u>1804.1204</u>	<u>1808.6105</u>	<u>1802.1119</u>	<u>1805.7119</u>	<u>1806.1202</u>	<u>1803.2402</u>
<u>1801.192</u>	<u>1802.1425</u>	<u>1801.1252</u>	<u>1801.1193</u>	<u>1801.1903</u>	<u>1801.6157</u>	<u>1802.1120</u>	<u>1807.1115</u>	<u>1802.1126</u>	<u>1804.2903</u>
<u>1802.1105</u>	<u>1801.1173</u>	<u>1801.613</u>	<u>1801.1197</u>	<u>1802.1160</u>	<u>1801.6159</u>	<u>1801.1907</u>	<u>1806.1908</u>	<u>1802.3106</u>	<u>1801.6155</u>
<u>1801.1912</u>	<u>1805.7107</u>	<u>1801.6156</u>	<u>1801.6123</u>	<u>1807.1111</u>	<u>1801.5107</u>	<u>1806.1909</u>	<u>1801.6104</u>	<u>1800.1115</u>	<u>1801.1920</u>