POS. 1

POS. 2

POS. 3



CIRCUIT: DPDT 3-WAY

NOTE: JUMPER PIN 3 TO PIN 5


SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
		
DN	DN	DN
2-3,5-6	2-3,5-4	2-1,5-4

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. RATING: 5A @120VAC OR 28VDC
2A @250VAC
5. MATERIALS: FIXED TERM. &MOVING CONTACT:
Cu Alloy w/Silver plate
6. ELECTRICAL LIFE: 50,000 make-and-break
cycles at full load.
7. INSULATION RESISTANCE: 1,000M ohm min.
8. DIELECTRIC STRENGTH: 1000V RMS @test level
9. OPERATING TEMP.: -30°C to 85°C



VIEW A-A



9. OPERATING TEMP.: -30°C to 85°C 10. SELECTING THE APPROPRIATE SCHEMATIC			
C	12604	REVISED FUNC/SCHEMATIC	12/13/02 CJB
B	11520	REVISED TERM NOS/SCHEMATIC	6/29/01 CJB
REV.	ECN No.	DESCRIPTION	DATE CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			

E-SWITCH®				
TITLE				
100 DP-6 T1 B1 M1 Q E				
SCALE	DATE	DR	DWG	REV
2:1	6/1/01	CJB	T126001	C