

PRODUCT NUMBER
76745-YXX-XXLF

- RoHS COMPATIBLE, SEE NOTE 8
- TOTAL NB OF POS (04 TO 72 POS)
- OPTION LETTER, SEE NOTE 6
- PIN STYLE

PLATING



- 1 = 0.76µm GOLD/GXT,
- 3 = 2µm MIN MATTE TIN FULL PLATED
- 5 / 8 = 0.38µm GOLD/GXT
- 1.27µm Ni MIN UNDERPLATING

NOTES:


- HOUSING MAT'L : HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: BLACK.
- PIN MATERIAL : PHOSPHOR BRONZE.
- 12N MIN RETENTION IN EITHER DIRECTION.
- TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS PER ROW, $N \times 2.54 = 20.32\text{mm}$
- FOR STANDARD SELECTIVE GOLD PLATED PRODUCTS SEE DRAWINGS 54111 & 54121.
- OPTION LETTER :
 - = STANDARD PACKAGING IN POLYBAG
 - V = POLYBAGS PACKAGING FOR CUSTOMER DEDICATED PART
 - B = TUBE WITH PICK UP CAP AS AVAILABLE
- RETENTION IS APPLIED TO TWO ADJACENT PINS AT EACH END OF THE PRODUCT SEE SCHEMA 1
OMIT FROM PRODUCT NUMBER IF THIS FEATURE IS NOT APPLICABLE

8. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

- a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.
- b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR WITH A 1.6mm MIN THICK CIRCUIT BOARD.
- c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
- d - LEGAL STATEMENT: SEE GS-47-0004



SCHEMA 1
TWO RETENTION PIN AT EACH
END OF THE PRODUCT




OAL (OVERALL LENGTH)
REF

STACK HEIGHT

NOTE 3

DIM "B"



mat'l. code				surface		tolerance		projection	product family	
SEE NOTES				ISO 1302	ISO 406	ISO 1101	BSTIK			
lfr	ecn no	dr	date	tolerances unless otherwise specified					title	
FF	B-19782	AMA	14.12.18	angles	linear	x.x ±0.3			HEADER STR,DR DOUBLE BODY	
FG	B-20322	AMA	15.01.27			x.xx ±0.13				
FH	F-22479	BVE	15.11.12			x.xxx ±0.05				
FK	F-28617	DDE	17.11.27	dr	NIZZI P	94.05.05			dwg no	
				enrg	COMPAGNON J	95.12.05			sheet 1 of 4	
FD	B-19264	LMU	14.11.03	chr					size	
FE	B-19345	LMU	14.11.07	appd	JMC	95.12.05		76745		A3
								type		Drawing
sheet	revision	FK	CC	F	A					
index	sheet	1	2	3	4					



FCIconnect.com

Copyright FCI

form: A3

APPLICATION SPECIFIC

PIN STYLE	MATING LENGTH ±0.2	STACK HEIGHT ±0.25	"B" ±0.25	("OAL") REF
01	8.71	19.76	2.65	31.12
02	6.87	16.5	3.05	26.42
03	6.87	13.0	3.63	23.5
04	5.6	6.5	2.88	14.98
05	5.51	8.0	3.05	16.56
06	6.61	11.3	3.05	20.96
07	5.58	10.3	2.54	18.42
08	5.81	7.7	3.05	16.56
09	5.72	5.08	2.54	13.34
10	6.9	10.45	2.71	20.06
11	11.2	9.5	2.8	23.5
13	9.07	6.3	3.05	18.42
14	5.33	21.5	2.48	29.31
17	7.5	23.45	3.05	34.0
19	9.5	10.45	3.55	23.5
21	11.96	18.5	3.2	33.66
23	9.0	25.9	3.05	37.95
24	8.87	14.5	3.05	26.42
25	9.84	11.43	9.85	31.12
28	6.6	8.25	2.8	17.65
29	9.1	15.7	3.2	28.0
34	8.0	12.0	3.0	23.0
36	10.55	7.5	10.53	28.58
40	7.0	6.5	3.06	16.56
55	13.0	20.0	3.2	36.2
57	11.78	5.08	3.23	20.06
58	23.0	8.5	5.5	36.97
59	9.0	18.2	9.0	36.2
62	9.2	9.3	3.5	22.0
68	6.75	8.0	2.9	17.65
71	6.8	5.2	2.69	14.69
79	9.95	39.0	3.05	52.0
80	5.68	7.0	2.3	15.0
88	10.8	8.0	3.7	22.5
AN	10.0	29.0	3.0	42.0
BD	11.7	13.5	3.21	28.41
BM	11.5	11.5	3.04	26.04
BT	8.5	35.0	8.5	52.0
CB	9.0	30.0	3.0	42.0
CD	9.24	12.0	9.24	30.48

SEE SHEET 3

APPLICATION SPECIFIC

PIN STYLE	MATING LENGTH ±0.2	STACK HEIGHT ±0.25	"B" ±0.25	("OAL") REF
CF	8.25	16.0	8.25	32.5
CG	6.0	40.0	6.0	52.0
CH	11.02	12.0	3.02	26.04
CN	7.08	5.60	7.08	19.77
CP	9.50	7.00	2.41	18.91
CT	11.0	6.0	11.0	28.0
CU	9.75	13.0	9.75	32.5
CV	9.44	13.00	3.60	26.04
CW	5.00	36.00	5.00	46.00
CX	10.00	26.00	6.00	42.00
CY	10.9	18.20	10.9	40.00
CZ	5.5	23.00	5.50	34.00
DA	13.00	14.50	6.50	34.00
DB	12.75	8.50	12.75	34.00
DC	SEE SHEET 3			
DE	6.00	34.00	6.00	46.00
DF	9.12	7.80	9.12	26.04
DG	3.50	43.00	3.50	50.00
DH	6.50	8.00	6.50	21.00
DJ	5.80	17.75	5.80	29.31
DK	5.40	9.00	2.90	17.30
DL	9.00	8.50	6.00	23.50
DM	7.40	23.70	3.30	34.40
DN	7.40	12.10	3.30	22.80
DP	8.00	16.80	5.40	30.20
DR	6.40	15.00	6.40	27.80
DS	7.00	29.00	7.00	43.00
DT	9.80	27.40	9.80	47.00
DU	9.50	36.50	9.50	55.50
DV	9.30	6.30	5.80	22.00
DW	5.30	40.40	3.30	49.00

SEE SHEET 3

SEE SHEET 3


SEE SHEET 3

APPLICATION SPECIFIC

PIN STYLE	MATING LENGTH ±0.2	STACK HEIGHT ±0.25	"B" ±0.25	("OAL") REF
DX	6.50	12.50	6.50	25.50
DY	6.50	9.50	6.50	22.50
EA	6.65	32.30	3.05	42.00
EB	2.66	15.00	5.84	23.50
EC	10.00	39.60	2.40	52.00
ED	5.40	57.20	2.40	65.00
EF	5.84	46.50	3.05	55.40
EG	5.60	20.00	5.64	31.24
EH	4.60	15.00	1.50	21.10
EJ	9.26	5.08	9.26	23.60
EK	6.00	7.50	6.00	19.50
EL	6.00	12.30	4.10	22.40
EM	9.00	9.30	6.21	24.51
EN	5.75	26.90	5.75	38.40

mat'l. code		surface ISO 1302 ☒ ISO 406 ISO 1101		tolerance ISO 406 ISO 1101		projection 		product family BSTIK	
ltr		ecn no		dr		date		title	
CB		B-20322		AMA		15.01.27		HEADER STR,DR	
CC		F-28617		DDE		17.11.27		DOUBLE BODY	
BW		F11-0045		LMU		11.04.04		scale	
BX		F12-0090		JFA		12.12.07		enrg JMC	
BY		B-16665		LMU		14.01.06		chr	
CA		B-1345		LMU		14.11.07		appd JMC	
sheet		revision							
index		sheet							

dwg no		sheet 2 of 4		size	
76745				A3	
type		CUSTOMER		Drawing	



SPECIFICS PLATING AREA FOR PART NUMBERS :

P/N 76745-1CH-10LF

P/N 76745-1CH-18LF

P/N 76745-579R24LF

P/N 76745-579R30LF

P/N 76745-1CU-20LF

P/N 76745-1DF-26LF

AREA "A" & "B" : GOLD/GXT PLATING AREA



FCIconnect.com

Copyright FCI

mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406 ISO 1101		BSTIK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
A	F06-110	LMU	06.01.26	angles	linear	mm	HEADER STR,DR
B	F06-0196	LMU	06.06.20				DOUBLE BODY
C	F07-0266	J.CO	07.10.15			scale	
D	F12-0023	LMU	12.06.06	dr	L.MULIN	06.01.31	dwg no
E	F12-0090	JFA	12.12.07	enr	J.COMPAGNON	06.01.31	sheet 3 of 4
F	B-16665	LMU	14..01.06	chr			size
				appd	JMC	06.01.31	76745
							A3
sheet	revision						type
index	sheet						CUSTOMER Drawing

form: A3



SPECIFIC PRODUCT NUMBER

76745-3DCA04LF

— RoHS COMPLIANT
 — TOTAL NB OF POS
 — PACKAGING TYPE, SEE NOTE 1
 — PIN STYLE
 — PLATING
 3 = 2µm MATTE TIN
 OVER 1.27µm Ni MIN

NOTES :

1. PACKAGING : A = TAPE & REEL PACKAGING
WITH PICK UP CAP INSTALLED
SEE TA 840
2. PRODUCT COMPATIBLE WITH REFLOW PROCESS.
255°C PEAK TEMPERATURE 10-40 SECONDES IN
A CONVECTION, INFRA-RED OR VAPOR PHASE



mat'l. code				surface	tolerance	projection	product family			
lfr	ecn no	dr	date	ISO 1302	ISO 406	ISO 1101	BSTIK			
A	B-16665	LMU	14.01.06	tolerances unless otherwise specified			title			
				angles	linear	mm	HEADER STR,DR			
						scale	DOUBLE BODY			
				dr	L.MULIN	13.02.18	dwg no	sheet 4 of 4	size	
				engr	J.COMPAGNON	13.02.18	76745		A3	
				chr						
				appd	JMC	13.02.18	type		CUSTOMER Drawing	
sheet	revision									
index	sheet									