

4		3		2		1			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION					
2010									
© COPYRIGHT 2010				BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.					
LOC		DIST		REVISIONS					
E		B		P	LTR	DESCRIPTION	DATE	DWN	APVD
					BA	NEW RELEASE	05AUG2010	PT	St.P

FOR FURTHER INFORMATION SEE DATA SHEET FOR
SERIES SC - AXIAL LEADED POWER INDUCTORS

Top View: $\varnothing 2.8 \text{ MAX}$

Side View: 25.0 MIN, 7.0 MAX, 25.0 MIN

Detail View: $\varnothing 0.50$

RoHS Compliant

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN	05AUG2010	
mm		CHK	PARUSURAM.T	
		APVD	ALLAN.P	
		PRODUCT SPEC	STEPHEN.P	
		APPLICATION SPEC		
		WEIGHT		
MATERIAL	FINISH	CUSTOMER DRAWING		

Tyco Electronics Corporation		Dorcan, Swindon, SN3 5HH	
NAME			
AXIAL LEADED POWER INDUCTORS			
SERIES SC30			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1624034	-
SCALE		SHEET	OF
10:1		1	1
		REV	BA

AMP 1470-19 REV 31MAR2000

Pro/ENGINEER DRAWING