





LOC		DIST		REVISIONS					
AD	00	P	LTR	DESCRIPTION		DATE	DWN	APVD	
			N1	REV PER ECO-07-002356		01MAR2007	BC	AS	
			N2	REVISED PER ECO-09-021826		08JAN10	KK	AEG	



RECOMMENDED P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. K. SEIFRIED CHK F. KIBLER APVD -	04/09/90 8-17-92 -	Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME		PRODUCT SPEC	
0 PLC ± -	1 PLC ± -	APPLICATION SPEC		SIZE	
2 PLC ± -	3 PLC ± 0.13 [.005]	CAGE CODE		DRAWING NO	
4 PLC ± -	ANGLES ± -	WEIGHT		RESTRICTED TO	
MATERIAL 1 2	FINISH 3	A1 00779		C=532430	
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 2	REV N2

LOC		DIST		REVISIONS					
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					—	SEE SHEET 1	—	—	—

- 1

HOUSING MATERIAL: THERMOPLASTIC, COLOR—NATURAL.
- 2

CONTACT MATERIAL: PHOSPHOR BRONZE.
- 3

CONTACT FINISH: .00127—.00254 [.000050—.000100] NICKEL UNDERPLATE ALL OVER; .00076 [.000030] GOLD PLATE IN CONTACT AREA, TIN—LEAD PLATED POSTS.
- 4

SOLDER PIN POST RECOMMENDED P.C. BOARD HOLE SIZES ARE 0.94—1.09 [.037—.043]; RECOMMENDED PAD DIA IS 1.52 [.060].
- 5

DIMENSIONS IN BRACKETS ARE IN INCHES.
- 6

PART NUMBER IS OBSOLETE.
- 7

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

6	251.46 [9.900]	—99	255.27 [10.050]	265.43 [10.450]	273.05 [10.750]	—200	1—532430—9
6	238.76 [9.400]	—94	242.57 [9.550]	252.73 [9.950]	260.35 [10.250]	—190	1—532430—8
6	226.06 [8.900]	—89	229.87 [9.050]	240.03 [9.450]	247.65 [9.750]	—180	1—532430—7
6	213.36 [8.400]	—84	217.17 [8.550]	227.33 [8.950]	234.95 [9.250]	—170	1—532430—6
6	200.66 [7.900]	—79	204.47 [8.050]	214.63 [8.450]	222.25 [8.750]	—160	1—532430—5
	187.96 [7.400]	74	191.77 [7.550]	201.93 [7.950]	209.55 [8.250]	150	1—532430—4
6	175.26 [6.900]	69	179.07 [7.050]	189.23 [7.450]	196.85 [7.750]	140	1—532430—3
6	162.56 [6.400]	—64	166.37 [6.550]	176.53 [6.950]	184.15 [7.250]	—130	1—532430—2
6	149.86 [5.900]	—59	153.67 [6.050]	163.83 [6.450]	171.45 [6.750]	—120	1—532430—1
	137.16 [5.400]	54	140.97 [5.550]	151.13 [5.950]	158.75 [6.250]	110	1—532430—0
	124.46 [4.900]	49	128.27 [5.050]	138.43 [5.450]	146.05 [5.750]	100	532430—9
6	111.76 [4.400]	—44	115.57 [4.550]	125.73 [4.950]	133.35 [5.250]	—90	532430—8
6	99.06 [3.900]	39	102.87 [4.050]	113.03 [4.450]	120.65 [4.750]	80	532430—7
6	86.36 [3.400]	—34	90.17 [3.550]	100.33 [3.950]	107.95 [4.250]	—70	532430—6
	73.66 [2.900]	29	77.47 [3.050]	87.63 [3.450]	95.25 [3.750]	60	532430—5
6	60.96 [2.400]	—24	64.77 [2.550]	74.93 [2.950]	82.55 [3.250]	—50	532430—4
	48.26 [1.900]	19	52.07 [2.050]	62.23 [2.450]	69.85 [2.750]	40	532430—3
7	35.56 [1.400]	14	39.37 [1.550]	49.53 [1.950]	57.15 [2.250]	30	532430—2
6	22.86 [.900]	—9	26.67 [1.050]	36.83 [1.450]	44.45 [1.750]	—20	532430—1
	E	D	C	B	A	POSN	PART NUMBER

7

OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. K. SEIFRIED 8-17-92	04/09/90 CHK F. KIBLER		Tyco Electronics Corporation Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
0 PLC ± .— 1 PLC ± .— 2 PLC ± .— 3 PLC ± 0.13 [.005] 4 PLC ± .— ANGLES ± .—		PRODUCT SPEC — APPLICATION SPEC —		HDI, 2 ROW, PIN ASSEMBLY, 4.83 [.190] LONG SOLDER PINS, .00076 [.000030] GOLD PLATE		
MATERIAL 1 2		FINISH 3		SIZE A1		
WEIGHT —		CAGE CODE 00779		DRAWING NO 532430		
CUSTOMER DRAWING				RESTRICTED TO —		
SCALE 4:1				SHEET 2 OF 2		
REV N2						