


REVISIONS			
P	LTR	DATE	OWN APVD
0		28APR05	HXF DF

D




C

NOTES:

1. HIROSE COMPATIBLE
2. 100% ELECTRICAL TESTING FOR: CONTINUITY AND SHORTS. HI-POT AT 150 VDC FOR 100ms
FREQUENCY RANGE: DC TO 6 GHz
VSWR 1.4:1 MAX
3. PRODUCT RATINGS:
TEMPERATURE: -40 TO +90 DEG.C
VOLTAGE: 60 VAC
CHARACTERISTIC IMPEDANCE: 50 OHMS
UMCC MATING DURABILITY: 30 CYCLES
MMCX MATING DURABILITY: 500 CYCLES

B



B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
MM		0 PLC	±
		1 PLC	±
		2 PLC	±
		3 PLC	±
		4 PLC	±
		ANGLES	±
MATERIAL	-	FINISH	-
WEIGHT		RESTRICTED TO	
-		-	

DMN	Hao. Xiangfeng	28APR05	
CHK	Paul Zhou	28APR05	
APVD	DENVER WILSON	13JUN05	
PRODUCT SPEC			
-			
APPLICATION SPEC			
-			

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A4	00779	1-1750110-0	-

SCALE	1:1	SHEET	1 of 1	REV	0
-------	-----	-------	--------	-----	---

A