




REMARK:1. AMONG NO.1, NO.5 AND NO.6 MUST WITHSTAND 15 IN-LBS TORQUE AFTER STAKING OPERATION
2. REMARK 1 IS MAINTAINED BY STAKING SHOWN ON THE DRAWING WITHOUT PUNCTURING NO.5

STAKE IN 6 PLACES
EQUALLY SPACED 60°
APART

FORMING

STAMP (IF ANY)

1/2-28UNEF-2A

11

19

32.5

7

16 HEX

8

13

12.1

RECOMMENDED
MOUNTING HOLE

NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)

- 1. BRASS PER QQ-B-626
- 2. BRASS PER QQ-B-613
- 3. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
- 4. PHOSPHOR BRONZE PER QQ-B-750
- 5. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE

1. MAX. PANEL THICKNESS=4.5mm

8	HEX NUT	NOTE 1	NOTE 3	1	HN16-1/2-28X28	DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED TOLERANCES 0.5-6 = ±0.2 6-30 = ±0.4 30-120 = ±0.6 120-315 = ±1 315-1000 = ±1.6 1000-2000 = ±2.4				PART NO. B7771B1-ND3G-50		Amphenol			
7	LOCK WASHER	NOTE 2	NOTE 3	1	LW-16/13X05					APPROVED				DATE 10-11-01'	
6	HOUSING	NOTE 1	NOTE 3	1	B7925-6-C					CHECKED				DATE 10-11-01'	
5	BODY	NOTE 1	NOTE 3	1	B7925-5					DRAWN				DATE 10-11-01'	
4	INSULATOR	DELTRIN	NATURAL	1	B7925-4-B					TITLE BNC FEMALE TO FEMALE BULKHEAD ISOLATED ADAPTOR					
3	CONTACT PIN	NOTE 4	NOTE 5	1	B7900-4	DRAWING NO. KJ-B7771B1-ND3G-50									
2	INSULATOR	DELTRIN	NATURAL	2	B7996ZZ-3-50							ITEM NO.			
1	BODY	NOTE 1	NOTE 3	1	B7925-1-D										
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.	SCALE	2.5/1	ISSUE	A	FILE NO.					