


Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION



9778 Coax - Single-Conductor, High-Impedance Cable

For more Information
please call

1-800-Belden1



Description:

20 AWG stranded (26x34) high-conductivity TC conductor, EPDM rubber insulation, conductive textile (100%) plus TC spiral shields (75% coverage), paper tape, CPE jacket.

Physical Characteristics (Overall)

Conductor

AWG:

#	Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1		20	26x34	High Conductivity TC - Tinned Copper	.037

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)	Dia. (in.)
EPDM - Ethylene Propylene Diene Monomer Rubber	.040	.117

Outer Shield

Outer Shield Material:

Layer #	Type	Outer Shield Material	Coverage (%)
1	Serve	Conductive Textile	100
2	Spiral Serve	TC - Tinned Copper	75
3	Tape	Paper	100

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
Neoprene	.050

Overall Cable

Overall Nominal Diameter: 0.235 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +60°C

Non-UL Temperature Rating: 60°C

Bulk Cable Weight: 34 lbs/1000 ft.

Max. Recommended Pulling Tension: 13 lbs.

Min. Bend Radius/Minor Axis: 2.400 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

9778 Coax - Single-Conductor, High-Impedance Cable

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
40

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
45

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
10.2

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
11.6

Max. Operating Voltage - Non-UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
4 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9778 0101000	1,000 FT	37.000 LB	CHROME		1 #20 EPDM SH CPE

Revision Number: 2 Revision Date: 03-25-2009

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9778 0101000](#)