

# MAX6225/MAX6241/MAX6250

## Low-Noise, Precision, +2.5V/+4.096V/+5V Voltage References

### General Description

The MAX6225/MAX6241/MAX6250 are low-noise, precision voltage references with extremely low 1ppm/°C temperature coefficients and excellent  $\pm 0.02\%$  initial accuracy. These devices feature buried-zener technology for lowest noise performance. Load-regulation specifications are guaranteed for source and sink currents up to 15mA. Excellent line and load regulation and low output impedance at high frequency make them ideal for high-resolution data-conversion systems up to 16 bits.

The MAX6225 is set for 2.500V output, the MAX6241 is set for 4.096V output, and the MAX6250 is set for 5.000V output. All three devices provide for the option of external trimming and noise reduction.

### Applications

- High-Resolution Analog-to-Digital and Digital-to-Analog Converters
- High-Accuracy Reference Standard
- High-Accuracy Industrial and Process Control
- Digital Voltmeters
- ATE Equipment
- Precision Current Sources

### Features

- Low 1.0ppm/°C Temperature Coefficient
- Very Low 1.5 $\mu$ V<sub>P-P</sub> Noise (0.1Hz to 10Hz)
- $\pm 0.02\%$  Initial Accuracy
- $\pm 15$ mA Output Source and Sink Current
- Low, 18mW Power Consumption (MAX6225)
- Industry-Standard Pinout
- Optional Noise Reduction and Voltage Trim
- Excellent Transient Response
- 8-Pin SO Package Available
- Low 20ppm/1000h Long-Term Stability
- Stable for All Capacitive Loads

### Ordering Information



| PART         | TEMP RANGE      | PIN-PACKAGE   | MAX TEMP CO (ppm/°C) |
|--------------|-----------------|---------------|----------------------|
| MAX6225ACPA+ | 0°C to +70°C    | 8 Plastic DIP | 2.0                  |
| MAX6225BCPA+ | 0°C to +70°C    | 8 Plastic DIP | 5.0                  |
| MAX6225ACSA+ | 0°C to +70°C    | 8 SO          | 2.0                  |
| MAX6225BCSA+ | 0°C to +70°C    | 8 SO          | 5.0                  |
| MAX6225AEPA+ | -40°C to +85°C  | 8 Plastic DIP | 3.0                  |
| MAX6225BEPA+ | -40°C to +85°C  | 8 Plastic DIP | 7.0                  |
| MAX6225AES+  | -40°C to +85°C  | 8 SO          | 5.0                  |
| MAX6225BES+  | -40°C to +85°C  | 8 SO          | 7.0                  |
| MAX6225AMJA  | -55°C to +125°C | 8 Cerdip      | 5.0                  |
| MAX6225BMJA  | -55°C to +125°C | 8 Cerdip      | 8.0                  |

+Denotes a lead(Pb)-free/RoHS-compliant package.

Ordering Information appears at end of data sheet.

### Pin Configuration

### Typical Operating Circuit



## Absolute Maximum Ratings

(Voltages Referenced to GND)

|                                                                 |               |                                                       |                 |
|-----------------------------------------------------------------|---------------|-------------------------------------------------------|-----------------|
| (Voltages Referenced to GND)                                    |               | 8-Pin CERDIP (derate 8.00mW/°C above +70°C).....640mW |                 |
| IN.....                                                         | -0.3V to +40V | Operating Temperature Ranges                          |                 |
| OUT, TRIM .....                                                 | -0.3V to +12V | MAX62__ _C_ A.....                                    | 0°C to +70°C    |
| NR .....                                                        | -0.3V to +6V  | MAX62__ _E_ A.....                                    | -40°C to +85°C  |
| OUT Short-Circuit to GND Duration (V <sub>IN</sub> ≤ 12V).....  | Continuous    | MAX62__ _MJA.....                                     | -55°C to +125°C |
| OUT Short-Circuit to GND Duration (V <sub>IN</sub> ≤ 40V) ..... | 5s            | Storage Temperature Range .....                       | -65°C to +150°C |
| OUT Short-Circuit to IN Duration (V <sub>IN</sub> ≤ 12V) .....  | Continuous    | Lead Temperature (soldering, 10s).....                | +300°C          |
| Continuous Power Dissipation (T <sub>A</sub> = +70°C)           |               | Soldering Temperature (reflow)                        |                 |
| 8-Pin Plastic DIP (derate 9.09mW/°C above +70°C)....727mW       |               | 8 PDIP, 8 SOIC.....                                   | +260°C          |
| 8-Pin SO (derate 5.88mW/°C above +70°C).....471mW               |               | 8 CDIP.....                                           | +240°C          |

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

## Electrical Characteristics—MAX6225

( $V_{IN} = +10V$ ,  $I_{OUT} = 0mA$ ,  $T_A = T_{MIN}$  to  $T_{MAX}$ , unless otherwise noted. Typical values are at  $T_A = +25^\circ\text{C}$ .)

| PARAMETER                                       | SYMBOL                           | CONDITIONS                 | $T_A$   | MIN   | TYP   | MAX   | UNITS  |
|-------------------------------------------------|----------------------------------|----------------------------|---------|-------|-------|-------|--------|
| Input Voltage Range                             | $V_{IN}$                         |                            | C, E, M | 8     |       | 36    | V      |
| Output Voltage                                  | $V_{OUT}$                        | MAX6225A                   | +25°C   | 2.499 | 2.500 | 2.501 | V      |
|                                                 |                                  | MAX6225B                   | +25°C   | 2.497 | 2.500 | 2.503 |        |
| Output Voltage Temperature Coefficient (Note 1) | $TCV_{OUT}$                      | MAX6225AC_A                | C       |       | 1.0   | 2.0   | ppm/°C |
|                                                 |                                  | MAX6225AE_A                | E       |       | 1.5   | 3.0   |        |
|                                                 |                                  | MAX6225AMJA                | M       |       | 2.0   | 5.0   |        |
|                                                 |                                  | MAX6225BC_A                | C       |       | 2.5   | 5.0   |        |
|                                                 |                                  | MAX6225BE_A                | E       |       | 2.5   | 7.0   |        |
|                                                 |                                  | MAX6225BMJA                | M       |       | 2.5   | 8.0   |        |
| Line Regulation (Note 2)                        | $\Delta V_{OUT} / \Delta V_{IN}$ | $8V \leq V_{IN} \leq 10V$  | +25°C   |       | 10    | 18    | ppm/V  |
|                                                 |                                  |                            | C       |       |       | 30    |        |
|                                                 |                                  |                            | E       |       |       | 35    |        |
|                                                 |                                  |                            | M       |       |       | 45    |        |
|                                                 |                                  | $10V \leq V_{IN} \leq 36V$ | +25°C   |       | 2     | 5     |        |
|                                                 |                                  |                            | C       |       |       | 7     |        |
|                                                 |                                  |                            | E       |       |       | 8     |        |
|                                                 |                                  |                            | M       |       |       | 10    |        |

**Electrical Characteristics—MAX6225 (continued)**(V<sub>IN</sub> = +10V, I<sub>OUT</sub> = 0mA, T<sub>A</sub> = T<sub>MIN</sub> to T<sub>MAX</sub>, unless otherwise noted. Typical values are at T<sub>A</sub> = +25°C.)

| PARAMETER                     | SYMBOL                            | CONDITIONS                              | T <sub>A</sub> | MIN | TYP | MAX | UNITS             |
|-------------------------------|-----------------------------------|-----------------------------------------|----------------|-----|-----|-----|-------------------|
| Load Regulation (Note 2)      | $\Delta V_{OUT} / \Delta I_{OUT}$ | Sourcing: 0mA ≤ I <sub>OUT</sub> ≤ 15mA | C              |     | 1   | 6   | ppm/mA            |
|                               |                                   |                                         | E              |     | 1   | 7   |                   |
|                               |                                   |                                         | M              |     | 3   | 15  |                   |
|                               |                                   | Sinking: -15mA ≤ I <sub>OUT</sub> ≤ 0mA | C              |     | 1   | 6   |                   |
|                               |                                   |                                         | E              |     | 1   | 7   |                   |
|                               |                                   |                                         | M              |     | 10  | 30  |                   |
| Supply Current                | I <sub>IN</sub>                   |                                         | +25°C          |     | 1.8 | 2.7 | mA                |
|                               |                                   |                                         | C, E, M        |     |     | 3.0 |                   |
| Trim-Adjustment Range         | ΔV <sub>OUT</sub>                 | Figure 1                                | C, E, M        | ±15 | ±25 |     | mV                |
| Turn-On Settling Time         | t <sub>ON</sub>                   | To ±0.01% of final value                | +25°C          |     | 5   |     | μs                |
| Output Noise Voltage (Note 3) | en                                | 0.1Hz ≤ f ≤ 10Hz                        | +25°C          |     | 1.5 |     | μV <sub>P-P</sub> |
|                               |                                   | 10Hz ≤ f ≤ 1kHz                         | +25°C          |     | 1.3 | 2.8 | μV <sub>RMS</sub> |
| Temperature Hysteresis        |                                   | (Note 4)                                | +25°C          |     | 20  |     | ppm               |
| Long-Term Stability           | ΔV <sub>OUT</sub> / t             |                                         | +25°C          |     | 20  |     | ppm/<br>1000h     |

## Electrical Characteristics—MAX6241

(V<sub>IN</sub> = +10V, I<sub>OUT</sub> = 0mA, T<sub>A</sub> = T<sub>MIN</sub> to T<sub>MAX</sub>, unless otherwise noted. Typical values are at T<sub>A</sub> = +25°C.)

| PARAMETER                                       | SYMBOL                          | CONDITIONS                              | T <sub>A</sub> | MIN   | TYP   | MAX   | UNITS             |
|-------------------------------------------------|---------------------------------|-----------------------------------------|----------------|-------|-------|-------|-------------------|
| Input Voltage Range                             | V <sub>IN</sub>                 |                                         | C, E, M        | 8     |       | 36    | V                 |
| Output Voltage                                  | V <sub>OUT</sub>                | MAX6241A                                | +25°C          | 4.095 | 4.096 | 4.097 | V                 |
|                                                 |                                 | MAX6241B                                | +25°C          | 4.092 | 4.096 | 4.100 |                   |
| Output Voltage Temperature Coefficient (Note 1) | TCV <sub>OUT</sub>              | MAX6241AC_A                             | C              |       | 1.0   | 2.0   | ppm/°C            |
|                                                 |                                 | MAX6241AE_A                             | E              |       | 1.5   | 3.0   |                   |
|                                                 |                                 | MAX6241AMJA                             | M              |       | 2.0   | 5.0   |                   |
|                                                 |                                 | MAX6241BC_A                             | C              |       | 2.5   | 5.0   |                   |
|                                                 |                                 | MAX6241BE_A                             | E              |       | 2.5   | 7.0   |                   |
|                                                 |                                 | MAX6241BMJA                             | M              |       | 2.5   | 8.0   |                   |
| Line Regulation (Note 2)                        | $\Delta V_{OUT}/\Delta V_{IN}$  | 8V ≤ V <sub>IN</sub> ≤ 10V              | +25°C          |       | 10    | 18    | ppm/V             |
|                                                 |                                 |                                         | C              |       |       | 30    |                   |
|                                                 |                                 |                                         | E              |       |       | 35    |                   |
|                                                 |                                 |                                         | M              |       |       | 45    |                   |
|                                                 |                                 | 10V ≤ V <sub>IN</sub> ≤ 36V             | +25°C          |       | 2     | 5     |                   |
|                                                 |                                 |                                         | C              |       |       | 7     |                   |
|                                                 |                                 |                                         | E              |       |       | 8     |                   |
|                                                 |                                 |                                         | M              |       |       | 10    |                   |
| Load Regulation (Note 2)                        | $\Delta V_{OUT}/\Delta I_{OUT}$ | Sourcing: 0mA ≤ I <sub>OUT</sub> ≤ 15mA | C              |       | 1     | 6     | ppm/mA            |
|                                                 |                                 |                                         | E              |       | 1     | 7     |                   |
|                                                 |                                 |                                         | M              |       | 3     | 9     |                   |
|                                                 |                                 | Sinking: -15mA ≤ I <sub>OUT</sub> ≤ 0mA | C              |       | 1     | 6     |                   |
|                                                 |                                 |                                         | E              |       | 1     | 7     |                   |
|                                                 |                                 |                                         | M              |       | 7     | 18    |                   |
| Supply Current                                  | I <sub>IN</sub>                 |                                         | +25°C          |       | 1.9   | 2.9   | mA                |
|                                                 |                                 |                                         | C, E, M        |       |       | 3.2   |                   |
| Trim-Adjustment Range                           | ΔV <sub>OUT</sub>               | Figure 1                                | C, E, M        | ±24   | ±40   |       | mV                |
| Turn-On Settling Time                           | t <sub>ON</sub>                 | To ±0.01% of final value                | +25°C          |       | 8     |       | μs                |
| Output Noise Voltage (Note 3)                   | en                              | 0.1Hz ≤ f ≤ 10Hz                        | +25°C          |       | 2.4   |       | μV <sub>P-P</sub> |
|                                                 |                                 | 10Hz ≤ f ≤ 1kHz                         | +25°C          |       | 2.0   | 4.0   | μV <sub>RMS</sub> |
| Temperature Hysteresis                          |                                 | (Note 4)                                | +25°C          |       | 20    |       | ppm               |
| Long-Term Stability                             | ΔV <sub>OUT</sub> /t            |                                         | +25°C          |       | 20    |       | ppm/1000h         |


## Electrical Characteristics—MAX6250

(V<sub>IN</sub> = +10V, I<sub>OUT</sub> = 0mA, T<sub>A</sub> = T<sub>MIN</sub> to T<sub>MAX</sub>, unless otherwise noted. Typical values are at T<sub>A</sub> = +25°C.)










| PARAMETER                                       | SYMBOL                            | CONDITIONS                              | T <sub>A</sub> | MIN   | TYP   | MAX   | UNITS             |
|-------------------------------------------------|-----------------------------------|-----------------------------------------|----------------|-------|-------|-------|-------------------|
| Input Voltage Range                             | V <sub>IN</sub>                   |                                         | C, E, M        | 8     |       | 36    | V                 |
| Output Voltage                                  | V <sub>OUT</sub>                  | MAX6250A                                | +25°C          | 4.999 | 5.000 | 5.001 | V                 |
|                                                 |                                   | MAX6250B                                | +25°C          | 4.995 | 5.000 | 5.005 |                   |
| Output Voltage Temperature Coefficient (Note 1) | TCV <sub>OUT</sub>                | MAX6250AC_A                             | C              |       | 1.0   | 2.0   | ppm/°C            |
|                                                 |                                   | MAX6250AE_A                             | E              |       | 1.5   | 3.0   |                   |
|                                                 |                                   | MAX6250AMJA                             | M              |       | 2.0   | 5.0   |                   |
|                                                 |                                   | MAX6250BC_A                             | C              |       | 2.5   | 5.0   |                   |
|                                                 |                                   | MAX6250BE_A                             | E              |       | 2.5   | 7.0   |                   |
|                                                 |                                   | MAX6250BMJA                             | M              |       | 2.5   | 8.0   |                   |
| Line Regulation (Note 2)                        | $\Delta V_{OUT} / \Delta V_{IN}$  | 8V ≤ V <sub>IN</sub> ≤ 10V              | +25°C          |       | 10    | 18    | ppm/V             |
|                                                 |                                   |                                         | C              |       |       | 30    |                   |
|                                                 |                                   |                                         | E              |       |       | 35    |                   |
|                                                 |                                   |                                         | M              |       |       | 45    |                   |
|                                                 |                                   | 10V ≤ V <sub>IN</sub> ≤ 36V             | +25°C          |       | 2     | 5     |                   |
|                                                 |                                   |                                         | C              |       |       | 7     |                   |
|                                                 |                                   |                                         | E              |       |       | 8     |                   |
|                                                 |                                   |                                         | M              |       |       | 10    |                   |
| Load Regulation (Note 2)                        | $\Delta V_{OUT} / \Delta I_{OUT}$ | Sourcing: 0mA ≤ I <sub>OUT</sub> ≤ 15mA | C              |       | 1     | 6     | ppm/mA            |
|                                                 |                                   |                                         | E              |       | 1     | 7     |                   |
|                                                 |                                   |                                         | M              |       | 3     | 9     |                   |
|                                                 |                                   | Sinking: -15mA ≤ I <sub>OUT</sub> ≤ 0mA | C              |       | 1     | 6     |                   |
|                                                 |                                   |                                         | E              |       | 1     | 7     |                   |
|                                                 |                                   |                                         | M              |       | 6     | 15    |                   |
| Supply Current                                  | I <sub>IN</sub>                   |                                         | +25°C          |       | 2.0   | 3.0   | mA                |
|                                                 |                                   |                                         | C, E, M        |       |       | 3.3   |                   |
| Trim-Adjustment Range                           | ΔV <sub>OUT</sub>                 | Figure 1                                | C, E, M        | ±30   | ±50   |       | mV                |
| Turn-On Settling Time                           | t <sub>ON</sub>                   | To ±0.01% of final value                | +25°C          |       | 10    |       | μs                |
| Output Noise Voltage (Note 3)                   | en                                | 0.1Hz ≤ f ≤ 10Hz                        | +25°C          |       | 3.0   |       | μV <sub>P-P</sub> |
|                                                 |                                   | 10Hz ≤ f ≤ 1kHz                         | +25°C          |       | 2.5   | 5.0   | μV <sub>RMS</sub> |
| Temperature Hysteresis                          |                                   | (Note 4)                                | +25°C          |       | 20    |       | ppm               |
| Long-Term Stability                             | ΔV <sub>OUT</sub> /t              |                                         | +25°C          |       | 20    |       | ppm/1000h         |

**Note 1:** Temperature coefficient is measured by the box method; i.e., the maximum ΔV<sub>OUT</sub> is divided by ΔT × V<sub>OUT</sub>.**Note 2:** Line regulation (ΔV<sub>OUT</sub> / (V<sub>OUT</sub> × ΔV<sub>IN</sub>)) and load regulation (ΔV<sub>OUT</sub> / (V<sub>OUT</sub> × ΔI<sub>OUT</sub>)) are measured with pulses and do not include output voltage changes due to die-temperature changes.**Note 3:** Noise specifications are 100% tested for the 10Hz to 1kHz bandwidth. Contact factory for 100% noise testing in the 0.1Hz to 10Hz bandwidth.**Note 4:** Temperature hysteresis is specified at T<sub>A</sub> = +25°C by measuring V<sub>OUT</sub> before and after changing temperature by +25°C using the PDIP package.

## Typical Operating Characteristics

(V<sub>IN</sub> = 10V, I<sub>OUT</sub> = 0mA, T<sub>A</sub> = +25°C, unless otherwise noted.)


## Typical Operating Characteristics (continued)

(V<sub>IN</sub> = 10V, I<sub>OUT</sub> = 0mA, T<sub>A</sub> = +25°C, unless otherwise noted.)


## Typical Operating Characteristics (continued)

(V<sub>IN</sub> = 10V, I<sub>OUT</sub> = 0mA, T<sub>A</sub> = +25°C, unless otherwise noted.)





LOAD-TRANSIENT RESPONSE (SOURCING)



LOAD-TRANSIENT RESPONSE (SINKING)



LOAD-TRANSIENT RESPONSE

MAX6225  
TURN-ON AND TURN-OFF TRANSIENT RESPONSEMAX6241  
TURN-ON AND TURN-OFF TRANSIENT RESPONSEMAX6250  
TURN-ON AND TURN-OFF TRANSIENT RESPONSE

## Pin Description

| PIN     | NAME | FUNCTION                                                                                                        |
|---------|------|-----------------------------------------------------------------------------------------------------------------|
| 1, 7, 8 | I.C. | Internally Connected. <b>Do not use.</b>                                                                        |
| 2       | IN   | Positive Power-Supply Input                                                                                     |
| 3       | NR   | Noise Reduction. Optional capacitor connection for wideband noise reduction. Leave open if not used (Figure 2). |
| 4       | GND  | Ground                                                                                                          |
| 5       | TRIM | External Trim Input. Allows $\pm 1\%$ output adjustment (Figure 1). Leave open if not used.                     |
| 6       | OUT  | Voltage Reference Output                                                                                        |

## Detailed Description

### Temperature Stability

The MAX6225/MAX6241/MAX6250 are highly stable, low-noise voltage references that use a low-power temperature-compensation scheme to achieve laboratory-standard temperature stability. This produces a nearly flat temperature curve, yet does not require the power associated with heated references.

The output voltage can be trimmed a minimum of 0.6% by connecting a 10k $\Omega$  potentiometer between OUT and GND, and connecting its tap to the TRIM pin, as shown in Figure 1. The external trimming does not affect temperature stability.




Figure 1. Output Voltage Adjustment

### Noise Reduction

To augment wideband noise reduction, add a 1 $\mu$ F capacitor to the NR pin (Figure 2). Larger values do not improve noise appreciably (see *Typical Operating Characteristics*).

Noise in the power-supply input can affect output noise, but can be reduced by adding an optional bypass capacitor to the IN pin and GND.

### Bypassing

The MAX6225/MAX6241/MAX6250 are stable with capacitive load values from 0 $\mu$ F to 100 $\mu$ F, for all values of load current. Adding an output bypass capacitor can help reduce noise and output glitching caused by load transients.

## Applications Information

### Negative Regulator

Figure 3 shows how both a +5V and -5V precision reference can be obtained from a single unregulated +5V supply. A MAX681 generates approximately  $\pm 9$ V to operate the MAX6250 reference and MAX432 inverting amplifier. The +5V is inverted by the MAX432 chopper-stabilized amplifier. Resistor R1 is optional, and may be used to trim the  $\pm 5$ V references. R2 and R4 should be matched, both in absolute resistance and temperature coefficient. R3 is optional, and is adjusted to set the -5V reference.




Figure 2. Noise-Reduction Capacitor




Figure 3. +5V and -5V References from a Single +5V Supply

## Ordering Information (continued)

| PART                 | TEMP RANGE      | PIN-PACKAGE   | MAX TEMPCO (ppm/°C) |
|----------------------|-----------------|---------------|---------------------|
| <b>MAX6241</b> ACPA+ | 0°C to +70°C    | 8 Plastic DIP | 2.0                 |
| MAX6241BCPA+         | 0°C to +70°C    | 8 Plastic DIP | 5.0                 |
| MAX6241ACSA+         | 0°C to +70°C    | 8 SO          | 2.0                 |
| MAX6241BCSA+         | 0°C to +70°C    | 8 SO          | 5.0                 |
| MAX6241AEPA+         | -40°C to +85°C  | 8 Plastic DIP | 3.0                 |
| MAX6241BEPA+         | -40°C to +85°C  | 8 Plastic DIP | 7.0                 |
| MAX6241AESA+         | -40°C to +85°C  | 8 SO          | 3.0                 |
| MAX6241BESA+         | -40°C to +85°C  | 8 SO          | 7.0                 |
| MAX6241AMJA          | -55°C to +125°C | 8 CERDIP      | 5.0                 |
| MAX6241BMJA          | -55°C to +125°C | 8 CERDIP      | 8.0                 |
| <b>MAX6250</b> ACPA+ | 0°C to +70°C    | 8 Plastic DIP | 2.0                 |
| MAX6250BCPA+         | 0°C to +70°C    | 8 Plastic DIP | 5.0                 |
| MAX6250ACSA+         | 0°C to +70°C    | 8 SO          | 2.0                 |
| MAX6250BCSA+         | 0°C to +70°C    | 8 SO          | 5.0                 |
| MAX6250AEPA+         | -40°C to +85°C  | 8 Plastic DIP | 3.0                 |
| MAX6250BEPA+         | -40°C to +85°C  | 8 Plastic DIP | 7.0                 |
| MAX6250AESA+         | -40°C to +85°C  | 8 SO          | 3.0                 |
| MAX6250BESA+         | -40°C to +85°C  | 8 SO          | 7.0                 |
| MAX6250AMJA          | -55°C to +125°C | 8 CERDIP      | 5.0                 |
| MAX6250BMJA          | -55°C to +125°C | 8 CERDIP      | 8.0                 |

+Denotes a lead(Pb)-free/RoHS-compliant package.

## Chip Information

PROCESS: CMOS

## Package Information

For the latest package outline information and land patterns (footprints), go to [www.maximintegrated.com/packages](http://www.maximintegrated.com/packages). Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

| PACKAGE TYPE | PACKAGE CODE | OUTLINE NO.             | LAND PATTERN NO.        |
|--------------|--------------|-------------------------|-------------------------|
| 8 SO         | S8+5         | <a href="#">21-0041</a> | <a href="#">90-0096</a> |
| 8 PDIP       | P8+3         | <a href="#">21-0043</a> | -                       |
| 8 CERDIP     | J8-2         | <a href="#">21-0045</a> | -                       |

## Revision History

| REVISION<br>NUMBER | REVISION<br>DATE | DESCRIPTION                                                                                    | PAGES<br>CHANGED |
|--------------------|------------------|------------------------------------------------------------------------------------------------|------------------|
| 0                  | 9/96             | Initial release                                                                                | —                |
| 4                  | 1/01             | Updated <i>Electrical Characteristics</i> Note 3                                               | 5                |
| 5                  | 3/14             | Added lead-free notation to <i>Ordering Information</i> and updated <i>Package Information</i> | 1, 10            |

For pricing, delivery, and ordering information, please contact Maxim Direct at 1-888-629-4642, or visit Maxim Integrated's website at [www.maximintegrated.com](http://www.maximintegrated.com).

Maxim Integrated cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim Integrated product. No circuit patent licenses are implied. Maxim Integrated reserves the right to change the circuitry and specifications without notice at any time. The parametric values (min and max limits) shown in the *Electrical Characteristics* table are guaranteed. Other parametric values quoted in this data sheet are provided for guidance.