



Input voltage up to 144 VDC
Single output of 3.3 to 48 VDC
No input-to-output isolation



Features

- RoHS lead solder exemption compliant
- Efficiency up to 95%
- Low input-output differential voltage
- No derating over temperature
- Board or chassis mountable

Model Selection

Output		Input voltage	Rated power	Efficiency	Type	Options
$V_{o\ nom}$ [VDC]	$I_{o\ nom}$ [A]	V_i [VDC]	$P_{o\ tot}$ [W]	η [%]		
5	2	8 - 80	10	74	PSR 52-7	Y
5	3	8 - 80	15	79	PSR 53-7	-9, i, P, R, Y
5	4	7 - 40	20	83	PSR 54-7	-9, i, P, R, Y
5	5	7 - 35	25	83	PSA 55-7	-9, i, P, R, Y
5.1	2	8 - 40	10.2	75	PSA 5A2-2	iRY-Package
5.1	5	7 - 35	25.5	83	PSA 5A5-2	iRY-Package
12	1.5	18 - 144	18	87	PSA 121.5-7iR	-9, P, Y
12	2.5	15 - 80	30	87	PSR 122.5-7	-9, i, P, R, Y
12	3	15 - 40	36	89	PSA 123-2	iRY-Package
15	1.5	22 - 144	22.5	89	PSA 151.5-7iR	-9, P, Y
15	2.5	19 - 80	37.5	89	PSR 152.5-7	-9, i, P, R, Y
15	3	19 - 40	45	90	PSA 153-2	iRY-Package
24	1.5	31 - 144	36	93	PSA 241.5-7iR	-9, P, Y
24	2	29 - 80	48	92	PSR 242-7	-9, i, P, R, Y
24	2.5	29 - 60	60	93	PSA 242.5-2	iRY-Package
36	1.2	44 - 144	43.2	95	PSA 361-7iR	-9, P, Y
36	2	42 - 80	72	94	PSR 362-7	-9, i, P, R, Y
48	1	58 - 144	48	95	PSA 481-7iR	-9, P, Y

Input

Input voltage	refer to selection chart
No load input current	≤50 mA

Output

Efficiency	$V_{i\text{ nom}}, I_{o\text{ nom}}$	up to 95%
Output voltage setting accuracy	$V_{i\text{ nom}}, I_{o\text{ nom}}$	±0.6% $V_{o\text{ nom}}$
Output voltage switching noise	IEC/EN 61204, total	typ. 0.3%
Line regulation	$V_{i\text{ min}} - V_{i\text{ max}}, I_{o\text{ nom}}$	typ. ±0.3%
Load regulation	$V_{i\text{ nom}}, 0 - I_{o\text{ nom}}$	typ. 0.3%
Minimum load	not required	0 A
Current limitation	rectangular U/I characteristic	typ. 110% $I_{o\text{ nom}}$
Operation in parallel	by current limitation	

Protection

Input reverse polarity	with external fuse	
Input undervoltage lockout		typ. 80% $V_{i\text{ min}}$
Input transient protection	suppressor diode	
Output	no-load, overload and short circuit proof	
Output overvoltage	suppressor diode	typ. 150% $V_{o\text{ nom}}$

Safety

Approvals	EN 60950, UL 1950, CSA C22.2 No. 950	
Protection degree		IP 20/40
Electric strength test voltage	I/case and O/case	500/750/1500 VDC

EMC

Electrostatic discharge	IEC/EN 61000-4-2
Electromagnetic field	IEC/EN 61000-4-3
Electr. fast transients/bursts	IEC/EN 61000-4-4
Surge	IEC/EN 61000-4-5
Conducted disturbances	IEC/EN 61000-4-6
Electromagnetic emissions	CISPR 22/EN 55022

Environmental


Operating ambient temperature	-2, $V_{i\text{ nom}}, I_{o\text{ nom}}$, convection cooled	-10 to 50 °C
Operating case temperature T_C	-2, $V_{i\text{ nom}}, I_{o\text{ nom}}$	-10 to 80 °C
Storage temperature	-2, non operational	-25 to 100 °C
Operating ambient temperature	-7, $V_{i\text{ nom}}, I_{o\text{ nom}}$, convection cooled	-25 to 71 °C
Operating case temperature T_C	-7, $V_{i\text{ nom}}, I_{o\text{ nom}}$	-25 to 95 °C
Storage temperature	-7, non operational	-40 to 100 °C
Damp heat	IEC/EN 60068-2-3	
Vibration, sinusoidal	IEC/EN 60068-2-6	
Shock	IEC/EN 60068-2-27	
Bump	IEC/EN 60068-2-29	
Random vibration	IEC/EN 60068-2-64	
MTBF	MIL-HDBK-217	

Options

Extended temperature range	-40 - 71 °C, ambient, operating	-9
Inhibit, TTL input, output(s) enabled if left open		i
Output voltage adjustment	0 - 108% $V_{o\text{ nom}}$	R
Output voltage adjustment	±8% $V_{o\text{ nom}}$	P
Soldering pins 0.5 x 1.0 mm for PCB mounting		Y

Mechanical data

Tolerances ± 0.3 mm (0.012") unless otherwise indicated.



Accessories

Isolation pads for easy and safe PCB mounting
Filters and ring core chokes for ripple and interference reduction
Adapter kits for DIN-rail and chassis mounting

NUCLEAR AND MEDICAL APPLICATIONS - Power-One products are not designed, intended for use in, or authorized for use as critical components in life support systems, equipment used in hazardous environments, or nuclear control systems without the express written consent of the respective divisional president of Power-One, Inc.

TECHNICAL REVISIONS - The appearance of products, including safety agency certifications pictured on labels, may change depending on the date manufactured. Specifications are subject to change without notice.